Power MOSFET

60 V, 16.5 m Ω , 27 A, Single N-Channel

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter		Symbol	Value	Unit	
Drain-to-Source Voltage		V_{DSS}	60	V	
Gate-to-Source Voltage			V_{GS}	±20	V
Continuous Drain Cur-	Steady State	$T_C = 25^{\circ}C$	I _D	27	Α
rent R _{θJC} (Notes 1 & 3)		T _C = 100°C		19	
Power Dissipation R _{θJC}		T _C = 25°C	P _D	25	W
(Note 1)		$T_C = 100^{\circ}C$		12	
Continuous Drain Current $R_{\theta JA}$ (Notes 1, 2 & 3)	Steady State	T _A = 25°C	I _D	10	Α
		T _A = 100°C		7.2	
Power Dissipation $R_{\theta JA}$		T _A = 25°C	P_{D}	3.6	W
(Notes 1 & 2)		T _A = 100°C		1.8	
Pulsed Drain Current	$T_A = 25^{\circ}C$, $t_p = 10 \mu s$		I _{DM}	130	Α
Operating Junction and Storage Temperature		T _J , T _{stg}	-55 to 175	ç	
Source Current (Body Diode)		I _S	28	Α	
Single Pulse Drain-to-Source Avalanche Energy ($T_J = 25$ °C, $I_{L(pk)} = 2.0$ A)		E _{AS}	93	mJ	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		TL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case (Drain) (Note 1)	$R_{\theta JC}$	6.0	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{ heta JA}$	41	


- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface–mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- 3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.



ON Semiconductor®

www.onsemi.com


V _{(BR)DSS}	R _{DS(on)}	I _D
60 V	16.5 mΩ @ 10 V	27 A
60 V	24.3 mΩ @ 4.5 V	21 A





DPAK CASE 369C STYLE 2

MARKING DIAGRAM & PIN ASSIGNMENT



A = Assembly Location

Y = Year
WW = Work Week
5C684L = Device Code
G = Pb-Free Package

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Test Cond	lition	Min	Тур	Max	Unit
OFF CHARACTERISTICS							•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J				27		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V, V _{DS} = 60 V	T _J = 25°C			10	μΑ
			T _J = 125°C			250	1
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{G}$	S = 20 V			100	nA
ON CHARACTERISTICS (Note 4)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_{D}$	= 20 μΑ	1.2		2.1	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J				4.5		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V, I _D = 15 A			13.7	16.5	mΩ
		V _{GS} = 4.5 V, I	_D = 15 A		19.4	24.3	1
Forward Transconductance	9FS	V _{DS} = 5.0 V, I	_D = 15 A		30		S
CHARGES, CAPACITANCES AND GATE RE	SISTANCES						
Input Capacitance	C _{iss}				700		pF
Output Capacitance	C _{oss}	$V_{GS} = 0 \text{ V, f} = 1.0 \text{ MHz,}$ $V_{DS} = 25 \text{ V}$			300		┦ !
Reverse Transfer Capacitance	C _{rss}				13		
Total Gate Charge		V _{DS} = 30 V,	V _{GS} = 4.5 V		4.6		nC
			V _{GS} = 10 V		9.6		1
Threshold Gate Charge	Q _{G(TH)}		•		1.2		nC
Gate-to-Source Charge	Q _{GS}	$V_{GS} = 4.5 \text{ V}, V_{DS} = 30 \text{ V},$ $I_{D} = 15 \text{ A}$			2.0		
Gate-to-Drain Charge	Q_{GD}				1.2		1
Plateau Voltage	V_{GP}				2.9		V
SWITCHING CHARACTERISTICS (Note 5)							•
Turn-On Delay Time	t _{d(on)}				8.0		ns
Rise Time	t _r	Vcs = 4.5 V. V.	ne = 30 V.		43		1
Turn-Off Delay Time	t _{d(off)}	$V_{GS} = 4.5 \text{ V}, V_{DS} = 30 \text{ V},$ $I_D = 15 \text{ A}, R_G = 2.5 \Omega$			25		1
Fall Time	t _f				40		1
DRAIN-SOURCE DIODE CHARACTERISTIC	S						
Forward Diode Voltage	V_{SD}	V _{GS} = 0 V,	T _J = 25°C		0.9	1.2	V
		$I_{S} = 15 \text{ A}$	T _J = 125°C		0.8		1
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 \text{ V, } dI_{S}/dt = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 15 \text{ A}$			20		ns
Charge Time	ta				10		1
Discharge Time	tb				10		1
Reverse Recovery Charge	Q _{RR}				10		nC

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 6. Drain-to-Source Leakage Current

vs. Voltage

Figure 5. On-Resistance Variation with

Temperature

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

TYPICAL CHARACTERISTICS





Figure 13. Thermal Response

ORDERING INFORMATION

Order Number	Package	Shipping [†]
NTD5C684NLT4G	DPAK (Pb-Free)	2500 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





DOCUMENT NUMBER:	98AON10527D	Electronic versions are uncontrolled except when accessed directly from the Document Reposito Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	DPAK (SINGLE GAUGE)		PAGE 1 OF 1	

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales