

# Silicon Carbide (SiC) MOSFET – EliteSiC, 52 mohm, 1200 V, M3S, TO247-4L, THIN LEADS NTH4LN070N120M3S

## Features

- Typ.  $R_{DS(on)} = 52 \text{ m}\Omega @ V_{GS} = 18 \text{ V}$
- Ultra Low Gate Charge ( $Q_{G(tot)} = 60 \text{ nC}$ )
- High Speed Switching with Low Capacitance ( $C_{oss} = 57 \text{ pF}$ )
- 100% Avalanche Tested
- This Device is Halide Free and RoHS Compliant with exemption 7a, Pb-Free 2LI (on second level interconnection)

## Typical Applications

- Solar Inverters
- Electric Vehicle Charging Stations
- UPS (Uninterruptible Power Supplies)
- Energy Storage Systems
- SMPS (Switch Mode Power Supplies)



## MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter                                                                               |                                    |                                     | Symbol         | Value       | Unit               |
|-----------------------------------------------------------------------------------------|------------------------------------|-------------------------------------|----------------|-------------|--------------------|
| Drain-to-Source Voltage                                                                 |                                    |                                     | $V_{DSS}$      | 1200        | V                  |
| Gate-to-Source Voltage                                                                  |                                    |                                     | $V_{GS}$       | -10/+22     | V                  |
| Continuous Drain Current (Notes 1, 3)                                                   | Steady State                       | $T_C = 25\text{ }^{\circ}\text{C}$  | $I_D$          | 34          | A                  |
| Power Dissipation (Note 1)                                                              |                                    |                                     | $P_D$          | 160         | W                  |
| Continuous Drain Current (Notes 1, 3)                                                   | Steady State                       | $T_C = 100\text{ }^{\circ}\text{C}$ | $I_D$          | 24          | A                  |
| Power Dissipation (Note 1)                                                              |                                    |                                     | $P_D$          | 80          | W                  |
| Pulsed Drain Current (Note 2)                                                           | $T_C = 25\text{ }^{\circ}\text{C}$ |                                     | $I_{DM}$       | 98          | A                  |
| Operating Junction and Storage Temperature Range                                        |                                    |                                     | $T_J, T_{stg}$ | -55 to +175 | $^{\circ}\text{C}$ |
| Source Current (Body Diode)<br>$T_C = 25\text{ }^{\circ}\text{C}, V_{GS} = -3\text{ V}$ |                                    |                                     | $I_S$          | 31          | A                  |
| Single Pulse Drain-to-Source Avalanche Energy (Note 4)                                  |                                    |                                     | $E_{AS}$       | 91          | mJ                 |
| Maximum Lead Temperature for Soldering<br>(1/25" from case for 10 s)                    |                                    |                                     | $T_L$          | 270         | $^{\circ}\text{C}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Single pulse, limited by max junction temperature.
3. The maximum current rating is based on typical  $R_{DS(on)}$  performance.
4. EAS of 91 mJ is based on starting  $T_J = 25^\circ\text{C}$ ;  $L = 1 \text{ mH}$ ,  $I_{AS} = 13.5 \text{ A}$ ,  $V_{DD} = 100 \text{ V}$ ,  $V_{GS} = 18 \text{ V}$ .

| $V_{(BR)DSS}$ | $R_{DS(ON)} \text{ MAX}$     | $I_D \text{ MAX}$ |
|---------------|------------------------------|-------------------|
| 1200 V        | 87 m $\Omega @ 18 \text{ V}$ | 34 A              |



## MARKING DIAGRAM



4LN070120M3S = Specific Device Code  
A = Assembly Location  
Y = Year  
WW = Work Week  
ZZ = Lot Traceability

## ORDERING INFORMATION

| Device           | Package                 | Shipping           |
|------------------|-------------------------|--------------------|
| NTH4LN070N120M3S | TO247-4L,<br>Thin Leads | 30 Units /<br>Tube |

# NTH4LN070N120M3S

**Table 1. THERMAL CHARACTERISTICS**

| Parameter                                   | Symbol          | Max  | Unit |
|---------------------------------------------|-----------------|------|------|
| Junction-to-Case – Steady State (Note 1)    | $R_{\theta JC}$ | 0.94 | °C/W |
| Junction-to-Ambient – Steady State (Note 1) | $R_{\theta JA}$ | 40   |      |

**Table 2. RECOMMENDED OPERATING CONDITIONS**

| Parameter                                  | Symbol     | Value         | Unit |
|--------------------------------------------|------------|---------------|------|
| Operation Values of Gate-to-Source Voltage | $V_{GSop}$ | -5...0<br>+18 | V    |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

\* Operation at 0 V turn-off requires consideration of switching behavior and system-level design trade-offs. Design guidance and application considerations are provided in Application Note [AND90255/D](#).

**Table 3. ELECTRICAL CHARACTERISTICS** ( $T_J = 25\text{ °C}$  unless otherwise specified)

| Parameter | Symbol | Test Condition | Min | Typ | Max | Unit |
|-----------|--------|----------------|-----|-----|-----|------|
|-----------|--------|----------------|-----|-----|-----|------|

## OFF-STATE CHARACTERISTICS

|                                                           |                   |                                                                   |      |     |     |      |
|-----------------------------------------------------------|-------------------|-------------------------------------------------------------------|------|-----|-----|------|
| Drain-to-Source Breakdown Voltage                         | $V_{(BR)DSS}$     | $V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$                          | 1200 |     |     | V    |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | $V_{(BR)DSS}/T_J$ | $I_D = 1\text{ mA}$ , referenced to $25\text{ °C}$ (Note 6)       |      | 0.3 |     | V/°C |
| Zero Gate Voltage Drain Current                           | $I_{DSS}$         | $V_{GS} = 0\text{ V}, V_{DS} = 1200\text{ V}, T_J = 25\text{ °C}$ |      |     | 100 | μA   |
| Gate-to-Source Leakage Current                            | $I_{GSS}$         | $V_{GS} = +22/-10\text{ V}, V_{DS} = 0\text{ V}$                  |      |     | ±1  | μA   |

## ON-STATE CHARACTERISTICS (Note 2)

|                               |              |                                                                         |      |     |     |    |
|-------------------------------|--------------|-------------------------------------------------------------------------|------|-----|-----|----|
| Gate Threshold Voltage        | $V_{GS(TH)}$ | $V_{GS} = V_{DS}, I_D = 7\text{ mA}$                                    | 2.04 | 2.7 | 4.4 | V  |
| Drain-to-Source On Resistance | $R_{DS(on)}$ | $V_{GS} = 18\text{ V}, I_D = 15\text{ A}, T_J = 25\text{ °C}$           |      | 52  | 87  | mΩ |
|                               |              | $V_{GS} = 18\text{ V}, I_D = 15\text{ A}, T_J = 175\text{ °C}$ (Note 6) |      | 110 |     |    |
| Forward Transconductance      | $g_{FS}$     | $V_{DS} = 10\text{ V}, I_D = 15\text{ A}$ (Note 6)                      |      | 12  |     | S  |

## CHARGES, CAPACITANCES & GATE RESISTANCE

|                              |              |                                                                     |  |      |  |    |
|------------------------------|--------------|---------------------------------------------------------------------|--|------|--|----|
| Input Capacitance            | $C_{ISS}$    | $V_{GS} = 0\text{ V}, f = 1\text{ MHz}, V_{DS} = 800\text{ V}$      |  | 1230 |  | pF |
| Output Capacitance           | $C_{OSS}$    |                                                                     |  | 57   |  |    |
| Reverse Transfer Capacitance | $C_{RSS}$    |                                                                     |  | 5    |  |    |
| Total Gate Charge            | $Q_{G(TOT)}$ | $V_{GS} = -3/18\text{ V}, V_{DS} = 800\text{ V}, I_D = 15\text{ A}$ |  | 60   |  | nC |
| Gate-to-Source Charge        | $Q_{GS}$     |                                                                     |  | 15   |  |    |
| Gate-to-Drain Charge         | $Q_{GD}$     |                                                                     |  | 16   |  |    |
| Gate-Resistance              | $R_G$        | $f = 1\text{ MHz}$                                                  |  | 4.3  |  | Ω  |

## SWITCHING CHARACTERISTICS

|                         |              |                                                                                                                        |  |     |  |    |
|-------------------------|--------------|------------------------------------------------------------------------------------------------------------------------|--|-----|--|----|
| Turn-On Delay Time      | $t_{d(ON)}$  | $V_{GS} = -3/18\text{ V}, V_{DS} = 800\text{ V}, I_D = 15\text{ A}, R_G = 4.7\text{ Ω}$<br>Inductive load (Notes 5, 6) |  | 9.2 |  | ns |
| Rise Time               | $t_r$        |                                                                                                                        |  | 11  |  |    |
| Turn-Off Delay Time     | $t_{d(OFF)}$ |                                                                                                                        |  | 29  |  |    |
| Fall Time               | $t_f$        |                                                                                                                        |  | 8.8 |  |    |
| Turn-On Switching Loss  | $E_{ON}$     |                                                                                                                        |  | 124 |  | μJ |
| Turn-Off Switching Loss | $E_{OFF}$    |                                                                                                                        |  | 36  |  |    |
| Total Switching Loss    | $E_{tot}$    |                                                                                                                        |  | 160 |  |    |

# NTH4LN070N120M3S

**Table 3. ELECTRICAL CHARACTERISTICS** ( $T_J = 25\text{ }^{\circ}\text{C}$  unless otherwise specified) (continued)

| Parameter                                          | Symbol    | Test Condition                                                                                                               | Min | Typ  | Max | Unit          |
|----------------------------------------------------|-----------|------------------------------------------------------------------------------------------------------------------------------|-----|------|-----|---------------|
| <b>SOURCE-DRAIN DIODE CHARACTERISTICS</b>          |           |                                                                                                                              |     |      |     |               |
| Continuous Source-Drain Diode Forward Current      | $I_{SD}$  | $V_{GS} = -3\text{ V}, T_C = 25\text{ }^{\circ}\text{C}$ (Note 6)                                                            |     |      | 31  | A             |
| Pulsed Source-Drain Diode Forward Current (Note 2) | $I_{SDM}$ |                                                                                                                              |     |      | 98  |               |
| Forward Diode Voltage                              | $V_{SD}$  | $V_{GS} = -3\text{ V}, I_{SD} = 15\text{ A}, T_J = 25\text{ }^{\circ}\text{C}$                                               |     | 4.7  |     | V             |
| Reverse Recovery Time                              | $t_{RR}$  | $V_{GS} = -3/18\text{ V}, I_{SD} = 15\text{ A},$<br>$dI_S/dt = 1000\text{ A}/\mu\text{s}, V_{DS} = 800\text{ V}$<br>(Note 6) |     | 14.4 |     | ns            |
| Reverse Recovery Charge                            | $Q_{RR}$  |                                                                                                                              |     | 60   |     | nC            |
| Reverse Recovery Energy                            | $E_{REC}$ |                                                                                                                              |     | 4.8  |     | $\mu\text{J}$ |
| Peak Reverse Recovery Current                      | $I_{RRM}$ |                                                                                                                              |     | 8.4  |     | A             |
| Charge Time                                        | $T_A$     |                                                                                                                              |     | 7.9  |     | ns            |
| Discharge Time                                     | $T_B$     |                                                                                                                              |     | 6.5  |     | ns            |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5.  $E_{ON}/E_{OFF}$  result is with body diode.

6. Defined by design, not subject to production test.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Switching Loss vs. Drain Current

TYPICAL CHARACTERISTICS




Figure 7. Switching Loss vs. Drain-to-Source Voltage




Figure 8. Switching Loss vs. Gate Resistance




Figure 9. Switching Loss vs. Temperature




Figure 10. Reverse Drain Current vs. Body Diode Forward Voltage




Figure 11. Gate-to-Source Voltage vs. Total Charge




Figure 12. Capacitance vs. Drain-to-Source Voltage

TYPICAL CHARACTERISTICS




Figure 13. Unclamped Inductive Switching Capability




Figure 14. Maximum Continuous Drain Current vs. Case Temperature




Figure 15. Safe Operating Area




Figure 16. Single Pulse Maximum Power Dissipation





Figure 17. Junction-to-Case Transient Thermal Response

# NTH4LN070N120M3S


## REVISION HISTORY

| Revision | Description of Changes                                 | Date      |
|----------|--------------------------------------------------------|-----------|
| 0        | Initial document release                               | 7/31/2026 |
| 1        | Changed Gate Charge value to 60 and updated Figure 11. | 8/10/2026 |



**TO-247 4-LEAD, THIN LEADS**  
**CASE 340CW**  
**ISSUE A**

DATE 16 SEP 2019



**NOTES:**

- A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
- B. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR EXTRUSIONS.
- C. ALL DIMENSIONS ARE IN MILLIMETERS.

| DIM | MILLIMETERS |       |       |
|-----|-------------|-------|-------|
|     | MIN         | NOM   | MAX   |
| A   | 4.80        | 5.00  | 5.20  |
| A1  | 2.10        | 2.40  | 2.70  |
| A2  | 1.80        | 2.00  | 2.20  |
| b   | 0.57        | 0.70  | 0.83  |
| b2  | 1.07        | 1.20  | 1.33  |
| b3  | 1.20        | 1.40  | 1.60  |
| b4  | 2.02        | 2.22  | 2.42  |
| c   | 0.50        | 0.60  | 0.70  |
| D   | 22.34       | 22.54 | 22.74 |
| D1  | 16.00       | 16.30 | 16.50 |
| D2  | 0.97        | 1.17  | 1.37  |
| e   |             | 2.54  |       |
| e1  |             | 2.79  |       |
| e2  |             | 5.08  |       |
| E   | 15.40       | 15.60 | 15.80 |
| E1  | 12.80       | 13.00 | 13.20 |
| E2  | 4.80        | 5.00  | 5.20  |
| L   | 18.12       | 18.42 | 18.72 |
| L1  | 2.42        | 2.62  | 2.82  |
| Øp  | 3.40        | 3.60  | 3.80  |
| ØP1 | 6.60        | 6.80  | 7.00  |
| Q   | 5.97        | 6.17  | 6.37  |
| S   | 5.97        | 6.17  | 6.37  |

|                         |                                  |                                                                                                                                                                                     |
|-------------------------|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON80893G</b>               | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>TO-247 4-LEAD, THIN LEADS</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)