NTMFS4923NE

Power MOSFET
30 V, 91 A, Single N−Channel, SO−8 FL

Features

- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Optimized Gate Charge to Minimize Switching Losses
- Dual Sided Cooling Capability
- These Devices are Pb−Free, Halogen Free and are RoHS Compliant

Applications

- CPU Power Delivery, DC−DC Converters

MAXIMUM RATINGS (T_J = 25°C unless otherwise stated)

Parameter			Symbol	Value	Unit
Drain−to−Source Voltage			V_{DSS}	30	V
Gate−to−Source Voltage			V_{GS}	±20	V
Continuous Drain Current $R_{\theta JA}$ (Note 1)	Steady State	T_A = 25°C	I_D	21.4	A
		T_A = 100°C		13.5	
Power Dissipation $R_{\theta JA}$ (Note 1)		T_A = 25°C	P_D	2.63	W
Continuous Drain Current $R_{\theta JA} \le$ 10 s (Note 1)		T_A = 25°C	I_D	38.8	A
		T_A = 100°C		24.5	
Power Dissipation $R_{\theta JA} \le$ 10 s (Note 1)		T_A = 25°C	P_D	8.7	W
Continuous Drain Current $R_{\theta JA}$ (Note 2)		T_A = 25°C	I_D	12.7	A
		T_A = 100°C		8.0	
Power Dissipation $R_{\theta JA}$ (Note 2)		T_A = 25°C	P_D	0.93	W
Continuous Drain Current $R_{\theta JC}$ (Note 1)		T_C = 25°C	I_D	91	A
		T_C = 85°C		66	
Power Dissipation $R_{\theta JC}$ (Note 1)		T_C = 25°C	P_D	48	W
Pulsed Drain Current	T_A = 25°C, t_p = 10 μs		I_{DM}	275	A
Current Limited by Package		T_A = 25°C	I_{Dmax}	100	A
Operating Junction and Storage Temperature			T_J, T_{STG}	−40 to +150	°C
Source Current (Body Diode)			I_S	44	A
Drain to Source DV/DT			dV/d_t	6	V/ns
Single Pulse Drain−to−Source Avalanche Energy T_J = 25°C, V_{DD} = 24 V, V_{GS} = 10 V, I_L = 47 A_{pk}, L = 0.1 mH, R_G = 25 Ω			E_{AS}	110	mJ
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)			T_L	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Surface−mounted on FR4 board using 1 sq−in pad, 1 oz Cu.
2. Surface−mounted on FR4 board using the minimum recommended pad size.

ON Semiconductor®

http://onsemi.com

$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
30 V	3.3 mΩ @ 10 V	91 A
	4.8 mΩ @ 4.5 V	75 A



N−CHANNEL MOSFET



SO−8 FLAT LEAD
CASE 488AA
STYLE 1

MARKING DIAGRAM



A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping†
NTMFS4923NET1G	SO−8 FL (Pb−Free)	1500 / Tape & Reel
NTMFS4923NET3G	SO−8 FL (Pb−Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction−to−Case (Drain)	$R_{\theta JC}$	2.6	°C/W
Junction−to−Ambient − Steady State (Note 3)	$R_{\theta JA}$	47.5	
Junction−to−Ambient − Steady State (Note 4)	$R_{\theta JA}$	134.8	
Junction−to−Ambient − (t ≤ 10 s) (Note 3)	$R_{\theta JA}$	14.4	
Junction−to−Top	$R_{\theta JT}$	8.3	

3. Surface−mounted on FR4 board using 1 sq−in pad, 1 oz Cu.
4. Surface−mounted on FR4 board using the minimum recommended pad size.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
OFF CHARACTERISTICS							
Drain−to−Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 250 μA		30			V
Drain−to−Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$				15		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{GS} = 0 V, V_{DS} = 24 V	T_J = 25°C			1.0	μA
			T_J = 125°C			10	
Gate−to−Source Leakage Current	I_{GSS}	V_{DS} = 0 V, V_{GS} = ±20 V				±100	nA
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 250 μA		1.2	1.63	2.0	V
Negative Threshold Temperature Coefficient	$V_{GS(TH)}/T_J$				4.0		mV/°C
Drain−to−Source On Resistance	$R_{DS(on)}$	V_{GS} = 10 V	I_D = 30 A		2.7	3.3	mΩ
			I_D = 15 A		2.7		
		V_{GS} = 4.5 V	I_D = 30 A		3.7	4.8	
			I_D = 15 A		3.7		
Forward Transconductance	g_{FS}	V_{DS} = 1.5 V, I_D = 15 A			32		S
CHARGES, CAPACITANCES & GATE RESISTANCE							
Input Capacitance	C_{ISS}	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 15 V			3579	4850	pF
Output Capacitance	C_{OSS}				1264	1710	
Reverse Transfer Capacitance	C_{RSS}				39	59	
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 4.5 V, V_{DS} = 15 V; I_D = 30 A			22		nC
Threshold Gate Charge	$Q_{G(TH)}$				5.6		
Gate−to−Source Charge	Q_{GS}				10.2		
Gate−to−Drain Charge	Q_{GD}				3.0		
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 10 V, V_{DS} = 15 V; I_D = 30 A			49.4		nC
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	$t_{d(ON)}$	V_{GS} = 4.5 V, V_{DS} = 15 V, I_D = 15 A, R_G = 3.0 Ω			16.3		ns
Rise Time	t_r				20		
Turn−Off Delay Time	$t_{d(OFF)}$				27.5		
Fall Time	t_f				6.6		

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	$t_{d(ON)}$	V_{GS} = 10 V, V_{DS} = 15 V, I_D = 15 A, R_G = 3.0 Ω			11.2		ns
Rise Time	t_r				18.7		
Turn−Off Delay Time	$t_{d(OFF)}$				28.3		
Fall Time	t_f				12.1		
DRAIN−SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V_{SD}	V_{GS} = 0 V, I_S = 30 A	T_J = 25°C		0.85	1.1	V
			T_J = 125°C		0.72		
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, dIS/dt = 100 A/μs, I_S = 30 A			44.4		ns
Charge Time	t_a				21.6		
Discharge Time	t_b				22.8		
Reverse Recovery Charge	Q_{RR}				45		nC
PACKAGE PARASITIC VALUES							
Source Inductance	L_S	T_A = 25°C			0.65		nH
Drain Inductance	L_D				0.005		nH
Gate Inductance	L_G				1.84		nH
Gate Resistance	R_G				1.1	2.0	Ω

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



Figure 1. On−Region Characteristics



Figure 2. Transfer Characteristics



Figure 3. On−Resistance vs. V_{GS}



Figure 4. On−Resistance vs. Drain Current and Gate Voltage



Figure 5. On−Resistance Variation with Temperature



Figure 6. Drain−to−Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS



Figure 7. Capacitance Variation



Figure 8. Gate−to−Source and Drain−to−Source Voltage vs. Total Charge



Figure 9. Resistive Switching Time Variation vs. Gate Resistance



Figure 10. Diode Forward Voltage vs. Current



Figure 11. Maximum Rated Forward Biased Safe Operating Area



Figure 12. Maximum Avalanche Energy vs. Starting Junction Temperature

TYPICAL CHARACTERISTICS



Figure 13. Thermal Response



Figure 14. GFS vs. ID



SCALE 2:1

DFN5 5x6, 1.27P
(SO−8FL)
CASE 488AA
ISSUE N

DATE 25 JUN 2018



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

	MILLIMETERS		
DIM	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.00	–––	0.05
b	0.33	0.41	0.51
c	0.23	0.28	0.33
D	5.00	5.15	5.30
D1	4.70	4.90	5.10
D2	3.80	4.00	4.20
E	6.00	6.15	6.30
E1	5.70	5.90	6.10
E2	3.45	3.65	3.85
e	1.27 BSC		
G	0.51	0.575	0.71
K	1.20	1.35	1.50
L	0.51	0.575	0.71
L1	0.125 REF		
M	3.00	3.40	3.80
θ	0 °	–––	12 °



GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present. Some products may not follow the Generic Marking.

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

STYLE 1:
PIN 1. SOURCE
2. SOURCE
3. SOURCE
4. GATE
5. DRAIN

STYLE 2:
PIN 1. ANODE
2. ANODE
3. ANODE
4. NO CONNECT
5. CATHODE

*For additional information on our Pb−Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	**98AON14036D**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.	
DESCRIPTION:	**DFN5 5x6, 1.27P (SO−8FL)**		**PAGE 1 OF 1**

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales