

# MOSFET - Power, Single N-Channel, STD Gate, DUAL COOL<sup>®</sup>, DFN8 5x6

80 V, 1.9 mΩ, 201 A

Preliminary Document

NTMFSCHT1D9N08X

## Features

- Advanced Dual-Side Cool Package with Enhanced Heat-Dissipation Molding Compound
- Low  $Q_{RR}$ , Soft Recovery Body Diode
- Low  $R_{DS(on)}$  to Minimize Conduction Losses
- Low  $Q_g$  to Minimize Gate Driving Losses
- MSL1 Robust Packaging Design
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

## Applications

- Power Supply Unit (PSU)
- DC/DC Intermediated Bus Converter
- Control FET in High Switching Frequency Application
- Synchronous Rectifier
- ORing FET


## MAXIMUM RATINGS ( $T_J = 25\text{ }^{\circ}\text{C}$ , Unless otherwise specified)

| Parameter                                                            |                                                                        | Symbol         | Value       | Unit               |
|----------------------------------------------------------------------|------------------------------------------------------------------------|----------------|-------------|--------------------|
| Drain-to-Source Voltage                                              |                                                                        | $V_{DSS}$      | 80          | V                  |
| Gate-to-Source Voltage                                               |                                                                        | $V_{GS}$       | $\pm 20$    | V                  |
| Continuous Drain Current<br>(Notes 1, 2)                             | $T_C = 25\text{ }^{\circ}\text{C}$                                     | $I_D$          | 201         | A                  |
|                                                                      | $T_C = 100\text{ }^{\circ}\text{C}$                                    |                | 142         |                    |
| Power Dissipation (Notes 1, 2)                                       | $T_C = 25\text{ }^{\circ}\text{C}$                                     | $P_D$          | 164         | W                  |
| Pulsed Drain Current                                                 | $T_C = 25\text{ }^{\circ}\text{C}$ ,<br>$t_p = 100\text{ }\mu\text{s}$ | $I_{DM}$       | 866         | A                  |
| Pulsed Source Current<br>(Body Diode)                                |                                                                        | $I_{SM}$       | 866         | A                  |
| Operating Junction and Storage Temperature Range                     |                                                                        | $T_J, T_{stg}$ | -55 to +175 | $^{\circ}\text{C}$ |
| Source-Drain Current<br>(Body Diode)                                 | $T_C = 25\text{ }^{\circ}\text{C}$                                     | $I_S$          | 164         | A                  |
| Single Pulse Avalanche Energy ( $I_{pk} = 58\text{ A}$ )<br>(Note 3) |                                                                        | $E_{AS}$       | 168         | mJ                 |
| Lead Temperature for Soldering Purposes<br>(1/8" from case for 10 s) |                                                                        | $T_L$          | 260         | $^{\circ}\text{C}$ |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- The entire application environment impacts the thermal resistance values shown. They are not constants and are only valid for the particular conditions noted.
- Actual continuous current will be limited by thermal & electromechanical application board design.
- $E_{AS}$  of 168 mJ is based on started  $T_J = 25\text{ }^{\circ}\text{C}$ ,  $I_{AS} = 58\text{ A}$ ,  $V_{DD} = 64\text{ V}$ ,  $V_{GS} = 10\text{ V}$ , 100% avalanche tested.

| $V_{(BR)DSS}$ | $R_{DS(ON)} \text{ MAX}$        | $I_D \text{ MAX}$ |
|---------------|---------------------------------|-------------------|
| 80 V          | 1.9 mΩ @ $V_{GS} = 10\text{ V}$ | 201 A             |




N-CHANNEL MOSFET



DFN8  
CASE 506EA

## MARKING DIAGRAM



XX = Specific Device Code  
A = Assembly Location  
Y = Year  
W = Work Week  
Z = Assembly Lot Code

## ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

This Preliminary document is for informational purposes only. onsemi may update or withdraw it without notice. Content and referenced products are under development and subject to change.

# NTMFSCHT1D9N08X

## THERMAL CHARACTERISTICS

| Parameter                                        | Symbol           | Max  | Unit |
|--------------------------------------------------|------------------|------|------|
| Thermal Resistance, Junction-to-Case (Bottom)    | $R_{\theta JCB}$ | 0.91 | °C/W |
| Thermal Resistance, Junction-to-Case (Top)       | $R_{\theta JCT}$ | 0.92 |      |
| Thermal Resistance, Junction-to-Ambient (Note 4) | $R_{\theta JA}$  | 39   |      |

4. Actual continuous current will be limited by thermal & electromechanical application board design.

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise specified)

| Parameter | Symbol | Test Conditions | Min | Typ | Max | Unit |
|-----------|--------|-----------------|-----|-----|-----|------|
|-----------|--------|-----------------|-----|-----|-----|------|

### OFF CHARACTERISTICS

|                                                           |                                   |                                                                  |    |    |     |               |
|-----------------------------------------------------------|-----------------------------------|------------------------------------------------------------------|----|----|-----|---------------|
| Drain-to-Source Breakdown Voltage                         | $V_{(BR)DSS}$                     | $V_{GS} = 0\text{ V}, I_D = 1\text{ mA}, T_J = 25^\circ\text{C}$ | 80 |    |     | V             |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | $\Delta V_{(BR)DSS} / \Delta T_J$ | $I_D = 1\text{ mA}$ , Referenced to $25^\circ\text{C}$           |    | 32 |     | mV/°C         |
| Zero Gate Voltage Drain Current                           | $I_{DSS}$                         | $V_{DS} = 80\text{ V}, T_J = 25^\circ\text{C}$                   |    |    | 10  | $\mu\text{A}$ |
|                                                           |                                   | $V_{DS} = 80\text{ V}, T_J = 125^\circ\text{C}$ (Note 5)         |    |    | 250 |               |
| Gate-to-Source Leakage Current                            | $I_{GSS}$                         | $V_{DS} = 0\text{ V}, V_{GS} = 20\text{ V}$                      |    |    | 100 | nA            |

### ON CHARACTERISTICS

|                                                |                                  |                                                                   |     |      |     |            |
|------------------------------------------------|----------------------------------|-------------------------------------------------------------------|-----|------|-----|------------|
| Drain-to-Source On Resistance                  | $R_{DS(ON)}$                     | $V_{GS} = 10\text{ V}, I_D = 50\text{ A}, T_J = 25^\circ\text{C}$ |     | 1.6  | 1.9 | m $\Omega$ |
|                                                |                                  | $V_{GS} = 6\text{ V}, I_D = 25\text{ A}, T_J = 25^\circ\text{C}$  |     | 2.5  | 3.8 |            |
| Gate Threshold Voltage                         | $V_{GS(TH)}$                     | $V_{GS} = V_{DS}, I_D = 252\text{ }\mu\text{A}$                   | 2.4 |      | 3.6 | V          |
| Gate Threshold Voltage Temperature Coefficient | $\Delta V_{GS(TH)} / \Delta T_J$ | $V_{GS} = V_{DS}, I_D = 252\text{ }\mu\text{A}$                   |     | -7.5 |     | mV/°C      |
| Forward Transconductance                       | $g_{FS}$                         | $V_{DS} = 5\text{ V}, I_D = 50\text{ A}$                          |     | 158  |     | S          |

### CHARGES, CAPACITANCES & GATE RESISTANCE

|                                       |              |                                                                                                                                       |      |      |      |          |
|---------------------------------------|--------------|---------------------------------------------------------------------------------------------------------------------------------------|------|------|------|----------|
| Input Capacitance (Note 5)            | $C_{ISS}$    | $V_{GS} = 0\text{ V}, V_{DS} = 40\text{ V}, f = 1\text{ MHz}$                                                                         | 2235 | 4470 | 6705 | pF       |
| Output Capacitance (Note 5)           | $C_{OSS}$    |                                                                                                                                       |      | 1290 | 1935 |          |
| Reverse Transfer Capacitance (Note 5) | $C_{RSS}$    |                                                                                                                                       |      | 20   | 40   |          |
| Output Charge                         | $Q_{OSS}$    | $V_{GS} = 6\text{ V}, V_{DD} = 40\text{ V}, I_D = 50\text{ A}$<br><br>$V_{GS} = 10\text{ V}, V_{DD} = 40\text{ V}, I_D = 50\text{ A}$ |      | 93   |      | nC       |
| Total Gate Charge (Note 5)            | $Q_{G(TOT)}$ |                                                                                                                                       |      | 39   | 59   |          |
| Threshold Gate Charge                 | $Q_{G(TH)}$  |                                                                                                                                       |      | 63   | 95   |          |
| Gate-to-Source Charge                 | $Q_{GS}$     |                                                                                                                                       |      | 14   |      |          |
| Gate-to-Drain Charge                  | $Q_{GD}$     |                                                                                                                                       |      | 21   |      |          |
| Gate-to-Drain Charge                  | $Q_{GD}$     |                                                                                                                                       |      | 10   | 20   |          |
| Gate Plateau Voltage                  | $V_{GP}$     |                                                                                                                                       |      | 4.7  |      | V        |
| Gate Resistance (Note 5)              | $R_G$        | $f = 1\text{ MHz}$                                                                                                                    | 0.4  | 0.8  | 1.2  | $\Omega$ |

### SWITCHING CHARACTERISTICS

|                     |              |                                                                                                                    |  |    |  |    |
|---------------------|--------------|--------------------------------------------------------------------------------------------------------------------|--|----|--|----|
| Turn-On Delay Time  | $t_{d(ON)}$  | Resistive Load,<br>$V_{GS} = 0/10\text{ V}, V_{DD} = 40\text{ V},$<br>$I_D = 50\text{ A}, R_G = 2.5\text{ }\Omega$ |  | 29 |  | ns |
| Rise Time           | $t_r$        |                                                                                                                    |  | 9  |  |    |
| Turn-Off Delay Time | $t_{d(OFF)}$ |                                                                                                                    |  | 42 |  |    |
| Fall Time           | $t_f$        |                                                                                                                    |  | 7  |  |    |

### SOURCE-TO-DRAIN DIODE CHARACTERISTICS

|                       |          |                                                                   |  |     |   |   |
|-----------------------|----------|-------------------------------------------------------------------|--|-----|---|---|
| Forward Diode Voltage | $V_{SD}$ | $V_{GS} = 0\text{ V}, I_S = 50\text{ A}, T_J = 25^\circ\text{C}$  |  | 0.8 | 1 | V |
|                       |          | $V_{GS} = 0\text{ V}, I_S = 50\text{ A}, T_J = 125^\circ\text{C}$ |  | 0.6 |   |   |

# NTMFSCHT1D9N08X

## ELECTRICAL CHARACTERISTICS ( $T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified) (continued)

| Parameter                                    | Symbol   | Test Conditions                                                                                                                                    | Min | Typ | Max | Unit |
|----------------------------------------------|----------|----------------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|-----|------|
| <b>SOURCE-TO-DRAIN DIODE CHARACTERISTICS</b> |          |                                                                                                                                                    |     |     |     |      |
| Reverse Recovery Time                        | $t_{RR}$ | $V_{GS} = 0\text{ V}$ , $dI/dt = 1000\text{ A}/\mu\text{s}$ ,<br>$I_S = 50\text{ A}$ , $V_{DD} = 40\text{ V}$ , $T_J = 25\text{ }^{\circ}\text{C}$ |     | 26  |     | ns   |
| Charge Time                                  | $t_a$    |                                                                                                                                                    |     | 15  |     |      |
| Discharge Time                               | $t_b$    |                                                                                                                                                    |     | 11  |     |      |
| Reverse Recovery Charge                      | $Q_{RR}$ |                                                                                                                                                    |     | 202 |     | nC   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Defined by design, not subject to production test.

# NTMFSCHT1D9N08X

## TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate Voltage




Figure 4. On-Resistance vs. Drain Current




Figure 5. Normalized ON Resistance vs. Junction Temperature




Figure 6. Drain Leakage Current vs. Drain Voltage

# NTMFSCHT1D9N08X

## TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Characteristics




Figure 11. Safe Operating Area (SOA)




Figure 12. Avalanche Current vs Pulse Time (UIS)

# NTMFSCHT1D9N08X

## TYPICAL CHARACTERISTICS




Figure 13. Gate Threshold Voltage vs Junction Temperature




Figure 14. Maximum Current vs. Case Temperature




Figure 15. Transient Thermal Response

## ORDERING INFORMATION

| Device             | Device Marking | Package                                | Shipping <sup>†</sup> |
|--------------------|----------------|----------------------------------------|-----------------------|
| NTMFSCHT1D9N08XTWG | 7W             | DFN8 4.9x5.8<br>(Pb-Free/Halogen Free) | 3000 / Tape & Reel    |

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).

DUAL COOL is a registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.

# NTMFSCHT1D9N08X

## REVISION HISTORY

| Revision | Description of Changes                                                                                | Date      |
|----------|-------------------------------------------------------------------------------------------------------|-----------|
| P0       | Initial Preliminary Document release.                                                                 | 11/5/2025 |
| P1       | Update fo Drain-to-Source On Resistance $I_D$ test condition in the Electrical Characteristics table. | 3/20/2026 |
| P2       | Edits to all tables, note 3, add characteristics curves, remove asterisk and its reference            | 7/6/2026  |
| P3       | Change the ID / IS values in the EC table, edit a figure 11 label                                     | 7/20/2026 |
| P4       | Table value changes and figure label edits                                                            | 7/23/2026 |





**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)