
MOSFET – Power, Single N-Channel, STD Gate, DUAL COOL®, DFN8 5x6

80 V, 3 mΩ, 135 A

NTMFSCHT3D0N08X

$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
80 V	3 mΩ @ 10 V	135 A




N-CHANNEL MOSFET

Features

- Advanced Dual-Side Cool Package with Enhanced Heat-Dissipation Molding Compound
- Low Q_{RR}, Soft Recovery Body Diode
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Q_g to Minimize Gate Driving Losses
- MSL1 Robust Packaging Design
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Power Supply Unit (PSU)
- DC/DC Intermediated Bus Converter
- Control FET in High Switching Frequency Application
- Synchronous Rectifier
- ORing FET



DFN8
CASE 506EA


MAXIMUM RATINGS (T_J = 25 °C unless otherwise stated)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V_{DSS}	80	V
Gate-to-Source Voltage		V_{GS}	±20	V
Continuous Drain Current (Note 1)	T_C = 25 °C	I_D	135	A
	T_C = 100 °C		96	
Power Dissipation (Note 1)	T_C = 25 °C	P_D	119	W
Pulsed Drain Current	T_C = 25 °C, t_p = 100 μs	I_{DM}	543	A
Pulsed Source Current (Body Diode)		I_{SM}	543	
Operating Junction and Storage Temperature Range		T_J, T_{STG}	−55 to +175	°C
Source Current (Body Diode)		I_S	119	A
Single Pulse Avalanche Energy (I_{PK} = 47 A) (Note 3)		E_{AS}	110	mJ
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)		T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Actual continuous current will be limited by thermal & electromechanical application board design.
3. E_{AS} of 110 mJ is based on started T_J = 25 °C, I_{AS} = 47 A, V_{DD} = 64 V, V_{GS} = 10 V, 100% avalanche tested

MARKING DIAGRAM



XX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
Z = Assembly Lot Code

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 6 of this data sheet.

© Semiconductor Components Industries, LLC, 2023

THERMAL CHARACTERISTICS

Parameter	Symbol	Max	Unit
Thermal Resistance, Junction-to-Case (Bottom)	$R_{\theta JCB}$	1.3	°C/W
Thermal Resistance, Junction-to-Case (Top)	$R_{\theta JCT}$	1.34	°C/W
Thermal Resistance, Junction-to-Ambient (Notes 4 and 5)	$R_{\theta JA}$	39	°C/W

4. Surface-mounted on FR4 board using 1 in^2 pad size, 1 oz. Cu pad.
5. R_{thJA} is determined by the user's board design.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA	80			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	I_D = 1 mA. Referenced to 25 °C		31.6		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 80 V, T_J = 25 °C			10	μA
		V_{DS} = 80 V, T_J = 125 °C			250 Note 6	
Gate-to-Source Leakage Current	I_{GSS}	V_{DS} = 0 V, V_{GS} = 20 V			100	nA
ON CHARACTERISTICS						
Drain-to-Source On Resistance	$R_{DS(on)}$	V_{GS} = 10 V, I_D = 31 A		2.5	3	mΩ
		V_{GS} = 8 V, I_D = 31 A		2.8	3.4	
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 153 μA	2.4		3.6	V
Gate Threshold Voltage Temperature Coefficient	$\Delta V_{GS(TH)}/\Delta T_J$	V_{GS} = V_{DS}, I_D = 153 μA		−7.5		mV/°C
Forward Transconductance	g_{FS}	V_{DS} = 5 V, I_D = 31 A		97		S
CHARGES, CAPACITANCES & GATE RESISTANCE						
Input Capacitance (Note 6)	C_{ISS}	V_{GS} = 0 V, V_{DS} = 40 V, f = 1 MHz	1340	2680	4020	pF
Output Capacitance (Note 6)	C_{OSS}			780	1170	
Reverse Transfer Capacitance (Note 6)	C_{RSS}			12	24	
Output Charge	Q_{OSS}			56		nC
Total Gate Charge (Note 6)	$Q_{G(TOT)}$	V_{GS} = 8 V, V_{DD} = 40 V; I_D = 31 A		30	45	nC
		V_{GS} = 10 V, V_{DD} = 40 V; I_D = 31 A		38	57	nC
Threshold Gate Charge	$Q_{G(TH)}$			8		
Gate-to-Source Charge	Q_{GS}			13		
Gate-to-Drain Charge (Note 6)	Q_{GD}			6	12	
Gate Plateau Voltage	V_{GP}			4.7		V
Gate Resistance (Note 6)	R_G	f = 1 MHz	0.35	0.7	1.05	Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	Resistive Load, V_{GS} = 0/10 V, V_{DD} = 40 V, I_D = 31 A, R_G = 2.5 Ω		23		ns
Rise Time	t_r			7		
Turn-Off Delay Time	$t_{d(OFF)}$			32		
Fall Time	t_f			5		
SOURCE-TO-DRAIN DIODE CHARACTERISTICS						
Forward Diode Voltage	V_{SD}	V_{GS} = 0 V, I_S = 31 A, T_J = 25 °C		0.82	1.0	V
		V_{GS} = 0 V, I_S = 31 A, T_J = 125 °C		0.66		

Share Feedback
Your Opinion Matters

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
SOURCE-TO-DRAIN DIODE CHARACTERISTICS						
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, dI/dt = 1000 A/μs, I_S = 31 A, V_{DD} = 40 V		22		ns
Charge Time	t_a			12		
Discharge Time	t_b			10		
Reverse Recovery Charge	Q_{RR}			144		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

6. Defined by design, not subject to production test.

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate Voltage




Figure 4. On-Resistance vs. Drain Current




Figure 5. Normalized ON Resistance vs. Junction Temperature




Figure 6. Drain Leakage Current vs. Drain Voltage

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Characteristics




Figure 11. Safe Operating Area (SOA)




Figure 12. Avalanche Current vs Pulse Time (UIS)

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS




Figure 13. I_{DM} vs. Pulse




Figure 14. Transient Thermal Response

ORDERING INFORMATION

Device	Device Marking	Package	Shipping†
NTMFSCHT3D0N08XTWG	7J	DFN8 4.9x5.8 (Pb-Free/Halogen Free)	3,000 / Tape & Reel

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


DUAL COOL is a registered trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.

Share Feedback
Your Opinion Matters

REVISION HISTORY


Revision	Description of Changes	Date
0	Initial Production Document release.	10/20/2026

Share Feedback
Your Opinion Matters




DFN−8 4.90x5.80x0.80, 1.27P
CASE 506EA
ISSUE A


DATE 25 SEP 2026




TOP VIEW



SIDE VIEW




FRONT VIEW



BOTTOM VIEW

NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS
3. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
4. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.




LAND PATTERN
RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.75	0.80	0.85
A1	-	-	0.05
A3		0.25 REF	
b	0.21	0.31	0.41
b1	0.44	0.54	0.64
D	4.90	5.00	5.10
D1		4.90 BSC	
D2	3.72	3.82	3.92
D3	4.30	4.40	4.50
D4		2.75 REF	
D5		0.79 REF	
E	6.05	6.15	6.25
E1		5.80 BSC	
E2	3.67	3.77	3.87
E3		0.60 REF	
E4		3.85 REF	
E5		0.54 REF	
E6		0.60 REF	
E7		0.50 REF	
E8	0.52	0.62	0.72
e		1.27 BSC	
e/2		0.635BSC	
k		1.10 REF	
L	0.56	0.66	0.76
L1	0.15	0.25	0.35
Θ	0°	---	7°




DETAIL B
SCALE: 2:1



DETAIL A
SCALE: 2:1

GENERIC MARKING DIAGRAM*



XX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
Z = Assembly Lot Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON69581H**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**DFN−8 4.90x5.80x0.80, 1.27P**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales