ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET - Power, N-Channel, SUPERFET® III, FAST

650 V, 95 mΩ, 30 A

NTP095N65S3H

Description

SUPERFET III MOSFET is ON Semiconductor's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provides superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III FAST MOSFET series helps minimize various power systems and improve system efficiency.

Features

- $700 \text{ V} @ \text{T}_{\text{J}} = 150^{\circ}\text{C}$
- Typ. $R_{DS(on)} = 77 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. $Q_g = 58 \text{ nC}$)
- Low Effective Output Capacitance (Typ. C_{oss(eff.)} = 522 pF)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant

Applications


- Telecom / Server Power Supplies
- Industrial Power Supplies
- UPS / Solar



ON Semiconductor®


www.onsemi.com

V _{DSS}	R _{DS(ON)} MAX	I _D MAX
650 V	95 mΩ @ 10 V	30 A





MARKING DIAGRAM



T095N65S3H

= Specific Device Code

A YWW = Assembly Plant Code= Date Code (Year & Week)

ZZ

= Lot Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^{\circ}C$, Unless otherwise noted)

Symbol	Parameter		Value	Unit	
V_{DSS}	Drain to Source Voltage		650	V	
V_{GSS}	Gate to Source Voltage	DC	±30	V	
		AC (f > 1 Hz)	±30	V	
I _D	Drain Current	Continuous (T _C = 25°C)	30	Α	
		Continuous (T _C = 100°C)	18		
I _{DM}	Drain Current	Pulsed (Note 1)	84	Α	
E _{AS}	Single Pulsed Avalanche Energy (Note 2)		284	mJ	
I _{AS}	Avalanche Current (Note 2)		5.5	Α	
E _{AR}	Repetitive Avalanche Energy (Note 1)		2.08	mJ	
dv/dt	MOSFET dv/dt		120	V/ns	
	Peak Diode Recovery dv/dt (Note 3)		20		
P_{D}	Power Dissipation	(T _C = 25°C)	208	W	
		Derate Above 25°C	1.67	W/°C	
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to +150	°C	
T_L	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 s		260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected. 1. Repetitive rating: pulse-width limited by maximum junction temperature. 2. $I_{AS} = 5.5 \text{ A}$, $R_{G} = 25 \Omega$, starting $T_{J} = 25^{\circ}\text{C}$. 3. $I_{SD} \le 15 \text{ A}$, $di/dt \le 200 \text{ A/µs}$, $V_{DD} \le 400 \text{ V}$, starting $T_{J} = 25^{\circ}\text{C}$.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{ heta JC}$	Thermal Resistance, Junction to Case, Max.	0.60	°C/W
$R_{ heta JA}$	Thermal Resistance, Junction to Ambient, Max.	62.5	

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Shipping
NTP095N65S3H	T095N65S3H	TO-220-3LD (Pb-Free / Halogen Free)	50 Units / Tube


ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHARACT	ERISTICS				•	•
BV _{DSS}	Drain to Source Breakdown Voltage	$V_{GS} = 0 \text{ V, } I_D = 1 \text{ mA, } T_J = 25^{\circ}\text{C}$	650			V
		V _{GS} = 0 V, I _D = 1 mA, T _J = 150°C	700			V
$\Delta BV_{DSS}/\Delta T_{J}$	Breakdown Voltage Temperature Coefficient	I _D = 10 mA, Referenced to 25°C		0.63		V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 650 V, V _{GS} = 0 V			1	μΑ
		V _{DS} = 520 V, T _C = 125°C		1.8		
I _{GSS}	Gate to Body Leakage Current	V _{GS} = ±30 V, V _{DS} = 0 V			±100	nA
ON CHARACTE	RISTICS		-		•	•
V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_D = 2.8 \text{ mA}$	2.4		4.0	V
R _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 15 A		77	95	mΩ
9FS	Forward Transconductance	V _{DS} = 20 V, I _D = 15 A		30		S
DYNAMIC CHA	RACTERISTICS		•	•		•
C _{iss}	Input Capacitance	V _{DS} = 400 V, V _{GS} = 0 V, f = 250 kHz		2833		pF
C _{oss}	Output Capacitance			43		pF
C _{oss(eff.)}	Effective Output Capacitance	V _{DS} = 0 V to 400 V, V _{GS} = 0 V		522		pF
C _{oss(er.)}	Energy Related Output Capacitance	V _{DS} = 0 V to 400 V, V _{GS} = 0 V		75		pF
Q _{g(tot)}	Total Gate Charge at 10 V			58		nC
Q _{gs}	Gate to Source Gate Charge	V _{DS} = 400 V, I _D = 15 A, V _{GS} = 10 V (Note 4)		14		nC
Q_{gd}	Gate to Drain "Miller" Charge			15		nC
ESR	Equivalent Series Resistance	f = 1 MHz		1.2		Ω
SWITCHING CH	IARACTERISTICS					
t _{d(on)}	Turn-On Delay Time			24		ns
t _r	Turn-On Rise Time	$V_{DD} = 400 \text{ V}, I_D = 15 \text{ A},$		7.4		ns
t _{d(off)}	Turn-Off Delay Time	$V_{DD} = 400 \text{ V}, I_D = 15 \text{ A}, \ V_{GS} = 10 \text{ V}, R_g = 4.7 \Omega \ (\text{Note 4})$		69		ns
t _f	Turn-Off Fall Time			2.4		ns
SOURCE-DRAI	N DIODE CHARACTERISTICS		-		•	
I _S	Maximum Continuous Source to Drain Diode Forward Current				30	Α
I _{SM}	Maximum Pulsed Source to Drain Diode Forward Current				84	Α
V _{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _{SD} = 15 A			1.2	٧
t _{rr}	Reverse Recovery Time	V _{DD} = 400 V, I _{SD} = 15 A,		367		ns
Q _{rr}	Reverse Recovery Charge	dl _F /dt = 100 A/μs		6.3		μС

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)



<u>ŵ</u>

100

0.1

 $T_J = 150^{\circ}C$

0.2

ID, DRAIN CURRENT (A) Figure 3. On-Resistance Variation vs. **Drain Current and Gate Voltage**

60

80

40

0

0

20




Figure 5. Capacitance Characteristics



 $T_J = -55^{\circ}C$

1.0

1.2

8.0

 $T_J = 25^{\circ}C$

0.4




Figure 6. Gate Charge Characteristics

TYPICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)




Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 11. E_{OSS} vs. Drain to Source Voltage

Figure 10. Maximum Drain Current vs. Case Temperature

vs. Temperature

TYPICAL CHARACTERISTICS ($T_C = 25^{\circ}C$ unless otherwise noted)




Figure 12. Transient Thermal Impedance




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms




Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms





Figure 16. Peak Diode Recovery dv/dt Test Circuit & Waveforms

SUPERFET is a registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

PACKAGE DIMENSIONS

TO-220-3LDCASE 340AT



ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability. arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative