

Silicon Carbide (SiC) MOSFET - EliteSiC, 12 mohm, 650 V, M3S, TO247-4L

NVH4L012N065M3S

Features

- Typ. $R_{DS(on)} = 12 \text{ m}\Omega$ @ $V_{GS} = 18 \text{ V}$
- Low Effective Output Capacitance
- Ultra Low Gate Charge
- 100% UIS Tested
- Qualified According to AECQ101
- This Device is Halide Free and RoHS Compliant with Exemption 7a, Pb-Free 2LI (on second level interconnection)

Applications

- Automotive On and Off Board Charger
- Automotive DC-DC Converter for EV-HEV


MAXIMUM RATINGS ($T_J = 25 \text{ }^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	V_{DSS}	650	V
Dynamic Gate-to-Source Voltage	V_{GS}	-10/22.6	V
Continuous Drain Current	I_D	102	A
Power Dissipation	P_D	375	W
Continuous Drain Current	I_D	81	A
Power Dissipation	P_D	187	W
Pulsed Drain Current (Note 1)	I_{DM}	330	A
Continuous Source-Drain Current (Body Diode)	I_S	62	A
		35	
Pulsed Source-Drain Current (Body Diode) (Note 1)	I_{SM}	250	A
Single Pulse Avalanche Energy ($I_{LPK} = 72 \text{ A}$, $L = 0.1 \text{ mH}$) (Note 2)	E_{AS}	259	mJ
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 to +175	$^\circ\text{C}$
Lead Temperature for Soldering Purposes (1/8" from case for 10 seconds)	T_L	270	$^\circ\text{C}$


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Single pulse, limited by max junction temperature.

$V_{(BR)DSS}$	$R_{DS(ON)} \text{ TYP}$	$I_D \text{ MAX}$
650 V	12 m Ω @ 18 V	102 A



N-CHANNEL MOSFET



MARKING DIAGRAM



H4L012065M3S = Specific Device Code

A = Assembly Location

Y = Year

WW = Work Week

ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping
NVH4L012N065M3S	TO-247-4L	30 Units / Tube

NVH4L012N065M3S

2. EAS of 259 mJ is based on starting $T_J = 25^\circ\text{C}$, $L = 0.1 \text{ mH}$, $I_{AS} = 72 \text{ A}$, $V_{DD} = 100 \text{ V}$, $V_{GS} = 18 \text{ V}$.

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Note 3)	$R_{\theta,JC}$	0.40	°C/W

3. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Value	Unit
Operation Values of Gate-to-Source Voltage	V_{GSop}	-3/+18	V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0 \text{ V}$, $I_D = 1 \text{ mA}$, $T_J = 25^\circ\text{C}$	650	—	—	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 650 \text{ V}$, $T_J = 25^\circ\text{C}$	—	—	10	μA
		$V_{DS} = 650 \text{ V}$, $T_J = 175^\circ\text{C}$ (Note 5)	—	—	500	μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{GS} = -10 \text{ V}$, $V_{DS} = 0 \text{ V}$	-1	—	—	μA
		$V_{GS} = +22.6 \text{ V}$, $V_{DS} = 0 \text{ V}$	—	—	1	μA

ON CHARACTERISTICS

Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS} = 18 \text{ V}$, $I_D = 40 \text{ A}$, $T_J = 25^\circ\text{C}$	—	12	17	$\text{m}\Omega$
		$V_{GS} = 18 \text{ V}$, $I_D = 40 \text{ A}$, $T_J = 175^\circ\text{C}$ (Note 5)	—	18	—	
		$V_{GS} = 15 \text{ V}$, $I_D = 40 \text{ A}$, $T_J = 25^\circ\text{C}$	—	15	—	
		$V_{GS} = 15 \text{ V}$, $I_D = 40 \text{ A}$, $T_J = 175^\circ\text{C}$ (Note 5)	—	20	—	
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}$, $I_D = 20 \text{ mA}$, $T_J = 25^\circ\text{C}$	2.0	2.7	4.0	V
Forward Transconductance	g_{FS}	$V_{DS} = 10 \text{ V}$, $I_D = 40 \text{ A}$ (Note 5)	—	45	—	S

CHARGES, CAPACITANCES & GATE RESISTANCE

Input Capacitance	C_{ISS}	$V_{DS} = 400 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 1 \text{ MHz}$ (Note 5)	—	3610	—	pF
Output Capacitance	C_{OSS}		—	281	—	
Reverse Transfer Capacitance	C_{RSS}		—	24	—	
Total Gate Charge	$Q_{G(TOT)}$	$V_{DD} = 400 \text{ V}$, $I_D = 40 \text{ A}$, $V_{GS} = -3/18 \text{ V}$ (Note 5)	—	135	—	nC
Gate-to-Source Charge	Q_{GS}		—	35	—	
Gate-to-Drain Charge	Q_{GD}		—	29	—	
Gate Resistance	R_G		$f = 1 \text{ MHz}$	—	1.6	—

NVH4L012N065M3S

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
-----------	--------	-----------------	-----	-----	-----	------

SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{d(\text{ON})}$	$V_{GS} = -3/18\text{ V}$, $I_D = 40\text{ A}$, $V_{DD} = 400\text{ V}$, $R_G = 4.7\text{ }\Omega$, $T_J = 25^\circ\text{C}$ (Notes 4, 5)	-	5	-	ns
Turn-Off Delay Time	$t_{d(\text{OFF})}$		-	49	-	
Rise Time	t_r		-	23	-	
Fall Time	t_f		-	12	-	
Turn-On Switching Loss	E_{ON}		-	143	-	μJ
Turn-Off Switching Loss	E_{OFF}		-	145	-	
Total Switching Loss	E_{TOT}		-	288	-	

SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{d(\text{ON})}$	$V_{GS} = -3/18\text{ V}$, $I_D = 40\text{ A}$, $V_{DD} = 400\text{ V}$, $R_G = 4.7\text{ }\Omega$, $T_J = 175^\circ\text{C}$ (Notes 4, 5)	-	3.6	-	ns
Turn-Off Delay Time	$t_{d(\text{OFF})}$		-	60	-	
Rise Time	t_r		-	23	-	
Fall Time	t_f		-	13	-	
Turn-On Switching Loss	E_{ON}		-	142	-	μJ
Turn-Off Switching Loss	E_{OFF}		-	172	-	
Total Switching Loss	E_{TOT}		-	314	-	

SOURCE-TO-DRAIN DIODE CHARACTERISTICS

Forward Diode Voltage	V_{SD}	$I_{SD} = 40\text{ A}$, $V_{GS} = -3\text{ V}$, $T_J = 25^\circ\text{C}$	-	4.5	6.0	V
		$I_{SD} = 40\text{ A}$, $V_{GS} = -3\text{ V}$, $T_J = 175^\circ\text{C}$ (Note 5)	-	4.2	-	
Reverse Recovery Time	t_{RR}	$V_{GS} = -3\text{ V}$, $I_S = 40\text{ A}$, $dI/dt = 1000\text{ A}/\mu\text{s}$, $V_{DS} = 400\text{ V}$, $T_J = 25^\circ\text{C}$ (Note 5)	-	26	-	ns
Charge Time	t_a		-	15	-	
Discharge Time	t_b		-	11	-	
Reverse Recovery Charge	Q_{RR}		-	195	-	nC
Reverse Recovery Energy	E_{REC}		-	16	-	μJ
Peak Reverse Recovery Current	I_{RRM}		-	13	-	A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. $E_{\text{ON}}/E_{\text{OFF}}$ result is with body diode.

5. Defined by design, not subject to production test.

NVH4L012N065M3S

TYPICAL CHARACTERISTICS




Figure 1. Output Characteristics




Figure 2. Output Characteristics




Figure 3. Output Characteristics




Figure 4. I_D vs. V_{GS}




Figure 5. $R_{DS(\text{ON})}$ vs. V_{GS}
















Figure 6. I_D vs. $R_{DS(\text{ON})}$

TYPICAL CHARACTERISTICS

Figure 7. I_D vs. $R_{DS(ON)}$

Figure 8. $R_{DS(ON)}$ vs. T_J

Figure 9. Capacitance Characteristics

Figure 10. Stored Energy vs. Drain to Source Voltage

Figure 11. Gate Charge Characteristics

Figure 12. Reverse Conduction Characteristics

TYPICAL CHARACTERISTICS

Figure 13. Reverse Conduction Characteristics

Figure 14. Safe Operating Area

Figure 15. Avalanche Current vs. Pulse Time (UIS)

Figure 16. Maximum Power Dissipation vs. Case Temperature

Figure 17. Inductive Switching Loss vs. Drain Current

Figure 18. Inductive Switching Loss vs. Drain Current

NVH4L012N065M3S

TYPICAL CHARACTERISTICS




Figure 19. Inductive Switching Loss vs. Gate Resistance




Figure 20. Inductive Switching Loss vs. Gate Resistance




Figure 21. Inductive Switching Loss vs. Gate Resistance




Figure 22. Inductive Switching Loss vs. Gate Resistance





Figure 23. Inductive Switching Loss vs. Drain Voltage

TYPICAL CHARACTERISTICS**Figure 24. Thermal Response Characteristics**


REVISION HISTORY

Revision	Description of Changes	Date
0	Initial data sheet release.	11/4/2025

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

PACKAGE DIMENSIONS

TO-247-4LD
CASE 340CJ
ISSUE A



NOTES:

- A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
- B. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- C. ALL DIMENSIONS ARE IN MILLIMETERS.
- D. DRAWING CONFORMS TO ASME Y14.5-2009.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.80	5.00	5.20
A1	2.10	2.40	2.70
A2	1.80	2.00	2.20
b	1.07	1.20	1.33
b1	1.20	1.40	1.60
b2	2.02	2.22	2.42
c	0.50	0.60	0.70
D	22.34	22.54	22.74
D1	16.00	16.25	16.50
D2	0.97	1.17	1.37
e	2.54 BSC		
e1	5.08 BSC		
E	15.40	15.60	15.80
E1	12.80	13.00	13.20
E/2	4.80	5.00	5.20
L	18.22	18.42	18.62
L1	2.42	2.62	2.82
p	3.40	3.60	3.80
p1	6.60	6.80	7.00
Q	5.97	6.17	6.37
S	5.97	6.17	6.37

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales