onsemi

<u>Silicon Carbide (SiC)</u> <u>MOSFET</u> – 20 mohm, 1200 V, M1, TO-247-4L NVH4L020N120SC1

Features

- Typ. $R_{DS(on)} = 20 \text{ m}\Omega$
- Ultra Low Gate Charge ($Q_{G(tot)} = 220 \text{ nC}$)
- High Speed Switching with Low Capacitance ($C_{oss} = 258 \text{ pF}$)
- 100% Avalanche Tested
- AEC-Q101 Qualified and PPAP Capable
- This Device is Halide Free and RoHS Compliant with exemption 7a, Pb–Free 2LI (on second level interconnection)

Typical Applications

- Automotive On Board Charger
- Automotive DC-DC Converter for EV/HEV
- Automotive Traction Inverter


MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Dever	Sumbal	Value	Unit		
Parameter			Symbol	value	Unit
Drain-to-Source Voltage			V _{DSS}	1200	V
Gate-to-Source Voltage			V _{GS}	-15/+25	V
	Recommended Operation Values T _C < 175°C of Gate-to-Source Voltage		V _{GSop}	-5/+20	V
Continuous Drain Current (Note 2)	Steady T _C = 25°C State		Ι _D	101	А
Power Dissipation (Note 2)			PD	500	W
Continuous Drain Current (Notes 1, 2)	Steady State	$T_C = 100^{\circ}C$	Ι _D	71.4	A
Power Dissipation (Notes 1, 2)			PD	250	W
Pulsed Drain Current (Note 3)	$T_A = 25^{\circ}C$		I _{DM}	408	А
Single Pulse Surge Drain Current Capability	$\begin{array}{l} T_{A} = 25^{\circ}C, t_{p} = 10 \; \mu s, \\ R_{G} = 4.7 \; \Omega \end{array}$		I _{DSC}	807	A
Operating Junction and Storage Temperature Range			T _J , T _{stg}	–55 to +175	°C
Source Current (Body Diode)			IS	46	А
Single Pulse Drain-to-Source Avalanche Energy ($I_{L(pk)} = 23 \text{ A}, L = 1 \text{ mH}$) (Note 4)			E _{AS}	264	mJ
Maximum Lead Temperature for Soldering (1/8" from case for 5 s)			ΤL	300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- JA is constant value to follow guide table of LV/HV discrete final datasheet generation.
- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 3. Repetitive rating, limited by max junction temperature.
- 4. EAS of 264 mJ is based on starting T_J = 25°C; L = 1 mH, I_{AS} = 23 A, V_{DD} = 120 V, V_{GS} = 18 V.


V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
1200 V	28 mΩ @ 20 V	102 A



N-CHANNEL MOSFET



MARKING DIAGRAM



A = Assembly Location

- Y = Year
- WW = Work Week
- ZZ = Lot Traceability

NVH4L020N120SC1 = Specific Device Code

ORDERING INFORMATION

Device	Package	Shipping
NVH4L020N120SC1	TO-247-4L	30 Units / Tube

Table 1. THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Мах	Unit
Junction-to-Case - Steady State (Note 2)		0.3	°C/W
Junction-to-Ambient - Steady State (Notes 1, 2)	$R_{\theta JA}$	40	

Table 2. ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS					•		
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 1 mA		1200	-	-	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J	$I_D = 1 \text{ mA}$, referenced to 25°C		-	0.5	-	V/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V,$	$T_J = 25^{\circ}C$	-	-	100	μA
		V _{DS} = 1200 V	T _J = 175°C	-	-	1	mA
Gate-to-Source Leakage Current	I _{GSS}	$V_{GS} = +25/-15 \text{ V}, \text{ V}_{D}$	s = 0 V	-	-	±1	μA
ON CHARACTERISTICS (Note 3)							-
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 20 \text{ m}$	A	1.8	2.7	4.3	V
Recommended Gate Voltage	V _{GOP}			-5	-	+20	V
Drain-to-Source On Resistance	R _{DS(on)}	$V_{GS} = 20 \text{ V}, \text{ I}_{D} = 60 \text{ A}$, T _J = 25°C	-	20	28	mΩ
		$V_{GS} = 20 \text{ V}, \text{ I}_{D} = 60 \text{ A}$, T _J = 175°C	-	37	50	
Forward Transconductance	9fs	$V_{DS} = 20 \text{ V}, \text{ I}_{D} = 60 \text{ A}$		-	36	-	S
CHARGES, CAPACITANCES & GATE RES	SISTANCE	•					
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 800 V		-	2943	-	pF
Output Capacitance	C _{OSS}			-	258	-	
Reverse Transfer Capacitance	C _{RSS}			-	24	-	
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = -5/20 \text{ V}, V_{DS} = 600 \text{ V},$ $I_D = 80 \text{ A}$		-	220	-	nC
Threshold Gate Charge	Q _{G(TH)}			-	33	-	
Gate-to-Source Charge	Q _{GS}			-	66	-	
Gate-to-Drain Charge	Q _{GD}			-	63	-	
Gate-Resistance	R _G	f = 1 MHz		-	1.6	-	Ω
SWITCHING CHARACTERISTICS, VGS =	10 V				•		
Turn-On Delay Time	t _{d(ON)}	$V_{GS} = -5/20 \text{ V}, \text{ V}_{DS} =$	800 V,	-	21.6	35	ns
Rise Time	t _r	$I_D = 80 \text{ A}, R_G = 2 \Omega$ Inductive load		-	21	34	
Turn-Off Delay Time	t _{d(OFF)}			-	41	66	
Fall Time	t _f			-	10	20	
Turn-On Switching Loss	E _{ON}	1		-	494	-	μJ
Turn–Off Switching Loss	E _{OFF}			-	397	-	
Total Switching Loss	E _{tot}			-	891	-	
DRAIN-SOURCE DIODE CHARACTERIST	TICS	-		-	-		-
Continuous Drain-Source Diode Forward Current	I _{SD}	V_{GS} = -5 V, T _J = 25°C		-	-	46	A
Pulsed Drain-Source Diode Forward Current (Note 3)	I _{SDM}			-	-	408	
Forward Diode Voltage	V _{SD}	V _{GS} = –5 V, I _{SD} = 30 A, T _J = 25°C		_	3.7	_	V

Table 2. ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified) (continued)


Parameter	Symbol	Test Condition	Min	Тур	Max	Unit		
DRAIN-SOURCE DIODE CHARACTERISTICS								
Reverse Recovery Time	t _{RR}	V _{GS} = -5/20 V, I _{SD} = 80 A, dI _S /dt = 1000 A/μs	-	30	-	ns		
Reverse Recovery Charge	Q _{RR}	αι _S /αt = 1000 Α/μs	-	225	-	nC		
Reverse Recovery Energy	E _{REC}		-	16	-	Lμ		
Peak Reverse Recovery Current	I _{RRM}		-	15	-	Α		
Charge Time	Та		-	16	-	ns		
Discharge Time	Tb		-	15	-	ns		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS (continued)



TYPICAL CHARACTERISTICS (continued)





Figure 13. Junction-to-Ambient Thermal Response



TO-247-4LD CASE 340CJ ISSUE A

DATE 16 SEP 2019



	MILLIMETERS				
DIM	MIN	NOM	MAX		
А	4.80	5.00	5.20		
A1	2.10	2.40	2.70		
A2	1.80	2.00	2.20		
b	1.07	1.20	1.33		
b1	1.20	1.40	1.60		
b2	2.02	2.22	2.42		
С	0.50	0.60	0.70		
D	22.34	22.54	22.74		
D1	16.00	16.25	16.50		
D2	0.97	1.17	1.37		
е	2.54 BSC				
e1	Ę	5.08 BSC	2		
Е	15.40	15.60	15.80		
E1	12.80	13.00	13.20		
E/2	4.80	5.00	5.20		
L	18.22	18.42	18.62		
L1	2.42	2.62	2.82		
р	3.40	3.60	3.80		
p1	6.60	6.80	7.00		
Q	5.97	6.17	6.37		
S	5.97	6.17	6.37		

DOCUMENT NUMBER:	98AON13852G	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	TO-247-4LD		PAGE 1 OF 1		
ON Semiconductor and 🕕 are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries.					

ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>