

# **MOSFET** - Power, N-Channel, SUPERFET<sup>®</sup> III, FRFET<sup>®</sup>

# 650 V, 40 mΩ, 65 A NVHL040N65S3HF

#### Description

SUPERFET III MOSFET is **onsemi**'s brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET is very suitable for the various power system for miniaturization and higher efficiency.

SUPERFET III HF version provides fast recovery for improved efficiency in high speed switching applications.


#### **Features**


- 700 V @  $T_I = 150^{\circ}\text{C}$
- Typ.  $R_{DS(on)} = 31 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. Q<sub>g</sub> = 157 nC)
- Low Effective Output Capacitance (Typ. Coss(eff.) = 1374 pF)
- 100% Avalanche Tested
- NVHL Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Applications**

- Automotive On Board Charger HEV-EV
- Automotive DC/DC Converter for HEV-EV


V <sub>DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX
650 V	40 mΩ @ 10 V	65 A





TO-247 Long Leads CASE 340CX

#### **MARKING DIAGRAM**



A = Assembly Plant Code
YWW = Data Code (Year & Week)
ZZ = Assembly Lot Code
NVHL040N65S3HF = Specific Device Code

#### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 2 of this data sheet.

# **ABSOLUTE MAXIMUM RATINGS** ( $T_C = 25^{\circ}C$ , Unless otherwise noted)

Symbol	Parameter		Value	Unit	
$V_{DSS}$	Drain-to-Source Voltage	urce Voltage		V	
$V_{GSS}$	Gate-to-Source Voltage - DC		±30	V	
		- AC (f > 1 Hz)	±30		
I <sub>D</sub>	Drain Current	- Continuous (T <sub>C</sub> = 25°C)		Α	
		- Continuous (T <sub>C</sub> = 100°C)	45		
I <sub>DM</sub>	Drain Current	- Pulsed (Note 1)	162.5	Α	
E <sub>AS</sub>	Single Pulsed Avalanche Energy (Note 2)	1009	mJ		
I <sub>AS</sub>	Avalanche Current (Note 2)		9	Α	
E <sub>AR</sub>	Repetitive Avalanche Energy (Note 1)		4.46	mJ	
dv/dt	MOSFET dv/dt		100	V/ns	
	Peak Diode Recovery dv/dt (Note 3)	50			
$P_{D}$	Power Dissipation	(T <sub>C</sub> = 25°C)	446	W	
		- Derate Above 25°C	3.57	W/°C	
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Temperature Range		-55 to +150	°C	
TL	Maximum Lead Temperature for Soldering, 1/8"	300	°C		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected. 
1. Repetitive rating: pulse–width limited by maximum junction temperature. 
2.  $I_{AS} = 9 \text{ A}$ ,  $R_G = 25 \Omega$ , starting  $T_J = 25^{\circ}\text{C}$ . 
3.  $I_{SD} \le 32.5 \text{ A}$ ,  $di/dt \le 200 \text{ A}/\mu\text{s}$ ,  $V_{DD} \le 400 \text{ V}$ , starting  $T_J = 25^{\circ}\text{C}$ .

#### THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{ hetaJC}$	Thermal Resistance, Junction-to-Case, Max.	0.28	°C/W
$R_{ heta JA}$	Thermal Resistance, Junction-to-Ambient, Max.	40	

### PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
NVHL040N65S3HF	NVHL040N65S3HF	TO-247	Tube	N/A	N/A	30 Units

#### **ELECTRICAL CHARACTERISTICS** (T<sub>C</sub> = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHARACT	reristics			•	•	
BV <sub>DSS</sub>	Drain-to-Source Breakdown Voltage	$V_{GS} = 0 \text{ V, I}_{D} = 1 \text{ mA, T}_{J} = 25^{\circ}\text{C}$	650	_	-	V
		V <sub>GS</sub> = 0 V, I <sub>D</sub> = 1 mA, T <sub>J</sub> = 150°C	700	-	-	V
ΔBV <sub>DSS</sub> /ΔT <sub>J</sub> Breakdown Voltage Temperature Coefficient		I <sub>D</sub> = 15 mA, Referenced to 25°C	-	0.63	-	V/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 650 V, V <sub>GS</sub> = 0 V	1	-	10	μΑ
		V <sub>DS</sub> = 520 V, T <sub>C</sub> = 125°C	1	28	-	
I <sub>GSS</sub>	Gate-to-Body Leakage Current	V <sub>GS</sub> = ±30 V, V <sub>DS</sub> = 0 V	_	-	±100	nA
ON CHARACT	ERISTICS					
V <sub>GS(th)</sub>	Gate Threshold Voltage	$V_{GS} = V_{DS}$ , $I_D = 2.1$ mA	3.0	_	5.0	V
R <sub>DS(on)</sub>	Static Drain-to-Source On Resistance	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 32.5 A	-	31	40	mΩ
9FS	Forward Transconductance	V <sub>DS</sub> = 20 V, I <sub>D</sub> = 32.5 A	1	45	-	S
DYNAMIC CHA	RACTERISTICS					
C <sub>iss</sub>	Input Capacitance	$V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$	-	6655	-	pF
C <sub>oss</sub>	Output Capacitance		1	143	-	pF
C <sub>oss(eff.)</sub>	Effective Output Capacitance	V <sub>DS</sub> = 0 V to 400 V, V <sub>GS</sub> = 0 V	-	1374	-	pF
C <sub>oss(er.)</sub>	Energy Related Output Capacitance	V <sub>DS</sub> = 0 V to 400 V, V <sub>GS</sub> = 0 V	-	250	-	pF
Q <sub>g(tot)</sub>	Total Gate Charge at 10 V	V <sub>DS</sub> = 400 V, I <sub>D</sub> = 32.5 A, V <sub>GS</sub> = 10 V	-	157	-	nC
Q <sub>gs</sub>	Gate-to-Source Gate Charge	(Note 4)	-	49	-	nC
$Q_{gd}$	Gate-to-Drain "Miller" Charge		-	61	-	nC
ESR	Equivalent Series Resistance	f = 1 MHz		1.1	-	Ω
SWITCHING C	HARACTERISTICS					
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> = 400 V, I <sub>D</sub> = 32.5 A,	-	42.2	-	ns
t <sub>r</sub>	Turn-On Rise Time	$V_{GS}$ = 10 V, $R_g$ = 2.2 $\Omega$ (Note 4)	_	27.4	-	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		-	103	-	ns
t <sub>f</sub>	Turn-Off Fall Time		ı	3.4	-	ns
SOURCE-DRA	IN DIODE CHARACTERISTICS					
Is	Maximum Continuous Source-to-Drain Diode Forward Current		-	_	65	Α
I <sub>SM</sub>	Maximum Pulsed Source-to-Drain Dio	de Forward Current	-	_	162.5	Α
$V_{SD}$	Source-to-Drain Diode Forward Voltage	V <sub>GS</sub> = 0 V, I <sub>SD</sub> = 32.5 A	-	-	1.3	٧
t <sub>rr</sub>	Reverse Recovery Time	V <sub>DD</sub> = 400 V, I <sub>SD</sub> = 32.5 A,	-	137	-	ns
Q <sub>rr</sub>	Reverse Recovery Charge	dI <sub>F</sub> /dt = 100 A/μs	-	792	-	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

#### **TYPICAL CHARACTERISTICS**




Figure 1. On-Region Characteristics




Figure 2. On-Region Characteristics




Figure 3. Transfer Characteristics




Figure 4. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 5. Body Diode Forward Voltage Variation vs. Source Current and Temperature





Figure 6. Capacitance Characteristics

#### **TYPICAL CHARACTERISTICS**



www.onsemi.com

**Temperature** 

#### **TYPICAL CHARACTERISTICS**





Figure 13. R<sub>DS(ON)</sub> vs. Gate Voltage

 $V_{GS} = V_{DS}$  $I_D = 2.1 \text{ mA}$ 80 40 120 160 T<sub>J</sub>, JUNCTION TEMPERATURE (°C)

Figure 14. Normalized Gate Threshold Voltage vs. Temperature


 $t_{AV} = (L/R) ln[(l_{AS}*R)/(1.3*RATED BV_{DSS} - V_{DD}) + 1]$ 

 $t_{AV} = (L)(I_{AS})/(1.3*RATED BV_{DSS} - V_{DD})$ 



Capability

Figure 15. Unclamped Inductive Switching



If R = 0




Figure 16. Transient Thermal Response Curve




Figure 17. Gate Charge Test Circuit & Waveform




Figure 18. Resistive Switching Test Circuit & Waveforms




Figure 19. Unclamped Inductive Switching Test Circuit & Waveforms





Figure 20. Peak Diode Recovery dv/dt Test Circuit & Waveforms

SUPERFET and FRFET are a registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.


#### **PACKAGE DIMENSIONS**

TO-247-3LD CASE 340CX **ISSUE A** 



NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 2009.
  D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.



DIM	MILLIMETERS					
DIM	MIN NOM MA		MAX			
Α	4.58	4.70	4.82			
<b>A</b> 1	2.20	2.40	2.60			
A2	1.40	1.50	1.60			
D	20.32	20.57	20.82			
Е	15.37	15.62	15.87			
E2	4.96	5.08	5.20			
е	~	5.56	~			
L	19.75	20.00	20.25			
L1	3.69	3.81	3.93			
ØΡ	3.51	3.58	3.65			
Q	5.34	5.46	5.58			
S	5.34	5.46	5.58			
b	1.17	1.26	1.35			
b2	1.53	1.65	1.77			
b4	2.42	2.54	2.66			
С	0.51	0.61	0.71			
D1	13.08	~	~			
D2	0.51	0.93	1.35			
E1	12.81	~	~			
ØP1	6.60	6.80	7.00			

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative