

# Silicon Carbide (SiC) MOSFET - EliteSiC, 960 mohm, 1700 V, M1, TO-247-3L

# NVHL1000N170M1

#### **Features**

- Typ.  $R_{DS(on)} = 960 \text{ m}\Omega$  @ VGS = 20 V
- Ultra Low Gate Charge  $(Q_{G(tot)} = 14 \text{ nC})$
- High Speed Switching with Low Capacitance (Coss = 11 pF)
- 100% Avalanche Tested
- AEC-Q101 Qualified and PPAP Capable
- This Device is Halide Free and RoHS Compliant with exemption 7a, Pb–Free 2LI (on second level interconnection)

#### **Typical Applications**

• Flyback Converter


#### MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V <sub>DSS</sub>	1700	V
Gate-to-Source Voltage			$V_{GS}$	-15/+25	٧
Recommended Operation Values of Gate-to-Source Voltage		$V_{GSop}$	-5/+20	<b>V</b>	
Continuous Drain Current (Note 1)	Steady State	T <sub>C</sub> = 25°C	I <sub>D</sub>	4.2	Α
Power Dissipation (Note 1)			P <sub>D</sub>	48	W
Continuous Drain Current (Note 1)	Steady State	T <sub>C</sub> = 100°C	I <sub>D</sub>	3	Α
Power Dissipation (Note 1)			P <sub>D</sub>	24	W
Pulsed Drain Current (Note 2)	T <sub>C</sub> = 25°C		I <sub>DM</sub>	14	Α
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stg</sub>	-55 to +175	°C	
Source Current (Body Diode)		IS	9.5	Α	
Single Pulse Drain-to-Source Avalanche Energy (Note 3)		E <sub>AS</sub>	24	mJ	
Maximum Lead Temperature for Soldering (1/25" from case for 10 s)		TL	270	°C	


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Repetitive rating, limited by max junction temperature.
- 3. E<sub>AS</sub> of 24 mJ is based on starting  $T_J$  = 25°C; L = 1 mH, I<sub>AS</sub> = 6.9 A,  $V_{DD}$  = 120 V,  $V_{GS}$  = 20 V.

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> TYP	I <sub>D</sub> MAX	
1700 V	960 mΩ @ 20 V	4.2 A	




**N-CHANNEL MOSFET** 



TO-247-3LD CASE 340CX

#### MARKING DIAGRAM



A = Assembly Location

Y = Year WW = Work Week ZZ = Lot Traceability

HL1000N170M1 = Specific Device Code

#### ORDERING INFORMATION

Device	Package	Shipping
NVHL1000N170M1	TO-247-3L	30 Units / Tube

#### THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Max	Unit
Junction-to-Case - Steady State (Note 1)	$R_{ heta JC}$	3.1	°C/W

Deventer	Coursels al	Tank On :: -!!!	lan	N/I:	Т	Mari	11
Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS	•	1		1	1		1
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = 1 \text{ mA}$		1700			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /T <sub>J</sub>	I <sub>D</sub> = 1 mA, referenced to 25°C (Note 4)			0.5		V/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 \text{ V},$ $V_{DS} = 1700 \text{ V}$	T <sub>J</sub> = 25°C			100	μΑ
		V <sub>DS</sub> = 1700 V	T <sub>J</sub> = 175°C			1	mA
Gate-to-Source Leakage Current	I <sub>GSS</sub>	$V_{GS} = +25/-15 V$ ,	$V_{DS} = 0 V$			±1	μΑ
ON CHARACTERISTICS (Note 2)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D =$	640 μΑ	1.8	3.2	4.3	V
Recommended Gate Voltage	$V_{GOP}$			-5		+20	V
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	$V_{GS} = 20 \text{ V}, I_D = 2 \text{ A}$	A, T <sub>J</sub> = 25°C		960	1430	mΩ
		V <sub>GS</sub> = 20 V, I <sub>D</sub> = 2 A, (Note 4)			1800		
Forward Transconductance	9FS	V <sub>DS</sub> = 10 V, I <sub>D</sub> = 2	A (Note 4)		0.6		S
CHARGES, CAPACITANCES & GATE RES	SISTANCE (Note	4)				•	•
Input Capacitance	C <sub>ISS</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz,	V <sub>DS</sub> = 1000 V		150		pF
Output Capacitance	C <sub>OSS</sub>				11		1
Reverse Transfer Capacitance	C <sub>RSS</sub>				0.6		
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS} = -5/20 \text{ V}, V_{DS} = 800 \text{ V},$ $I_{D} = 2 \text{ A}$			14		nC
Threshold Gate Charge	Q <sub>G(TH)</sub>				1.5		
Gate-to-Source Charge	Q <sub>GS</sub>	1			2.6		
Gate-to-Drain Charge	$Q_{GD}$	1			7.5		
Gate-Resistance	$R_{G}$	f = 1 MHz			5.7		Ω
SWITCHING CHARACTERISTICS (Notes 4	l, 5)						
Turn-On Delay Time	t <sub>d(ON)</sub>	V <sub>GS</sub> = -5/20			5.6		ns
Rise Time	t <sub>r</sub>	$V_{DS} = 800$ $I_{D} = 2 A$	V,		30		
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$R_{G} = 25  \Omega$	Ω		11		
Fall Time	t <sub>f</sub>	inductive load $L = 300 \mu H$			84		
Turn-On Switching Loss	E <sub>ON</sub>	1			120		μJ
Turn-Off Switching Loss	E <sub>OFF</sub>				11		·
Total Switching Loss	E <sub>tot</sub>				131		
DRAIN-SOURCE DIODE CHARACTERIST							
Continuous Drain-Source Diode Forward Current (Note 1)	I <sub>SD</sub>	V <sub>GS</sub> = -5 V, T <sub>J</sub>	= 25°C			9.5	А
Pulsed Drain-Source Diode Forward Current (Note 2)	I <sub>SDM</sub>					48	
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = -5 V, I <sub>SD</sub> = 2 /	A, T <sub>J</sub> = 25°C		4.2		V
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = -5/20 V, I <sub>S</sub>	<sub>SD</sub> = 2 A,		5.9		ns
Reverse Recovery Charge	Q <sub>RR</sub>	$dI_S/dt = 1000 \text{ A/µs (Note 4)}$			11		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Defined by design, not subject to production test.

5. E<sub>ON</sub>/E<sub>OFF</sub> result is with body diode.

#### **TYPICAL CHARACTERISTICS**




Figure 1. On-Region Characteristics




Figure 2. On-Region Characteristics




Figure 3. On-Region Characteristics




Figure 4. Normalized On–Resistance vs. Drain Current and Gate Voltage




Figure 5. Normalized On-Resistance Variation with Temperature




Figure 6. On-Resistance vs. Gate-to-Source Voltage

#### **TYPICAL CHARACTERISTICS**




Figure 7. Transfer Characteristics




Figure 8. Switching Loss vs. Drain Current




Figure 9. Switching Loss vs. Drain Current




Figure 10. Switching Loss vs. Gate Resistance




Figure 11. Reverse Drain Current vs. Body Diode Forward Voltage




Figure 12. Gate-to-Source Voltage vs. Total Charge

#### **TYPICAL CHARACTERISTICS**




Figure 13. Capacitance vs. Drain-to-Source Voltage




Figure 14. Unclamped Inductive Switching Capability




Figure 15. Maximum Continuous Drain Current vs. Case Temperature




Figure 16. Maximum Rated Forward Biased Safe Operating Area




Figure 17. Single Pulse Maximum Power Dissipation






Figure 18. Transient Thermal Impedance

### **ESD RATINGS**

ESD Test	ESD Test Classification	
ESD-HBM	0B (125 V to <250 V)	ANSI/ESDA/JEDEC JS-001
ESD-CDM	C3 (>1000 V)	ANSI/ESDA/JEDEC JS-002



**DATE 06 JUL 2020** 




#### NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.

  B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 2009.
- D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

# **GENERIC MARKING DIAGRAM\***



XXXXX = Specific Device Code = Assembly Location

= Year WW = Work Week G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " =", may or may not be present. Some products may not follow the Generic Marking.

DIM	MILLIMETERS				
DIM	MIN	NOM	MAX		
Α	4.58	4.70	4.82		
<b>A</b> 1	2.20	2.40	2.60		
A2	1.40	1.50	1.60		
D	20.32	20.57	20.82		
Е	15.37	15.62	15.87		
E2	4.96	5.08	5.20		
е	~	5.56	~		
L	19.75	20.00	20.25		
L1	3.69	3.81	3.93		
ØΡ	3.51	3.58	3.65		
Q	5.34	5.46	5.58		
S	5.34	5.46	5.58		
b	1.17	1.26	1.35		
b2	1.53	1.65	1.77		
b4	2.42	2.54	2.66		
С	0.51	0.61	0.71		
D1	13.08	~	~		
D2	0.51	0.93	1.35		
E1	12.81	~	~		
Ø <b>P</b> 1	6.60	6.80	7.00		

DOCUMENT NUMBER:	98AON93302G	Electronic versions are uncontrolled except when accessed directly from the Document Reposi Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TO-247-3LD		PAGE 1 OF 1	

ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales