

MOSFET - Power, Single N-Channel, TOLL 100 V, 1.8 mΩ, 265 A

NVBLS1D7N10MC

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- Lowers Switching Noise/EMI
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V_{DSS}	100	V
Gate-to-Source Voltage	Э		V_{GS}	±20	V
Continuous Drain		T _C = 25°C	I _D	265	Α
Current R _{θJC} (Notes 1, 3)	Steady	T _C = 100°C		187	
Power Dissipation	State	T _C = 25°C	P_{D}	303	W
R _{θJC} (Note 1)		T _C = 100°C		152	
Continuous Drain		T _A = 25°C		32.4	Α
Current R _{θJA} (Notes 1, 2, 3)	Steady	T _A = 100°C		22.9	
Power Dissipation	State	T _A = 25°C	P_{D}	4.5	W
R _{θJA} (Notes 1, 2)		T _A = 100°C		2.3	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \mu s$		I _{DM}	900	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			I _S	233	Α
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 23.7 A)			E _{AS}	2716	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	0.49	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	33	

- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

1

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
100 V	1.8 mΩ @ 10 V	265 A



N-CHANNEL MOSFET



H-PSOF8L CASE 100CU

MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
ZZ = Lot Traceability
1D7N10MC = Specific Device Code

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS				•	•	•	•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA		100			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /				60		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V$	T _J = 25 °C			10	
		V _{DS} = 100 V	T _J = 125°C			100	μΑ
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS}$	s = 20 V			100	nA
ON CHARACTERISTICS (Note 4)					-		
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D =$	= 698 μA	2.0		4.0	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-10.5		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 80 A		1.5	1.8	mΩ
Forward Transconductance	9FS	V _{DS} = 10 V, I _D	= 80 A		220		S
CHARGES AND CAPACITANCES				•	•	•	•
Input Capacitance	C _{ISS}				9200		
Output Capacitance	C _{OSS}	V _{GS} = 0 V, f = 1 MHz	z, V _{DS} = 50 V		4600		pF
Reverse Transfer Capacitance	C _{RSS}				79		
Total Gate Charge	Q _{G(TOT)}				115		
Threshold Gate Charge	Q _{G(TH)}				24		
Gate-to-Source Charge	Q_GS	V _{GS} = 10 V, V _{DS} = 50 V; I _D = 80 A			47		nC
Gate-to-Drain Charge	Q_GD				16		
Plateau Voltage	V_{GP}				5		V
SWITCHING CHARACTERISTICS (Note	5)			•	•	•	•
Turn-On Delay Time	t _{d(ON)}				48		
Rise Time	t _r	Vcs = 10 V. Vns	s = 50 V.		38		1
Turn-Off Delay Time	t _{d(OFF)}	$I_D = 80 \text{ A}, R_G$	V_{GS} = 10 V, V_{DS} = 50 V, I_D = 80 A, R_G = 6 Ω		76		ns
Fall Time	t _f				31		1
DRAIN-SOURCE DIODE CHARACTERIS	STICS			1		1	•
Forward Diode Voltage	V_{SD}	V _{GS} = 0 V,	T _J = 25°C		0.82	1.3	
		$V_{GS} = 0 V,$ $I_{S} = 80 A$ $T_{J} = 125^{\circ}0$			0.70		V
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 \text{ V, dIS/dt} = 100 \text{ A/}\mu\text{s,}$ $I_{S} = 62 \text{ A}$			98		ns
Reverse Recovery Charge	Q _{RR}				160		nC
Charge Time	ta				47		ns
Discharge Time	t _b				52		ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width $\leq 300~\mu s$, duty cycle $\leq 2\%$.


5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



500 $V_{DS} = 10 V$ 450 400 ID, DRAIN CURRENT (A) 350 300 250 200 $T_J = 25^{\circ}C$ 150 100 50 $T_J = -55^{\circ}C$ $T_J = 150^{\circ}C$ 0 2 0 3 5 6 V_{GS}, GATE-TO-SOURCE VOLTAGE (V)

Figure 2. Transfer Characteristics







Figure 3. On-Resistance vs. Gate-to-Source Voltage

Figure 4. On-Resistance vs. Drain Current and Gate Voltage






Figure 5. On–Resistance Variation with Temperature

Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Maximum Rated Forward Biased Safe Operating Area




Figure 12. Maximum Drain Current vs. Time in Avalanche

TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Impedance

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NVBLS1D7N10MCTXG	1D7N10MC	H-PSOF8L (Pb-Free)	2000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



-D7-**BOTTOM VIEW**

DIM MILLIMETERS			RS
Divi	MIN.	NOM.	MAX.
Α	2.20	2.30	2.40
А3	0.40	0.50	0.60
b	0.70	0.80	0.90
b1	8.00 REF		
С	0.40	0.50	0.60
c1	0.10		
D	9.70	9.80	9.90
D1	9.80	9.90	10.00
D2	4.73 BSC		
D3	0.40 REF		
D4	;	3.75 BSC	;
D5	_	1.20	
D6	7.40	7.50	7.60
D7	(8.30)		
Е	11.58	11.68	11.78
E1	10.28	10.38	10.48
E2	0.60	0.70	0.80
E3	3.30 REF		
E4		2.60	

DIM	MILLIMETERS			
DIM	MIN. NOM. MAX			
е	1.20 BSC			
e/2	(0.60 BSC	;	
e1	,	3.40 BSC	;	
K	1.50 1.57 1.70			
L	1.90	2.00	2.10	
L2	0.50	0.60	0.70	
Z		0.35 REF	:	
θ	0°		12°	
aaa	0.20			
bbb	0.25			
CCC	0.20			
ddd	0.20			
eee	0.10			
E5		3.30	_	
E6		0.65	_	
E7	7.15 REF			
E8	6.55	6.65	6.75	
E9	5.89 BSC			
E10	5.19 BSC			

2.95

2.90

0.60-2.80

1.20

13 28

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative