

MOSFET - SiC Power, Single N-Channel, TO247-3L 650 V, 19 mΩ, 99 A

NVHL025N065SC1

Features

- Typ. $R_{DS(on)} = 19 \text{ m}\Omega$ @ $V_{GS} = 18 \text{ V}$ Typ. $R_{DS(on)} = 25 \text{ m}\Omega$ @ $V_{GS} = 15 \text{ V}$
- Ultra Low Gate Charge (Q_{G(tot)} = 164 nC)
- Low Capacitance (C_{oss} = 278 pF)
- 100% Avalanche Tested
- AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free and is RoHS Compliant

Typical Applications

- Automotive On Board Charger
- Automotive DC/DC Converter for EV/HEV

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V_{DSS}	650	V
Gate-to-Source Voltage			V_{GS}	-8/+22	V
Recommended Operation Values of Gate-to-Source Voltage		T _C < 175°C	V_{GSop}	-5/+18	V
Continuous Drain Current (Note 1)	Steady State T _C = 25°C		I _D	99	Α
Power Dissipation (Note 1)			P _D	348	W
Continuous Drain Current (Note 1)	Steady State	T _C = 100°C	I _D	70	Α
Power Dissipation (Note 1)			P _D	174	W
Pulsed Drain Current (Note 2)	T _C = 25°C		I _{DM}	323	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			I _S	75	Α
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 11.2 A, L = 1 mH) (Note 3)			E _{AS}	62	mJ
Maximum Lead Temperature for Soldering (1/8" from case for 5 s)			TL	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

 The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.


1

- 2. Repetitive rating, limited by max junction temperature.
- 3. EAS of 62 mJ is based on starting $T_J = 25^{\circ}C$; L = 1 mH, $I_{AS} = 11.2$ A, $V_{DD} = 50$ V, $V_{GS} = 18$ V.


V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX	
650 V	28.5 mΩ @ 18 V	99 A	



N-CHANNEL MOSFET



MARKING DIAGRAM



H4L025065SC1 = Specific Device Code

A = Assembly Location

Y = Year WW = Work Week ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping
NVHL025N065SC1	TO247-3L	30 Units / Tube

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Max	Unit
Junction-to-Case - Steady State (Note 1)	$R_{ heta JC}$	0.43	°C/W
Junction-to-Ambient - Steady State (Note 1)	$R_{\theta JA}$	40	

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 1 mA		650	_	-	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J	I _D = 20 mA, referenced to 25°C		-	0.15	-	V/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 \text{ V}, \qquad T_{J} = 25^{\circ}\text{C}$		-	-	10	μΑ
		V _{DS} = 650 V	T _J = 175°C	-	-	1	mA
Gate-to-Source Leakage Current	I _{GSS}	$V_{GS} = +18/-5 \text{ V}, \text{ V}$	V _{DS} = 0 V	_	_	250	nA
ON CHARACTERISTICS (Note 2)					•		
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D =$	15.5 mA	1.8	2.8	4.3	V
Recommended Gate Voltage	V_{GOP}			-5	_	+18	V
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 15 V, I _D = 45 A, T _J = 25°C		-	25	-	mΩ
		V _{GS} = 18 V, I _D = 45 A	A, T _J = 25°C	-	19	28.5	
		V _{GS} = 18 V, I _D = 45 A, T _J = 175°C		-	24	-	
Forward Transconductance	9FS	V _{DS} = 10 V, I _D	= 45 A	_	27	_	S
CHARGES, CAPACITANCES & GATE RES	SISTANCE				•		
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 325 V		-	3480	_	pF
Output Capacitance	C _{OSS}			_	278	_	
Reverse Transfer Capacitance	C _{RSS}			_	25	_	
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = -5/18 \text{ V}, V_{DS} = 520 \text{ V},$ $I_{D} = 45 \text{ A}$		-	164	_	nC
Gate-to-Source Charge	Q _{GS}			_	48	_	
Gate-to-Drain Charge	Q_{GD}			-	48	_	
Gate-Resistance	R _G	f = 1 MHz		_	1.5	_	Ω
SWITCHING CHARACTERISTICS	•					•	
Turn-On Delay Time	t _{d(ON)}	$V_{GS} = -5/18 \text{ V},$ $V_{DS} = 400 \text{ V},$ $I_{D} = 45 \text{ A},$ $R_{G} = 2.2 \Omega$ inductive load		-	18	_	ns
Rise Time	t _r			-	51	_	
Turn-Off Delay Time	t _{d(OFF)}			-	34	_	
Fall Time	t _f	madon o lo	, au	-	9	_	
Turn-On Switching Loss	E _{ON}			-	560	_	μJ
Turn-Off Switching Loss	E _{OFF}			-	112	_	
Total Switching Loss	E _{tot}			-	672	_	
DRAIN-SOURCE DIODE CHARACTERIST	ics				-		
Continuous Drain-Source Diode Forward Current	I _{SD}	$V_{GS} = -5 \text{ V}, T_J$	= 25°C	-	-	75	Α
Pulsed Drain-Source Diode Forward Current (Note 2)	I _{SDM}			-	-	323	
Forward Diode Voltage	V_{SD}	V _{GS} = -5 V, I _{SD} = 45 A, T _J = 25°C		-	4.7	-	V

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise specified) (continued)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit		
DRAIN-SOURCE DIODE CHARACTERISTICS								
Reverse Recovery Time	t _{RR}	$V_{GS} = -5/18 \text{ V, } I_{SD} = 45 \text{ A,}$ $dI_{S}/dt = 1000 \text{ A/}\mu\text{s}$	-	25	-	ns		
Reverse Recovery Charge	Q _{RR}		-	165	-	nC		
Reverse Recovery Energy	E _{REC}		_	18.8	_	μJ		
Peak Reverse Recovery Current	I _{RRM}		-	13	-	Α		
Charge time	Ta		-	15	-	ns		
Discharge time	Tb]	-	10.3	_	ns		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 3. On–Resistance Variation with Temperature




Figure 5. Transfer Characteristics






Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 6. Diode Forward Voltage vs. Current

TYPICAL CHARACTERISTICS




Figure 7. Gate-to-Source Voltage vs. Total Charge




Figure 8. Capacitance vs. Drain-to-Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 11. Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS






Figure 13. Junction-to-Case Thermal Response

PACKAGE DIMENSIONS



DATE 06 JUL 2020



DIM MAXMIN MOM Α 4.58 4.70 4.82 **A1** 2.20 2.40 2.60 A2 1.40 1.50 1.60 20.32 20.82 D 20.57 Ε 15.37 15.62 15.87 E2 4.96 5.08 5.20 5.56 е 19.75 20.00 20.25 L L1 3.69 3.81 3.93 ØΡ 3.51 3.58 3.65 Q 5.34 5.46 5.58 S 5.34 5.46 5.58 1.17 1.26 1.35 h b2 1.53 1.65 1.77 b4 2.42 2.54 2.66 0.51 0.61 0.71 С D1 13.08 D2 0.51 0.93 1.35 12.81 E1 ØP1 6.60 6.80 7.00

NOTES: UNLESS OTHERWISE SPECIFIED.

(2X) b2


(2X) e

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DRAWING CONFORMS TO ASME Y14.5 2009.
- D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.

 \oplus 0.25 (M)

E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code A = Assembly Location

Y = Year WW = Work Week G = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present. Some products may not follow the Generic Marking.

onsemi, ONSEMI., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative