onsemi

MOSFET - Power, Single N-Channel 60 V, 62 mΩ, 11 A NVLJWS070N06CL

Features

- Small Footprint for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Wettable Flank Option for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T	$_{\rm J}$ = 25°C unless otherwise noted)
--------------------	---

Parameter		Symbol	Value	Unit	
Drain-to-Source Voltage		V _{DSS}	60	V	
Gate-to-Source Voltage	Э		V _{GS}	±20	V
Continuous Drain	Steady	T _C = 25°C	Ι _D	11	А
Current R _{θJC} (Notes 1, 3)		T _C = 100°C		8	
Power Dissipation	State	$T_C = 25^{\circ}C$	PD	15	W
$R_{\theta JC}$ (Note 1)		T _C = 100°C		8	
Continuous Drain		T _A = 25°C	۱ _D	4.4	А
Current R _{θJA} (Notes 1, 2, 3)	Steady	T _A = 100°C		3.1	
Power Dissipation	State	T _A = 25°C	PD	2.4	W
$R_{\theta JA}$ (Notes 1, 2)		T _A = 100°C		1.2	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \ \mu s$		I _{DM}	31	А
Operating Junction and Storage Temperature Range		T _J , T _{stg}	–55 to +175	°C	
Source Current (Body Diode)		I _S	13	А	
Single Pulse Drain-to-Source Avalanche Energy $(I_{L(pk)} = 0.4 A)$		E _{AS}	17	mJ	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		ΤL	260	°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	9.8	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	63	


1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.


2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.

3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
60 V	62 mΩ @ 10 V	11 A
00 V	85 mΩ @ 4.5 V	

ELECTRICAL CONNECTION





ORDERING INFORMATION


See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 250 µA		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				26		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V,$	T _J = 25 °C			10	μΑ
		$V_{DS} = 60 V$	T _J = 125°C			100	
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 V, V_G$	_S = 20 V			100	nA
ON CHARACTERISTICS (Note 4)				-			-
Gate Threshold Voltage	V _{GS(TH)}	V _{GS} = V _{DS} , I _I	_D = 6 μA	1.2		2.0	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-5.5		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 5 A		51	62	mΩ
		V _{GS} = 4.5 V	I _D = 5 A		68	85	1
Forward Transconductance	9 _{FS}	V _{DS} =10 V, I _D = 5 A			11		S
CHARGES AND CAPACITANCES	•						
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 25 V			160		pF
Output Capacitance	C _{OSS}				81		1
Reverse Transfer Capacitance	C _{RSS}				2		1
Total Gate Charge	Q _{G(TOT)}	V_{GS} = 4.5 V, V_{DS} = 48 V; I_{D} = 5 A			8		nC
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 48 V; I _D = 5 A			18		nC
Threshold Gate Charge	Q _{G(TH)}	V _{GS} = 10 V, V _{DS} = 48 V; I _D = 5 A			1.8		nC
Gate-to-Source Charge	Q _{GS}				2.5		1
Gate-to-Drain Charge	Q _{GD}				2.0		1
Plateau Voltage	V _{GP}				2.2		V
SWITCHING CHARACTERISTICS (Note 5	5)						
Turn-On Delay Time	t _{d(ON)}				4.4		ns
Rise Time	tr	V _{CS} = 10 V. Vr	ne = 48 V.		1.3		1
Turn-Off Delay Time	t _{d(OFF)}	$\begin{array}{l} V_{GS} = 10 \; V, \; V_{DS} = 48 \; V, \\ I_{D} = 5 \; A, \; R_{G} = 6 \; \Omega \end{array}$			9.4		1
Fall Time	t _f				1.3		1
DRAIN-SOURCE DIODE CHARACTERIS	TICS						
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V,	$T_J = 25^{\circ}C$		0.91	1.2	V
			T _J = 125°C		0.81		1
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dI _S /dt = 100 A/µs, I _S = 5 A			16		ns
Charge Time	t _a				9		1
Discharge Time	t _b				7		1
Reverse Recovery Charge	Q _{RR}				7	l	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Pulse Test: pulse width $\leq 300 \ \mu$ s, duty cycle $\leq 2\%$. 5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS




Figure 13. Transient Thermal Response Curve

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NVLJWS070N06CLTAG	070N	WDFN6 (Pb-Free, Wettable Flanks)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

WDFNW6 2.05x2.05, 0.65P

CASE 515AD **ISSUE O**

NDTES

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1. 2009.
- 2.

-A3

- CONTROLLING DIMENSION: MILLIMETERS DIMENSION & APPLIES TO PLATED TERMINALS AND IS MEASURED BETWEEN 0.15 AND 0.30MM FROM THE З. TERMINAL TIP.
- COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL 4. AS THE TERMINALS.
- POSITIONAL TOLERANCE APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS. 5.

DIM


L3


L3


MILLIMETERS


NDM.

MAX.











L3-



BOTTOM VIEW (SUPPLEMENTAL)


DETAIL A


-L3



0.09

MIN.





onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters, including "Typicals" must be validated for each customer applications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless agains

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Voice Mail: 1 800–282–9855 Toll Free U Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

NVLJWS070N06CL