onsemi

MOSFET - Power, Single N-Channel, STD Gate, SO8FL

40 V, 4.7 mΩ, 66 A NVMFWS004N04XM

Features

- Low R_{DS(on)} to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Small Footprint (5x6 mm) for Compact Design
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Motor Drive
- Battery Protection
- Synchronous Rectification

MAXIMUM RATINGS (T_J = 25° C unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V _{DSS}	40	V
Gate-to-Source Voltage	DC	V _{GS}	±20	V
Continuous Drain Current	$T_{C} = 25^{\circ}C$	I _D	66	А
	$T_{\rm C}$ = 100°C		47	
Power Dissipation	$T_{C} = 25^{\circ}C$	PD	38	W
Pulsed Drain Current	$\begin{array}{l} T_{C} = 25^{\circ}C, \\ t_{p} = 10 \ \mu s \end{array}$	I _{DM}	332	A
Operating Junction and Storage Temperature Range		T _J , T _{stg}	–55 to +175	°C
Source Current (Body Diode)		۱ _S	32	А
Single Pulse Avalanche Energy (I _{PK} = 32 A)		E _{AS}	68	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Note 2)	$R_{\theta JC}$	3.9	°C/W
Thermal Resistance, Junction-to-Ambient (Notes 1, 2)	$R_{\theta JA}$	42	

1. Surface-mounted on FR4 board using 650 mm², 2 oz. Cu pad.

The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.


V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
40 V	4.7 m Ω @ 10 V	66 A



N-CHANNEL MOSFET



DFNW5 (SO-8FL) CASE 507BA



ORDERING INFORMATION

Device	Package	Shipping [†]
NVMFWS004N04XMT1G	DFN5 (Pb–Free)	1500 / Tape & Reel


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted)


Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 1 mA, T _J = 25°C	40	-	-	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS}/\Delta T_{J}$	I _D = 1 mA, Referenced to 25°C	-	15	-	mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V_{DS} = 40 V, T_{J} = 25°C	-	-	10	μA
		V _{DS} = 40 V, T _J = 125°C	-	-	100	
Gate-to-Source Leakage Current	I _{GSS}	V_{GS} = 20 V, V_{DS} = 0 V	-	-	100	nA
ON CHARACTERISTICS						
Drain-to-Source On Resistance	R _{DS(on)}	V_{GS} = 10 V, I _D = 10 A, T _J = 25°C	-	4.1	4.7	mΩ
Gate Threshold Voltage	V _{GS(TH)}	V_{GS} = V_{DS} , I_D = 30 μ A, T_J = 25°C	2.5	-	3.5	V
Gate Threshold Voltage Temperature Coefficient	$\Delta V_{GS(TH)}/ \Delta T_J$	$V_{GS}=V_{DS},\ I_{D}=30\ \mu A$	-	-7.29	-	mV/°C
Forward Transconductance	9 FS	V _{DS} = 5 V, I _D = 10 A	-	45.5	-	S
CHARGES, CAPACITANCES & GATE RE	ESISTANCE	-			-	
Input Capacitance	C _{ISS}	V_{DS} = 25 V, V_{GS} = 0 V, f = 1 MHz	-	669	-	pF
Output Capacitance	C _{OSS}		-	431	-	
Reverse Transfer Capacitance	C _{RSS}		-	9.4	-	
Total Gate Charge	Q _{G(TOT)}	V_{DD} = 32 V, I _D = 30 A, V _{GS} = 10 V	-	10.6	-	nC
Threshold Gate Charge	Q _{G(TH)}		-	2.0	-	
Gate-to-Source Charge	Q _{GS}		-	3.2	-	
Gate-to-Drain Charge	Q _{GD}		-	2.1	-	
Gate-Resistance	R _G	f = 1 MHz	-	1.6	-	Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	t _{d(ON)}	Resistive Load, $V_{GS} = 0/10 V$,	-	11.9	-	ns
Rise Time	t _r	V_{DD} = 32 V, I _D = 30 A, R _G = 0 Ω	-	4.0	-	
Turn-Off Delay Time	t _{d(OFF)}		-	17.2	-]
Fall Time	t _f		-	3.6	-	
SOURCE-TO-DRAIN DIODE CHARACT	ERISTICS					
Forward Diode Voltage	V _{SD}	I_S = 10 A, V_{GS} = 0 V, T_J = 25°C	-	0.8	1.2	V
		I_{S} = 10 A, V_{GS} = 0 V, T_{J} = 125°C	-	0.7	-	1
Reverse Recovery Time	t _{RR}	$V_{GS} = 0 V, I_{S} = 30 A,$	-	28	-	ns
Charge Time	ta	dl/dt = 100 A/µs, V _{DD} = 32 V	-	11	-	1
Discharge Time	t _b		-	17	-	1
Reverse Recovery Charge	Q _{RR}	1	-	9.5	-	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. Transient Thermal Response

PACKAGE DIMENSIONS



onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters, including "Typicals" must be validated for each customer applications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights or the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any s

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS: Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com ONLINE SUPPORT: www.onsemi.com/support For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales