

MOSFET - Power, Single N-Channel 40 V, 1.65 mΩ, 314 A

NVMJST1D6N04C

Features

- Small Footprint (5x7 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- TCPAK57 5x7 Top Cool Package
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	40	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain Current R _{0.IC}	Steady T _C = 25°C		I _D	314	Α
(Notes 1, 3)	State	T _C = 100°C	1	222	
Power Dissipation		T _C = 25°C	P_{D}	300	W
R _{θJC} (Note 1)		T _C = 100°C		150	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \mu s$		I _{DM}	900	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			I _S	250	Α
Single Pulse Drain-to-Source Avalanche Energy (I _{L(pk)} = 15 A)			E _{AS}	338	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Drain Lead	$\Psi_{\sf JL}$	5.7	°C/W
Junction-to-Source Lead	$\Psi_{\sf JL}$	5.4	°C/W
Junction-to-Heatsink Top (Note 2)	Ψ_{JH}	1.9	°C/W
Junction-to-Ambient (Note 2)	$R_{\theta JA}$	29.7	°C/W
Junction-to-Case - Steady State	$R_{\theta JC}$	0.5	°C/W

- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2s2p JEDEC51-7 standard PCB mounted to a 25x25x3 (mm) aluminum heatsink with a 12 w/mK TIM interface.
- Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
40 V	1.65 mΩ @ 10 V	314 A



N-CHANNEL MOSFET



TCPAK57 CASE 760AG

MARKING DIAGRAM



XXXX = Specific Device Code A = Assembly Location

Y = Year W = Work Week

ZZ = Assembly Lot Code

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS					•	•	•
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$		40			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				21		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V,	T _J = 25 °C			10	μΑ
		$V_{DS} = 40 \text{ V}$	T _J = 125°C			100	
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 V, V_{GS}$	= 20 V			100	nA
ON CHARACTERISTICS (Note 4)							
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D =$	= 130 μA	2.5		3.5	V
Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-7.8		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 50 A		1.41	1.65	mΩ
Forward Transconductance	9 _{FS}	V _{DS} =15 V, I _D	= 50 A		130		S
CHARGES, CAPACITANCES & GATE RE	SISTANCE						
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MH	z, V _{DS} = 25 V		3300		pF
Output Capacitance	C _{OSS}				1600		1
Reverse Transfer Capacitance	C _{RSS}				45		1
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 10 V, V _{DS} = 20 V; I _D = 50 A			47		nC
Threshold Gate Charge	Q _{G(TH)}	$V_{GS} = 10 \text{ V}, V_{DS} = 20 \text{ V}; I_D = 50 \text{ A}$			10		
Gate-to-Source Charge	Q _{GS}				16		1
Gate-to-Drain Charge	Q_{GD}				7.0		
Plateau Voltage	V_{GP}				4.7		V
SWITCHING CHARACTERISTICS (Note 9	5)				•	•	•
Turn-On Delay Time	t _{d(ON)}	$V_{GS} = 10 \text{ V}, V_{DS}$	s = 20 V,		13		ns
Rise Time	t _r	$I_D = 50 \text{ A}, R_G = 2.5 \Omega$			48		
Turn-Off Delay Time	t _{d(OFF)}				29		
Fall Time	t _f				8.0		
DRAIN-SOURCE DIODE CHARACTERIS	TICS					1	
Forward Diode Voltage	V_{SD}	$V_{GS} = 0 \text{ V},$ $I_{S} = 50 \text{ A}$	T _J = 25°C		0.83	1.2	V
-			T _J = 125°C		0.7		1
Reverse Recovery Time	t _{RR}	V_{GS} = 0 V, dIS/dt = 100 A/ μ s, I_S = 50 A			57		ns
Charge Time	t _a				30		1
Discharge Time	t _b				27		1
Reverse Recovery Charge	Q _{RR}				68		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width $\leq 300~\mu s$, duty cycle $\leq 2\%$.

5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



vs. Voltage

Temperature

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation

Figure 8. Gate-to-Source Voltage vs. Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Safe Operating Area




Figure 12. I_{PEAK} vs. Time in Avalanche

TYPICAL CHARACTERISTICS




Figure 13. Thermal Characteristics

DEVICE ORDERING INFORMATION


Device	Marking	Package	Shipping [†]
NVMJST1D6N04CTXG	1D64C	TCPAK57 Top Cool (Pb-Free)	3000 / Tape & Reel


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

TCPAK57 7.5x5


CASE 760AG ISSUE B






NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. UNIT DIMENSIÓN: MILLIMETERS
- DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- 5. OPTIONAL MOLD FEATURE.
- LAND PAD UNDER THE PACKAGE BODY IS FOR MECHANICAL SUPPORT ONLY. SOLDER CONNECTION IS NOT REQUIRED.






SIDE VIEW

LAND PAD RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

MILLIMETERS				
DIM	MIN	NOM	MAX	
Α	1.30	1.35	1.45	
A1	-0.05	0.00	0.05	
A2	1.30	1.35	1.40	
b	0.36	0.41	0.46	
b1	0.30	0.40	0.50	
С	0.16	0.21	0.26	
D	5.20	5.30	5.40	
D1	3.47	3.57	3.67	
D2		0.17 RE	F	
D3		4.82 RE	F	
Е	5.00	5.10	5.20	
E1	4.02	4.12	4.22	
E2	0.30		0.50	
E3	0.14 REF			
е	1.00 BSC			
e1	0.50 BSC			
K	0.93	1.03	1.13	
Ι	7.30	7.50	7.70	
L	0.49	0.69	0.89	
L1	0.90	1.10	1.30	
α	0.60	0.65	0.70	
ڬ	0°	2.5°	5°	



DETAIL 'A'

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative