ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

Power MOSFET 40 V, 2.3 mΩ, 185 A, Single N–Channel

Features

- Small Footprint (5x6 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- NVMFS5830NLWF Wettable Flanks Product
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

	,				
Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	40	V
Gate-to-Source Voltage			V _{GS}	± 20	V
Continuous Drain Cur-		T _{mb} = 25°C	I _D	185	А
rent R _{ΨJ–mb} (Notes 1, 2, 3, 4)	Steady	$T_{mb} = 100^{\circ}C$		131	
Power Dissipation	State	T _{mb} = 25°C	PD	158	W
R _{ΨJ-mb} (Notes 1, 2, 3)		$T_{mb} = 100^{\circ}C$		79	
Continuous Drain Cur-		$T_A = 25^{\circ}C$	۱ _D	29	А
rent R _{θJA} (Notes 1, 3, 4)	Steady	$T_A = 100^{\circ}C$		20	
Power Dissipation	State	$T_A = 25^{\circ}C$	PD	3.8	W
R _{θJA} (Notes 1 & 3)		T _A = 100°C		1.9	
Pulsed Drain Current	T _A = 25	°C, t _p = 10 μs	I _{DM}	1012	А
Operating Junction and Storage Temperature			T _J , T _{stg}	–55 to + 175	°C
Source Current (Body Diode)			I _S	185	А
Single Pulse Drain-to-Source Avalanche Energy (T _J = 25°C, V _{GS} = 10 V, I _{L(pk)} = 85 A, L = 0.1 mH, R _G = 25 Ω)			E _{AS}	361	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Mounting Board (top) - Steady State (Notes 2, 3)	$R_{\Psi J-mb}$	1.0	°C/W
Junction-to-Ambient - Steady State (Note 3)	R_{\thetaJA}	39	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Psi (Ψ) is used as required per JESD51-12 for packages in which substantially less than 100% of the heat flows to single case surface.

Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
Maximum current for pulses as long as 1 second is higher but is dependent


on pulse duration and duty cycle.




ON Semiconductor®

http://onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
40 V	$2.3~\mathrm{m}\Omega$ @ 10 V	105 4
40 V	3.6 mΩ @ 4.5 V	185 A





ORDERING INFORMATION


See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit	
OFF CHARACTERISTICS								
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 250 μ A		40			V	
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J				32		mV/°C	
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V,	T _J = 25 °C			1		
		V _{DS} = 40 V	T _J = 125°C			100	μΑ	
Gate-to-Source Leakage Current	I _{GSS}	V_{DS} = 0 V, V_{GS} = ±20 V				±100	nA	
ON CHARACTERISTICS (Note 5)					•			
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 250 \mu A$		1.4		2.4	V	
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J				7.2		mV/°C	
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 20 A		1.7	2.3	_	
		V _{GS} = 4.5 V	I _D = 20 A		2.6	3.6	mΩ	
Forward Transconductance	9 _{FS}	V _{DS} = 5 V, I _D = 10 A			38		S	
CHARGES, CAPACITANCES & GATE RESIS	TANCE							
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 25 V			5880		pF	
Output Capacitance	C _{OSS}				750			
Reverse Transfer Capacitance	C _{RSS}				500			
Total Gate Charge	Q _{G(TOT)}	V _{GS} = 4.5 V, V _{DS} = 32 V; I _D = 60 A			58		nC	
Total Gate Charge	Q _{G(TOT)}	V_{GS} = 10 V, V_{DS} = 32 V; I_{D} = 60 A			113		nC	
Threshold Gate Charge	Q _{G(TH)}	V _{GS} = 4.5 V, V _{DS} = 32 V; I _D = 60 A			5.5		nC V	
Gate-to-Source Charge	Q _{GS}				19.5			
Gate-to-Drain Charge	Q _{GD}				32			
Plateau Voltage	V _{GP}				3.6			
SWITCHING CHARACTERISTICS (Note 6)	1							
Turn–On Delay Time	t _{d(ON)}	V_{GS} = 4.5 V, V _{DS} = 20 V, I _D = 10 A, R _G = 2.5 Ω			22		ns	
Rise Time	tr				32			
Turn-Off Delay Time	t _{d(OFF)}				40			
Fall Time	t _f				27			
DRAIN-SOURCE DIODE CHARACTERISTIC	s	4						
Forward Diode Voltage	e Voltage V _{SD}	$V_{GS} = 0 V, T_{J} = 25^{\circ}C T_{S} = 10 A T_{J} = 125^{\circ}C$	$T_J = 25^{\circ}C$		0.74	1.0		
				0.58		V		
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dIS/dt = 100 A/µs, I _S = 60 A			41			
Charge Time	t _a				19		ns	
Discharge Time	t _b				19		1	
Reverse Recovery Charge	Q _{RR}				33		nC	

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



http://onsemi.com 4

V_{DS}, DRAIN-TO-SOURCE VOLTAGE (V) Figure 11. Maximum Rated Forward Biased Safe Operating Area

10

10

1

0.1

0.01 0.1 V_{GS} = 10 V

Single Pulse $T_C = 25^{\circ}C$

E R_{DS(on)} Limit

Thermal Limit Package Limit

1

1 ms

10 ms

dc

100

TYPICAL CHARACTERISTICS





Figure 12. Thermal Response

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NVMFS5830NLT1G	V5830L	DFN5 (Pb–Free)	1500 / Tape & Reel
NVMFS5830NLWFT1G	5830LW	DFN5 (Pb-Free)	1500 / Tape & Reel
NVMFS5830NLT3G	V5830L	DFN5 (Pb–Free)	5000 / Tape & Reel
NVMFS5830NLWFT3G	5830LW	DFN5 (Pb–Free)	5000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and use registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use periors and science to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

For additional information, please contact your local Sales Representative