# onsemi

# **MOSFET** – Power, Single N-Channel 100 V, 14 mΩ, 46 A

# NVMYS016N10MCL

#### Features

- Small Footprint (5x6 mm) for Compact Design
- Low R<sub>DS(on)</sub> to Minimize Conduction Losses
- Low Q<sub>G</sub> and Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free, Beryllium Free and are RoHS Compliant

Г	Parameter Symbol Value Unit					
Falai			-	value	Unit	
Drain-to-Source Voltage		V <sub>DSS</sub>	100	V		
Gate-to-Source Voltage	Gate-to-Source Voltage		V <sub>GS</sub>	±20	V	
Continuous Drain		$T_{C} = 25^{\circ}C$	I <sub>D</sub>	46	А	
Current $R_{\theta JC}$ (Note 1)	Steady	$T_{C} = 100^{\circ}C$		32		
Power Dissipation	State	$T_{C} = 25^{\circ}C$	PD	64	W	
R <sub>θJC</sub> (Note 1)		$T_{C} = 100^{\circ}C$		32		
Continuous Drain		$T_A = 25^{\circ}C$	I <sub>D</sub>	10.9	А	
Current R <sub>θJA</sub> (Notes 1, 2)	Steady	T <sub>A</sub> = 100°C		7.7		
Power Dissipation	State	$T_A = 25^{\circ}C$	PD	3.6	W	
R <sub>θJA</sub> (Notes 1, 2)		T <sub>A</sub> = 100°C		1.8	1	
Pulsed Drain Current	$T_A = 25^{\circ}C, t_p = 10 \ \mu s$		I <sub>DM</sub>	264	А	
Operating Junction and Range	Storage T	emperature	T <sub>J</sub> , T <sub>stg</sub>	–55 to +175	°C	
Source Current (Body Diode)			۱ <sub>S</sub>	49	А	
Single Pulse Drain-to-Source Avalanche Energy (I <sub>L(pk)</sub> = 2.2 A)			E <sub>AS</sub>	358	mJ	
Lead Temperature Soldering Reflow for Solder- ing Purposes (1/8" from case for 10 s)			ΤL	260	°C	

**MAXIMUM RATINGS** (T<sub>1</sub> = 25°C unless otherwise noted)

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


#### THERMAL RESISTANCE RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 1)	$R_{\theta JC}$	2.35	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	41	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Surface-mounted on FR4 board using 1 in<sup>2</sup> pad size, 2 oz. Cu pad.

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX	
100 V	14 m $\Omega$ @ 10 V	46 A	
100 V	20 mΩ @ 4.5 V	40 A	





#### **ORDERING INFORMATION**


See detailed ordering, marking and shipping information on page 5 of this data sheet.

# **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 V, I_D = 250 \mu A$		100			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> / T <sub>J</sub>	$I_D = 250 \ \mu A$ , ref to $25^{\circ}C$			60		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$I_{DSS}$ $V_{CS} = 0.V$ $T_J = 25^{\circ}$	$T_J = 25^{\circ}C$			1	μA
		V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 100 V	T <sub>J</sub> = 125°C			100	1
Gate-to-Source Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = 20 V				100	nA
ON CHARACTERISTICS				-			-
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}, I_D =$	= 64 μA	1		3	V
Threshold Temperature Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>	I <sub>D</sub> = 64 μA, ref	to 25°C		-5.6		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V, I <sub>D</sub>	= 11 A		11.5	14	mΩ
		V <sub>GS</sub> = 4.5 V, I <sub>E</sub>	<sub>)</sub> = 9 A		16	20	1
Forward Transconductance	9 <sub>FS</sub>	V <sub>DS</sub> = 10 V, I <sub>D</sub>	= 11 A		42		S
Gate-Resistance	R <sub>G</sub>	T <sub>A</sub> = 25°0	2		1.2		Ω
CHARGES & CAPACITANCES	•						
Input Capacitance	C <sub>ISS</sub>				1250		pF
Output Capacitance	C <sub>OSS</sub>	V <sub>GS</sub> = 0 V, f = 1 MHz	, V <sub>DS</sub> = 50 V		460		1
Reverse Transfer Capacitance	C <sub>RSS</sub>				8		1
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 4.5 V, V <sub>DS</sub> = 50 V, I <sub>D</sub> = 11 A			9.0		nC
Total Gate Charge	Q <sub>G(TOT)</sub>	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 50 V, I <sub>D</sub> = 11 A			19		
Threshold Gate Charge	Q <sub>G(TH)</sub>				2.1		-
Gate-to-Source Charge	Q <sub>GS</sub>				3.7		
Gate-to-Drain Charge	Q <sub>GD</sub>				2.0		
Plateau Voltage	V <sub>GP</sub>				2.8		V
SWITCHING CHARACTERISTICS (Note	3)						
Turn-On Delay Time	t <sub>d(ON)</sub>				10		ns
Rise Time	t <sub>r</sub>	Vcs = 10 V. Vcs	s = 50 V.		3.4		1
Turn-Off Delay Time	t <sub>d(OFF)</sub>	$\begin{array}{l} V_{GS} = 10 \; V, V_{DS} = 50 \; V, \\ I_{D} = 11 \; A, \; R_{G} = 6 \; \Omega \end{array}$			26		-
Fall Time	t <sub>f</sub>				4.2		
DRAIN-SOURCE DIODE CHARACTER	ISTICS	L		1			
Forward Diode Voltage	V <sub>SD</sub>	V <sub>GS</sub> = 0 V,	$T_J = 25^{\circ}C$		0.84	1.3	V
		$I_{\rm S} = 11  {\rm A}$	T <sub>J</sub> = 125°C		0.72		
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = 0 V, dI <sub>S</sub> /dt = 100 A/µs, I <sub>S</sub> = 6 A			34		ns
Reverse Recovery Charge	Q <sub>RR</sub>				24		nC
Charge Time	t <sub>a</sub>				16		ns
Discharge Time	t <sub>b</sub>				17		ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Switching characteristics are independent of operating junction temperatures


#### **TYPICAL CHARACTERISTICS**



#### **TYPICAL CHARACTERISTICS**



### **TYPICAL CHARACTERISTICS**




#### Figure 13. Transient Thermal Impedance

#### **DEVICE ORDERING INFORMATION**

Device	Marking	Package	Shipping <sup>†</sup>
NVMYS016N10MCLTWG	016N10MCL	LFPAK4 (Pb–Free)	3000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### PACKAGE DIMENSIONS



PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL. SOLDERRM/D.

NOTES:

- DIMENSIONING AND TOLERANCING 1. PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: 2. MILLIMETERS.
- DIMENSIONS D AND E DO NOT 3. INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
- DATUMS A AND B ARE 5. DETERMINED AT DATUM PLANE H.

L	UNIT IN MILLIMETER					
DIM	MIN	NOM	MAX			
А	1.10	1.20	1.30			
A1	0.00	0.08	0.15			
A2	1.10	1.15	1.20			
A3	(	).25 REF	-			
A4	0.45	0.50	0.55			
b	0.40	0.45	0.50			
b2	3.80	4.10	4.40			
b3	2.00	2.10	2.20			
b4	0.70	0.80	0.90			
b5	0.55	0.65	0.75			
b6		0.31 REI	F			
С	0.19	0.22	0.25			
c2	0.19	0.22	0.25			
D	4.05	4.15	4.25			
D1	3.80	4.00	4.20			
D2	3.00	3.10	3.20			
D3	0.30	0.40	0.50			
D4	0.90	1.00	1.10			
Е	4.80	4.90	5.00			
E1	3.10	3.20	3.30			
E2	5.00	5.15	5.30			
е	1.27 BSC					
1/2e	0.635 BSC					
e1	0.40 REF					
Н	6.00	6.15	6.30			
L	0.40	0.65	0.85			
L1	0.80	0.90	1.00			
L2	0.90	1.10	1.30			
L3	0.00	0.10	0.20			
q	0°	4°	8°			

onsemi. OnSemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries. LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

٥