

Silicon Carbide (SiC) Module – 30 mohm SiC M3S MOSFET, 1200 V, 2-PACK Half Bridge Topology, F1 Package

Product Preview

NXH030P120M3F1PTG

The NXH030P120M3F1 is a power module containing 30 mΩ / 1200 V SiC MOSFET half-bridge and a thermistor in an F1 package.

Features

- 30 mΩ / 1200 V M3S SiC MOSFET Half-Bridge
- Thermistor
- Options with Pre-Applied Thermal Interface Material (TIM) and without Pre-Applied TIM
- Press-Fit Pins
- These Devices are Pb-Free, Halide Free and are RoHS Compliant

Typical Applications

- Solar Inverter
- Uninterruptible Power Supplies
- Electric Vehicle Charging Stations
- Industrial Power





Figure 1. NXH030P120M3F1 Schematic Diagram


This document contains information on a product under development. onsemi reserves the right to change or discontinue this product without notice.

PACKAGE PICTURE




PIM18 33.8x42.5 (PRESS FIT)
CASE 180BW

MARKING DIAGRAM



NXH030P120M3F1PTG = Specific Device Code
AT = Assembly & Test Site Code
YYWW = Year and Work Week Code

PIN CONNECTIONS



See Pin Function Description for pin names

ORDERING INFORMATION

See detailed ordering and shipping information on page 4 of this data sheet.

NXH030P120M3F1PTG

PIN FUNCTION DESCRIPTION

Pin	Name	Description
1	DC+	DC Positive Bus connection
2	DC+	DC Positive Bus connection
3	S1	M1 Kelvin Emitter (High side switch)
4	G1	M1 Gate (High side switch)
5	DC+	DC Positive Bus connection
6	DC+	DC Positive Bus connection
7	TH2	Thermistor Connection 2
8	TH1	Thermistor Connection 1
9	DC-	DC Negative Bus connection
10	DC-	DC Negative Bus connection
11	DC-	DC Negative Bus connection
12	DC-	DC Negative Bus connection
13	PHASE	Center point of half bridge
14	PHASE	Center point of half bridge
15	G2	M2 Gate (Low side switch)
16	S2	M2 Kelvin Emitter (Low side switch)
17	PHASE	Center point of half bridge
18	PHASE	Center point of half bridge

NXH030P120M3F1PTG

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
SiC MOSFET			
Drain–Source Voltage	V_{DS}	1200	V
Gate–Source Voltage	V_{GS}	+22/–10	V
Continuous Drain Current @ $T_c = 80^\circ\text{C}$ ($T_J = 175^\circ\text{C}$)	I_D	42	A
Pulsed Drain Current ($T_J = 150^\circ\text{C}$)	I_{Dpulse}	84	A
Maximum Power Dissipation ($T_J = 175^\circ\text{C}$)	P_{tot}	116	W
Minimum Operating Junction Temperature	T_{JMIN}	–40	$^\circ\text{C}$
Maximum Operating Junction Temperature	T_{JMAX}	175	$^\circ\text{C}$

THERMAL PROPERTIES

Storage Temperature Range	T_{stg}	–40 to 150	$^\circ\text{C}$
---------------------------	-----------	------------	------------------

INSULATION PROPERTIES

Isolation Test Voltage, $t = 1\text{ s}$, 60 Hz	V_{is}	4800	V_{RMS}
Creepage Distance		12.7	mm
CTI		600	
Substrate Ceramic Material		Al_2O_3	
Substrate Ceramic Material Thickness		0.32	mm

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.

RECOMMENDED OPERATING RANGES

Rating	Symbol	Min	Max	Unit
Module Operating Junction Temperature	T_J	–40	150	$^\circ\text{C}$

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
SiC MOSFET CHARACTERISTICS						
Zero Gate Voltage Drain Current	$V_{GS} = 0\text{ V}$, $V_{DS} = 1200\text{ V}$, $T_J = 25^\circ\text{C}$	I_{DSS}	–	–	100	μA
Drain–Source On Resistance	$V_{GS} = 18\text{ V}$, $I_D = 30\text{ A}$, $T_J = 25^\circ\text{C}$	$R_{DS(ON)}$	–	31.5	38.5	$\text{m}\Omega$
	$V_{GS} = 18\text{ V}$, $I_D = 30\text{ A}$, $T_J = 125^\circ\text{C}$		–	49.5	–	
	$V_{GS} = 18\text{ V}$, $I_D = 30\text{ A}$, $T_J = 150^\circ\text{C}$		–	57.2	–	
	$V_{GS} = 18\text{ V}$, $I_D = 30\text{ A}$, $T_J = 175^\circ\text{C}$		–	66	–	
Gate–Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 15\text{ mA}$	$V_{GS(TH)}$	2.04	2.6	4.4	V
Gate Leakage Current	$V_{GS} = -10\text{ V} / 22\text{ V}$, $V_{DS} = 0\text{ V}$	I_{GSS}	–1	–	1	μA
Input Capacitance	$V_{DS} = 800\text{ V}$, $V_{GS} = 0\text{ V}$, $f = 1\text{ MHz}$	C_{ISS}	–	2271	–	pF
Reverse Transfer Capacitance		C_{RSS}	–	11.6	–	
Output Capacitance		C_{OSS}	–	153	–	
Total Gate Charge	$V_{DS} = 800\text{ V}$, $V_{GS} = -3/18\text{ V}$, $I_D = 30\text{ A}$	$Q_{G(TOTAL)}$	–	110	–	nC
Gate–Source Charge		Q_{GS}	–	19	–	nC
Gate–Drain Charge		Q_{GD}	–	33	–	nC

NXH030P120M3F1PTG

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
SiC MOSFET CHARACTERISTICS						
Turn-on Delay Time	$T_J = 25^\circ\text{C}$ $V_{DS} = 800\text{ V}$, $I_D = 30\text{ A}$ $V_{GS} = -3\text{ V}$ / 18 V , $R_G = 3.9\ \Omega$	$t_{d(on)}$	—	19.6	—	ns
Rise Time		t_r	—	6.6	—	
Turn-off Delay Time		$t_{d(off)}$	—	84.8	—	
Fall Time		t_f	—	9.4	—	
Turn-on Switching Loss per Pulse		E_{ON}	—	610	—	μJ
Turn-off Switching Loss per Pulse		E_{OFF}	—	54	—	
Turn-on Delay Time	$T_J = 150^\circ\text{C}$ $V_{DS} = 800\text{ V}$, $I_D = 30\text{ A}$ $V_{GS} = -3\text{ V}$ / 18 V , $R_G = 3.9\ \Omega$	$t_{d(on)}$	—	18.8	—	ns
Rise Time		t_r	—	5.6	—	
Turn-off Delay Time		$t_{d(off)}$	—	93	—	
Fall Time		t_f	—	9	—	
Turn-on Switching Loss per Pulse		E_{ON}	—	800	—	μJ
Turn-off Switching Loss per Pulse		E_{OFF}	—	89	—	
Diode Forward Voltage	$V_{GS} = -3\text{ V}$, $I_{SD} = 30\text{ A}$, $T_J = 25^\circ\text{C}$	V_{SD}	—	4.67	6	V
	$V_{GS} = -3\text{ V}$, $I_{SD} = 30\text{ A}$, $T_J = 125^\circ\text{C}$		—	4.45	—	
	$V_{GS} = -3\text{ V}$, $I_{SD} = 30\text{ A}$, $T_J = 150^\circ\text{C}$		—	4.4	—	
Thermal Resistance – Chip-to-Case	M1, M2	R_{thJC}	—	0.816	—	$^\circ\text{C/W}$
Thermal Resistance – Chip-to-Heatsink	Thermal grease, Thickness = 2 Mil +2%, A = 2.8 W/mK	R_{thJH}	—	(TBD)	—	$^\circ\text{C/W}$

THERMISTOR CHARACTERISTICS

Nominal Resistance	$T = 25^\circ\text{C}$	R_{25}	—	5	—	$\text{k}\Omega$
	$T = 100^\circ\text{C}$	R_{100}	—	457	—	Ω
	$T = 150^\circ\text{C}$	R_{150}	—	159.5	—	Ω
Deviation of R_{100}	$T = 100^\circ\text{C}$	$\Delta R/R$	-5	—	5	%
Power Dissipation – Recommended Limit	0.15 mA, Non-self-heating Effect	P_D	—	0.1	—	mW
Power Dissipation – Absolute Maximum	5 mA	P_D	—	34.2	—	mW
Power Dissipation Constant			—	1.4	—	mW/K
B-value	B (25/50), tolerance $\pm 3\%$		—	3375	—	K
B-value	B (25/100), tolerance $\pm 3\%$		—	3436	—	K

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

ORDERING INFORMATION

Orderable Part Number	Marking	Package	Shipping
NXH030P120M3F1PTG	NXH030P120M3F1PTG	F1HALFBR: Case 180BW Press-fit Pins with pre-applied thermal interface material (TIM) (Pb-Free / Halide Free)	20 Units / Blister Tray

NXH030P120M3F1PTG

TYPICAL CHARACTERISTIC M1/M2 SiC MOSFET CHARACTERISTIC




Figure 2. MOSFET Typical Output Characteristic
 $V_{GS} = 15V$




Figure 3. MOSFET Typical Output Characteristic
 $V_{GS} = 18V$




Figure 4. MOSFET Typical Output Characteristic
 $V_{GS} = \text{var.}$




Figure 5. Body Diode Forward Voltage




Figure 6. $R_{DS(ON)}$ Drain to Source On Resistance
vs. Junction Temperature




Figure 7. Reverse Bias Safe Operating Area
(RBSOA)

NXH030P120M3F1PTG

TYPICAL CHARACTERISTIC (continued) M1/M2 SiC MOSFET CHARACTERISTIC




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Gate to Source Voltage vs. Gate Charge




Figure 10. Switching On Loss vs. Drain Current
 $V_{DS} = 600 \text{ V}$




Figure 11. Switching On Loss vs. Gate Resistance
 $V_{DS} = 600 \text{ V}$




Figure 12. Switching Off Loss vs. Drain Current
 $V_{DS} = 600 \text{ V}$




Figure 13. Switching Off Loss vs. Gate Resistance
 $V_{DS} = 600 \text{ V}$

NXH030P120M3F1PTG

TYPICAL CHARACTERISTIC (continued) M1/M2 SiC MOSFET CHARACTERISTIC




Figure 14. Switching On Loss vs. Drain Current
 $V_{DS} = 800\text{ V}$




Figure 15. Switching On Loss vs. Gate Resistance
 $V_{DS} = 800\text{ V}$




Figure 16. Switching Off Loss vs. Drain Current
 $V_{DS} = 800\text{ V}$




Figure 17. Switching Off Loss vs. Gate Resistance
 $V_{DS} = 800\text{ V}$




Figure 18. Reverse Recovery Energy vs. Drain Current, $V_{DS} = 800\text{ V}$




Figure 19. Reverse Recovery Energy vs. Gate Resistance, $V_{DS} = 800\text{ V}$

NXH030P120M3F1PTG

TYPICAL CHARACTERISTIC (continued) M1/M2 SiC MOSFET CHARACTERISTIC




Figure 20. di/dt Turn On vs. Drain Current
 $V_{DS} = 800\text{ V}$




Figure 21. di/dt Turn On vs. Gate Resistance
 $V_{DS} = 800\text{ V}$




Figure 22. di/dt Turn Off vs. Drain Current
 $V_{DS} = 800\text{ V}$




Figure 23. di/dt Turn Off vs. Gate Resistance
 $V_{DS} = 800\text{ V}$




Figure 24. dv/dt Turn On vs. Drain Current
 $V_{DS} = 800\text{ V}$




Figure 25. dv/dt Turn On vs. Gate Resistance
 $V_{DS} = 800\text{ V}$

NXH030P120M3F1PTG

TYPICAL CHARACTERISTIC (continued) M1/M2 SiC MOSFET CHARACTERISTIC




Figure 26. dv/dt Turn Off vs. Drain Current
 $V_{DS} = 800\text{ V}$




Figure 27. dv/dt Turn Off vs. Gate Resistance
 $V_{DS} = 800\text{ V}$


NXH030P120M3F1PTG

Table 1. CAUER NETWORKS

Cauer Element #	Rth (K/W)	Cth (Ws/K)
1	0.0008598	0.0006888
2	0.0060273	0.0001577
3	0.0131590	0.0002630
4	0.0651160	0.0013257
5	0.1977800	0.0040903
6	0.3716200	0.0208140
7	0.1618000	0.5875200

PIN POSITION INFORMATION

scale = 2.5 : 1



S Pin position

Pin #	X	Y	Function	Pin #	X	Y	Function
1	6.4	3.2	DC+	10	19.2	12.8	DC-
2	6.4	6.4	DC+	11	22.4	12.8	DC-
3	19.2	0.0	S1	12	25.6	12.8	DC-
4	19.2	3.2	G1	13	6.4	22.4	Phase
5	32.0	3.2	DC+	14	6.4	25.6	Phase
6	32.0	6.4	DC+	15	19.2	22.4	G2
7	0.0	12.8	TH2	16	19.2	25.6	S2
8	0.0	16.0	TH1	17	32.0	22.4	Phase
9	12.8	12.8	DC-	18	32.0	25.6	Phase


NXH030P120M3F1PTG

PACKAGE DIMENSIONS

PIM18 33.8x42.5 (PRESS FIT)

CASE 180BW



ISSUE B



NOTES:

1. CONTROLLING DIMENSION: MILLIMETERS
2. PIN POSITION TOLERANCE IS $\pm 0.4\text{mm}$

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	11.65	12.00	12.35
A1	16.00	16.50	17.00
A2	0.00	0.35	0.60
A3	12.85	13.35	13.85
b	1.15	1.20	1.25
b1	0.59	0.64	0.69
D	33.50	33.80	34.10
D1	4.40	4.50	4.60
D2	27.95	28.10	28.25
E	47.70	48.00	48.30
E1	42.35	42.50	42.65
E2	52.90	53.00	53.10
E3	62.30	62.80	63.30
E4	4.90	5.00	5.10
P	2.20	2.30	2.40



onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marketing.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales