onsemi

Q1PACK Module

NXH50M65L4Q1SG, NXH50M65L4Q1PTG

This high-density, integrated power module combines high-performance IGBTs with rugged anti-parallel diodes.

Features

- Extremely Efficient Trench with Fieldstop Technology
- Low Switching Loss Reduces System Power Dissipation
- Module Design Offers High Power Density
- Low Inductive Layout
- Q1PACK Packages with Solder and Pressfit Pins

Typical Applications

- Solar Inverters
- Uninterruptable Power Supplies




Figure 1. Schematic







Figure 2. Pin Assignments





(SOLDER PIN) CASE 180CA PIM27, 71x37.4 (PRESSFIT PIN) CASE 180CP

MARKING DIAGRAM



ORDERING INFORMATION

See detailed ordering and shipping information on page 9 of this data sheet.

ABSOLUTE MAXIMUM RATINGS

Rating	Symbol	Value	Unit
GBT (T11, T12, T13, T14, T21, T22)	•		
Collector-emitter voltage	V _{CES}	650	V
Collector current @ $T_h = 80^{\circ}C$ (per IGBT)	۱ _C	48	А
Pulsed collector current, T _{pulse} limited by T _{jmax}	I _{CM}	144	А
Power Dissipation Per IGBT $T_j = T_{jmax}$, $T_h = 80^{\circ}C$	P _{tot}	72	W
Gate-emitter voltage	V _{GE}	±20	V
Maximum Junction Temperature	TJ	175	°C
DIODE (D12, D14, D20, D21, D22)			
Peak Repetitive Reverse Voltage	V _{RRM}	650	V
Forward Current, DC @ $T_h = 80^{\circ}C$ (per Diode)	١ _F	50	А
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	I _{FSM}	225	A
Power Dissipation Per Diode $T_j = T_{jmax}, T_h = 80^{\circ}C$	P _{tot}	86	W
Maximum Junction Temperature	Τ _J	175	°C
HERMAL PROPERTIES			
Operating Temperature under switching condition	T _{VJ OP}	–40 to (T _{jmax} – 25)	°C
Storage Temperature range	T _{stg}	-40 to 125	°C
NSULATION PROPERTIES	-		
Isolation test voltage, t = 2 min, 60 Hz	V _{is}	4000	Vac
Creepage distance		12.7	mm

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)


Parameter	Test Condition	Symbol	Min	Тур	Max	Unit
GBT (T11, T12, T13, T14, T21, T22)						
Collector-emitter cutoff current	$V_{GE} = 0 \text{ V}, V_{CE} = 650 \text{ V}$	I _{CES}	-	-	300	μΑ
Collector-emitter saturation voltage	V_{GE} = 15 V, I _C = 50 A, T _j = 25°C V _{GE} = 15 V, I _C = 50 A, T _j = 150°C	V _{CE(sat)}	-	1.56 1.76	2.22 _	V
Gate-emitter threshold voltage	$V_{GE} = V_{CE}, I_C = 50 \text{mA}$	V _{GE(TH)}	3.1	4.45	5.2	V
Gate leakage current	$V_{GE} = 20 \text{ V}, \text{ V}_{CE} = 0 \text{ V}$	I _{GES}	-	-	400	nA
Turn-on delay time	T _i = 25°C V _{CE} =350 V, I _C = 50 A	t _{d(on)}	-	14	-	ns
Rise time	$V_{CE} = 350$ V, I _C = 50 A V _{GE} = 15 V, -9 V, R _G = 6 Ω	t _r	-	20	-	
Turn-off delay time		t _{d(off)}	-	68	-	
Fall time		t _f	-	20	-	
Turn on switching loss		Eon	-	0.46	-	mJ
Turn off switching loss		E _{off}	-	0.44	-	
Turn-on delay time	$T_j = 125^{\circ}C$	t _{d(on)}	-	16	-	ns
Rise time	V'_{CE} = 350 V, I _C = 50 A V _{GE} = 15 V, -9 V, R _G = 6 Ω	t _r	-	23	-	
Turn-off delay time		t _{d(off)}	-	78	-	
Fall time		t _f	-	52	-	
Turn on switching loss	7	Eon	-	0.78	-	mJ
Turn off switching loss	7	E _{off}	-	0.60	-	


ELECTRICAL CHARACTERISTICS (T_J = $25^{\circ}C$ unless otherwise specified) (continued)


Parameter	Test Condition	Symbol	Min	Тур	Max	Unit
IGBT (T11, T12, T13, T14, T21, T22)						
Input capacitance	$V_{CE} = 20 \text{ V}, \text{ V}_{GE} = 0 \text{ V}, \text{ f} = 1 \text{ MHz}$	Cies	-	3137	-	pF
Output capacitance		C _{oes}	-	146	-	
Reverse transfer capacitance		C _{res}	-	17	-	
Gate charge total	V_{CE} = 350 V, I_{C} = 40 A, V_{GE} = ±15 V	Qg	-	180	-	nC
Thermal Resistance - chip-to-heatsink	Thermal grease, Thickness = 2.1 Mil	R _{thJH}	-	1.32	-	°C/W
Thermal Resistance - chip-to-case	±2% λ = 2.9 W/mK	R _{thJC}	-	0.96	-	°C/W
IGBT INVERSE DIODE (D12, D14, D21, D2	22)					
Forward voltage	I _F = 50 A, T _j = 25°C I _F = 50 A, T _j = 175°C	V _F	-	2.25 1.7	2.7 _	V
Reverse Recovery Time		t _{rr}	-	28	-	ns
Reverse Recovery Current	− T _i = 25°C	Q _{rr}	-	281	-	nc
Peak Reverse Recovery Current	V _{CE} = 350 V, I _C = 50 A	I _{rrm}	-	18	-	А
Peak Rate of Fall of Recovery Current	$V_{GE} = 15 \text{ V}, -9 \text{ V}, \text{ R}_{G} = 6 \Omega$	Di/dt _{max}	-	1.42	-	A/μs
Reverse Recovery Energy		E _{rr}	-	33	-	μJ
Reverse Recovery Time		t _{rr}	-	65	-	ns
Reverse Recovery Current		Q _{rr}	-	1094	-	nc
Peak Reverse Recovery Current	$V_{CF} = 350 \text{ V}, \text{ I}_{C} = 50 \text{ A}$	I _{rrm}	-	33	-	Α
Peak Rate of Fall of Recovery Current	$V_{GE} = 15 \text{ V}, -9 \text{ V}, \text{ R}_{G} = 6 \Omega$	Di/dt _{max}	-	1.32	-	A/μs
Reverse Recovery Energy		Err	-	198	-	μJ
Thermal Resistance - chip-to-heatsink	Thermal grease, Thickness = 2.1 Mil	R _{thJH}	-	1.10	-	°C/W
Thermal Resistance - chip-to-case	±2% λ = 2.9 W/mK	R _{thJC}	-	0.79	-	°C/W
DIODE (D20)						
Forward voltage	$ I_F = 50 \text{ A}, \ T_j = 25^{\circ}\text{C} \\ I_F = 50 \text{ A}, \ T_j = 175^{\circ}\text{C} $	V _F		2.25 1.7	2.7 _	V
Reverse leakage current	$V_{CE} = 650 \text{ V}, V_{GE} = 0 \text{ V}$	l _r	-	-	300	μA
Thermal Resistance - chip-to-heatsink	Thermal grease, Thickness = 2.1 Mil	R _{thJH}	-	1.10	-	°C/W
Thermal Resistance - chip-to-case	±2% λ = 2.9 W/mK	R _{thJC}	-	0.79	-	°C/W
THERMISTOR CHARACTERISTICS						
Nominal resistance	T = 25°C	R ₂₅	-	22	-	kΩ
Nominal resistance	T = 100°C	R ₁₀₀	-	1486	-	Ω
Deviation of R25		R/R	-5	-	5	%
Power dissipation		PD	-	200	-	mW
Power dissipation constant			-	2	-	mW/∘C
B-value	B (25/50), tol ±3%		-	-	3950	°C
B-value	B (25/100), tol ±3%		-	-	3998	°C
NTC reference			_	-	В	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


TYPICAL CHARACTERISTICS - IGBT (T11, T12, T13, T14, T21, T22)








TYPICAL CHARACTERISTICS - (T11, T12, T13, T14) IGBT COMMUTATES D21, D22 DIODE (CONTINUED)






R_g, GATE RESISTOR (Ω)


Figure 14. Typical Turn-On Switching Time vs. Rg

R_a, GATE RESISTOR (Ω)

TYPICAL CHARACTERISTICS - (T21, T22) IGBT COMMUTATES D20 DIODE



TYPICAL CHARACTERISTICS - (T21, T22) IGBT COMMUTATES D20 DIODE (CONTINUED)



TYPICAL CHARACTERISTICS – DIODE









Figure 23. Typical Reverse Recovery Energy Loss vs. IC



20





TYPICAL CHARACTERISTICS - DIODE (CONTINUED)






Figure 27. Typical Reverse Recovery Peak Current vs. Rg












TYPICAL THERMAL CHARACTERISTICS









Figure 33. Transient Thermal Impedance – Diode

ORDERING INFORMATION

Device	Package Type	Status	Shipping
NXH50M65L4Q1SG (Solder Pin)	PIM27, 71x37.4 Q1PACK	In Development	21 Units / BTRAY
NXH50M65L4Q1PTG (Pressfit Pin)	PIM27, 71x37.4 Q1PACK	In Development	21 Units / BTRAY

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS


onsemi



NOTES:

PIM27, 71x37.4 (SOLDER PIN) CASE 180CA ISSUE B


DATE 14 DEC 2022



. A	
4	
END VIEW	

NOTE 4

	MILLIMETERS			
DIM	MIN.	NOM.	MAX.	
Α	15.90	16.40	16.90	
A2	11.70	11.90	12.10	
A3	0.00	0.20	0.60	
b	0.95	1.00	1.05	
b1	0.75	0.80	0.85	
D	70.80	71.00	71.20	
D1	81.70	82.00	82.30	
D2	70.80	71.00	71.20	
Е	37.10	37.40	37.70	
E2	30.60	30.80	31.00	
Р	4.10	4.30	4.50	
P1	9.30	9.50	9.70	
P2	1.80	2.00	2.20	



1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009

5. PACKAGE MARKING IS LOCATED AS SHOWN ON THE SIDE

OPPOSITE THE PACKAGE ORIENTATION FEATURES

3. DIMENSIONS b AND b1 APPLY TO THE PLATED TERMINALS AND

2. CONTROLLING DIMENSION ; MILLIMETERS

ARE MEASURED AT DIMENSION A1

4. PIN POSITION TOLERANCE IS ± 0.4mm

PIN POSITION PIN POSITION PIN PIN Х Υ Х γ 1 52.20 0.00 15 20.35 28.20 2 49.20 0.00 16 22.85 28.20 26.10 0.00 17 29.35 28.20 3 23.10 0.00 18 31.85 28.20 4 5 3.00 0.00 19 39.20 28.20 0.00 0.00 20 42.20 28.20 6 49.20 7 0.00 8.00 21 28.20 8 0.00 10.50 52.20 28.20 22 17.70 52.20 20.20 9 0.00 23 10 0.00 20.20 24 52.20 17.70 11 0.00 28.20 25 52.20 10.50 12 3.00 28.20 26 52.20 8.00 13 10.00 28.20 27 26.10 22.10 14 13.00 28.20

 DOCUMENT NUMBER:
 98AON20006H
 Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

 DESCRIPTION:
 PIM27, 71X37.4 (SOLDER PIN)
 PAGE 1 OF 2

 onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation


special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2019

onsemí

PIM27, 71x37.4 (SOLDER PIN) CASE 180CA ISSUE B


DATE 14 DEC 2022



DOCUMENT NUMBER:	98AON20006H	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	PIM27, 71X37.4 (SOLDER PIN)		PAGE 2 OF 2	

onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi



 DOCUMENT NUMBER:
 98AON26650H
 Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

 DESCRIPTION:
 PIM27, 71X37.4 (PRESSFIT PIN)
 PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights or the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>