

EliteSiC Power MOSFET Module 650 V, 32 mΩ H-Bridge

NXVF6532M3TG01

Features

- 650 V 32 mΩ SiC MOSFET Module with Al₂O₃ DBC
- H-Bridge with SIP for On-Board Charger (OBC)
- Creepage/Clearance per IEC60664-1, IEC 60950-1
- Compact Design for Low Total Module Resistance
- Module Serialization for Full Traceability
- Lead Free, ROHS and UL94V-0 Compliant
- Automotive Qualified per AEC-Q101/Q200 and AQG324

Typical Applications

- PFC/DC-DC Converter for On-Board Charger in xEV Applications

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	650	V
Gate-to-Source Voltage	V _{GS}	-8/+22	V
Recommended Operation Values of Gate-to-Source Voltage, T _J ≤ 175 °C	V _{GSop}	-3/+18	V
Continuous Drain Current (Note 1)	I _D	31	A
Power Dissipation (Note 1)			
Pulsed Drain Current (Note 2)	I _{DM}	165	A
Operating Junction Temperature Range	T _J	-55 to +175	°C
Storage Temperature Range	T _{stg}	-40 to +125	°C
Source Current (Body Diode)	I _S	14.5	A
Single Pulse Drain-to-Source Avalanche Energy, I _{av} = 16.7 A, L = 1 mH	E _{AS}	139	mJ

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. Maximum continuous current and power, without switching losses, to reach T_J = 175 °C defined by design based on MOSFET R_{DS(on)} and R_{θJC} and not subject to production test
2. Repetitive rating limited by maximum junction temperature

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Max	Unit
Thermal Resistance, Junction-to-Case (Note 3)	R _{θJC}	1.74	2.3	°C/W
Thermal Resistance, Junction-to-Sink (Note 4)	R _{θJS}	2.43	-	


3. Test method compliant with MIL STD 883-1012.1, Cosmetic oxidation and discoloration on the DBC surface allowed
4. Defined by thermal simulation assuming the module is mounted on a 3 mm Al-360 die casting material with 38 μm of 3.0 W/mK thermal interface material

V _{(BR)DSS}	R _{DS(on)} TYP	I _D MAX
650 V	32 mΩ @ 18 V	31 A



AUTOMOTIVE POWER MODULE16
40.10x21.90x4.50, 1.90P
CASE 829AA

MARKING DIAGRAM



- XXXX = Specific Device Code
- ZZZ = Lot ID
- AT = Assembly & Test Location
- Y = Year
- W = Work Week
- NNN = Serial Number

ORDERING INFORMATION

Device	Package	Shipping
NXVF6532M3TG01	APM16	12 / Tube

NXVF6532M3TG01

ELECTRICAL CHARACTERISTICS SiC MOSFET

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
-----------	--------	----------------	-----	-----	-----	------

OFF CHARACTERISTICS MOSFET

Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$	650	–	–	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS} / T_J$	$I_D = 1\text{ mA}$, Referenced to -55 °C to 175 °C (Note 5)	–	90	–	mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	$V_{GS} = 0\text{ V}, V_{DS} = 650\text{ V}$	–	–	100	μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{GS} = -8/+22\text{ V}, V_{DS} = 0\text{ V}$	–	–	±1	μA

ON CHARACTERISTICS SiC MOSFET (Note 5)

Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}, I_D = 7.5\text{ mA}$	2	2.6	4	V
Recommended Gate Voltage	V_{GOP}		–3	–	+18	V
Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS} = 18\text{ V}, I_D = 15\text{ A}, T_J = 25\text{ °C}$	–	32	44	mΩ
		$V_{GS} = 18\text{ V}, I_D = 15\text{ A}, T_J = 175\text{ °C}$ (Note 5)	–	49	–	
Forward Transconductance	g_{FS}	$V_{DS} = 10\text{ V}, I_D = 15\text{ A}$ (Note 5)	–	12	–	S

CHARGES, CAPACITANCES & GATE RESISTANCE SiC MOSFET

Input Capacitance	C_{ISS}	$V_{DS} = 400\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$ (Note 5)	–	1215	–	pF
Output Capacitance	C_{OSS}		–	198	–	
Reverse Transfer Capacitance	C_{RSS}		–	9.8	–	
Total Gate Charge	$Q_{G(TOT)}$	$V_{DS} = 400\text{ V}, I_D = 15\text{ A}, V_{GS} = 18\text{ V}$ (Note 5)	–	58	–	nC
Threshold Gate Charge	$Q_{G(TH)}$		–	8.5	–	
Gate-to-Source Charge	Q_{GS}		–	15	–	
Gate-to-Drain Charge	Q_{GD}		–	19	–	
Gate Resistance	R_G	$V_{GS} = 0\text{ V}, f = 1\text{ MHz}$	–	5	–	Ω

INDUCTIVE SWITCHING CHARACTERISTICS SiC MOSFET

Turn-On Delay Time	$t_{d(ON)}$	$V_{GS} = -3/18\text{ V}, V_{DS} = 400\text{ V}, I_D = 15\text{ A}, R_G = 4.7\text{ Ω}, T_J = 25\text{ °C}$ (Note 5)	–	9	–	ns
Rise Time	t_r		–	7.6	–	
Turn-Off Delay Time	$t_{d(OFF)}$		–	27.6	–	
Fall Time	t_f		–	7.6	–	
Turn-On Switching Loss	E_{ON}		–	12.8	–	μJ
Turn-Off Switching Loss	E_{OFF}		–	22.7	–	
Total Switching Loss	E_{tot}		–	35.5	–	

INDUCTIVE SWITCHING CHARACTERISTICS SiC MOSFET

Turn-On Delay Time	$t_{d(ON)}$	$V_{GS} = -3/18\text{ V}, V_{DS} = 400\text{ V}, I_D = 15\text{ A}, R_G = 4.7\text{ Ω}, T_J = 175\text{ °C}$ (Note 5)	–	8.4	–	ns
Rise Time	t_r		–	6	–	
Turn-Off Delay Time	$t_{d(OFF)}$		–	33.2	–	
Fall Time	t_f		–	9.2	–	
Turn-On Switching Loss	E_{ON}		–	11.3	–	μJ
Turn-Off Switching Loss	E_{OFF}		–	27.6	–	
Total Switching Loss	E_{tot}		–	38.9	–	

NXVF6532M3TG01

ELECTRICAL CHARACTERISTICS SiC MOSFET (continued)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit	
SOURCE-TO-DRAIN DIODE CHARACTERISTICS SiC MOSFET							
Forward Diode Voltage	V_{SD}	$I_{SD} = 15 \text{ A}, V_{GS} = -3 \text{ V}, T_J = 25 \text{ }^\circ\text{C}$	-	4.5	6.0	V	
		$I_{SD} = 15 \text{ A}, V_{GS} = -3 \text{ V}, T_J = 175 \text{ }^\circ\text{C}$ (Note 5)	-	4.1	-		
Reverse Recovery Time	t_{RR}	$V_{GS} = -3 \text{ V}, I_S = 15 \text{ A},$ $dI/dt = 1000 \text{ A}/\mu\text{s}, V_{DS} = 400 \text{ V}$ $T_J = 25 \text{ }^\circ\text{C}$ (Note 5)	-	17.6	-	ns	
Charge Time	t_a		-	10	-		
Discharge Time	t_b		-	7.6	-		
Reverse Recovery Charge	Q_{RR}		-	91.1	-		nC
Reverse Recovery Energy	E_{REC}		-	9.3	-		μJ
Peak Reverse Recovery Current	I_{RRM}		-	10	-		A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Defined by design, not subject to production test.

COMPONENTS

Component	Description	Type	Quality	Specification
NTC (Note 6)	10 k Ω , $\pm 3\%$ Case Size 0603	Discrete	1	B Constants B25/50 : 3590 B25/85 = 3635 B25/100 = 3650 \pm

6. The value is the temperature of the thermistor itself.

ISOLATION VOLTAGE

Parameter	Symbol	Condition	Rating	Unit
Isolation Voltage	V_{ISO}	60 Hz, Sinusoidal, AC 1 minute, Connection Pins to Heat Sink Plate (Note 7)	3300	V_{rms}

7. Equivalent to 60 Hz, Sinusoidal, AC 1 second, 3960 V_{rms}

TYPICAL CHARACTERISTICS




Figure 3. Output Characteristics




Figure 4. Output Characteristics




Figure 5. Transfer Characteristics




Figure 6. On-Resistance vs. Gate Voltage




Figure 7. On-Resistance vs. Drain Current




Figure 8. On-Resistance vs. Junction Temperature

NXVF6532M3TG01

TYPICAL CHARACTERISTICS (CONTINUED)




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics




Figure 11. Reverse Conduction Characteristics




Figure 12. Safe Operating Area




Figure 13. Avalanche Current vs. Pulse Time (UIS)




Figure 14. Inductive Switching Loss vs. Drain Current

NXVF6532M3TG01

TYPICAL CHARACTERISTICS (CONTINUED)




Figure 15. Inductive Switching Loss vs. T_{J}




Figure 16. Inductive Switching Loss vs. Drain Voltage




Figure 17. Inductive Switching Loss vs. Gate Resistance






Figure 18. Thermal Response Characteristics



AUTOMOTIVE POWER MODULE16 40.10x21.90x4.50, 1.90P
CASE 829AA
ISSUE O

DATE 21 JAN 2025




NOTES:

1. DIMENSIONING AND TOLERANCING PER. ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR EXTRUSIONS.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A2	4.30	4.50	4.70
b	0.45	0.50	0.60
b1	0.75	0.80	0.90
c	0.45	0.50	0.60
D	39.90	40.10	40.30
E	26.20	26.70	27.20
E1	21.70	21.90	22.10
E2	12.10	12.30	12.50
e	1.60	1.90	2.20
e1	2.20	2.50	2.80
L	9.20	9.55	9.90
L1	1.80	2.05	2.30
q	36.85	37.10	37.35
S	2.95 REF		
ØA	3.00	3.20	3.40

GENERIC MARKING DIAGRAM*



XXXX = Specific Device Code
ZZZ = Lot ID
AT = Assembly & Test Location
Y = Year
WW = Work Week
NNN = Serial Number

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON64549H	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	AUTOMOTIVE POWER MODULE16 40.10x21.90x4.50, 1.90P	PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales