MOSFET - Power, Single N-Channel, Logic Level, µ8FL

80 V, 5.3 mΩ, 79 A

NVTFWS005N08XL

$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
80 V	5.3 mΩ @ 10 V	79 A
	8.4 mΩ @ 4.5 V	



N–CHANNEL MOSFET



WDFNW8
(µ8FL)
CASE 515AP

Features

- Low Q_{RR}, Soft Recovery Body Diode
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- Synchronous Rectification (SR) in DC–DC and AC–DC
- Primary Switch in Isolated DC–DC Converter
- Motor Drives
- Automotive 48 V System

MAXIMUM RATINGS (T_J = 25°C unless otherwise stated)

Parameter		Symbol	Value	Unit
Drain–to–Source Voltage		V_{DSS}	80	V
Gate–to–Source Voltage		V_{GS}	±20	V
Continuous Drain Current (Note 1)	T_C = 25°C	I_D	79	A
	T_C = 100°C		56	
Power Dissipation (Note 1)	T_C = 25°C	P_D	82	W
	T_C = 100°C		41	
Pulsed Drain Current	T_C = 25°C, t_p = 100 µs	I_{DM}	290	A
Pulsed Source Current (Body Diode)		I_{SM}	290	
Operating Junction and Storage Temperature Range		T_J, T_{STG}	–55 to +175	°C
Source Current (Body Diode)		I_S	118	A
Single Pulse Avalanche Energy (I_{PK} = 34 A) (Note 3)		E_{AS}	57	mJ
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)		T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Actual continuous current will be limited by thermal & electromechanical application board design.
3. Surface mounted on FR4 board using a 1 in^2, 1 oz. Cu pad.
4. $R_{\theta JA}$ is determined by the users board design.

MARKING DIAGRAM



W005 = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
▪ = Pb–Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping†
NVTFWS005N08XLTAG	WDFN8 (µ8FL)	1500 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2024

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction−to−Case	$R_{\theta JC}$	1.8	°C/W
Thermal Resistance, Junction−to−Ambient (Notes 5, 6)	$R_{\theta JA}$	46	

5. Surface−mounted on FR4 board using a 1 in^2, 1 oz. Cu pad.
6. $R_{\theta JA}$ is determined by the user's board design.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain−to−Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA	80			V
Drain−to−Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	I_D = 1 mA. Referenced to 25°C		31		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 80 V			1	μA
		V_{DS} = 80 V, T_J = 125°C			250	
Gate−to−Source Leakage Current	I_{GSS}	V_{GS} = 20 V, V_{DS} = 0 V			100	nA
ON CHARACTERISTICS						
Drain−to−Source On Resistance	$R_{DS(on)}$	V_{GS} = 10 V, I_D = 17 A		4.3	5.3	mΩ
		V_{GS} = 4.5 V, I_D = 14 A		5.7	8.4	
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 85 μA	1.5		2.1	V
Gate Threshold Voltage Temperature Coefficient	$\Delta V_{GS(TH)}/\Delta T_J$	V_{GS} = V_{DS}, I_D = 85 μA		−6.4		mV/°C
Forward Transconductance	g_{FS}	V_{DS} = 5 V, I_D = 17 A		113		S
CHARGES, CAPACITANCES & GATE RESISTANCE						
Input Capacitance	C_{ISS}	V_{GS} = 0 V, V_{DS} = 40 V, f = 1 MHz		1800		pF
Output Capacitance	C_{OSS}			450		
Reverse Transfer Capacitance	C_{RSS}			14		
Output Charge	Q_{OSS}			33		nC
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 4.5 V, V_{DD} = 40 V; I_D = 17 A		14		
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 10 V, V_{DD} = 40 V; I_D = 17 A		28		
Threshold Gate Charge	$Q_{G(TH)}$			3		
Gate−to−Source Charge	Q_{GS}			5		
Gate−to−Drain Charge	Q_{GD}			4		
Gate Plateau Voltage	V_{GP}			2.7		V
Gate Resistance	R_G	f = 1 MHz		0.6		Ω
SWITCHING CHARACTERISTICS						
Turn−On Delay Time	$t_{d(ON)}$	Resistive Load, V_{GS} = 0/10 V, V_{DD} = 64 V, I_D = 17 A, R_G = 2.5 Ω		10		ns
Rise Time	t_r			4		
Turn−Off Delay Time	$t_{d(OFF)}$			25		
Fall Time	t_f			3		
SOURCE−TO−DRAIN DIODE CHARACTERISTICS						
Forward Diode Voltage	V_{SD}	V_{GS} = 0 V, I_S = 17 A		0.8	1.2	V
		V_{GS} = 0 V, I_S = 17 A, T_J = 125°C		0.7		
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, dI/dt = 1000 A/μs, I_S = 17 A, V_{DD} = 64 V		19		ns
Charge Time	t_a			11		
Discharge Time	t_b			9		
Reverse Recovery Charge	Q_{RR}			105		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS



Figure 1. On−Region Characteristics



Figure 2. Transfer Characteristics



Figure 3. On−Resistance vs. Gate Voltage



Figure 4. On−Resistance vs. Drain Current



Figure 5. Normalized ON Resistance vs. Junction Temperature



Figure 6. Drain Leakage Current vs. Drain Voltage

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS



Figure 7. Capacitance Characteristics



Figure 8. Gate Charge Characteristics



Figure 9. Resistive Switching Time Variation vs. Gate Resistance



Figure 10. Diode Forward Characteristics



Figure 11. Safe Operating Area (SOA)



Figure 12. Avalanche Current vs. Pulse Time (UIS)

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS



Figure 13. Maximum Current vs. Case Temperature



Figure 14. Transient Thermal Response

Share Feedback
Your Opinion Matters

PACKAGE DIMENSIONS

WDFNW8 3.30x3.30x0.75, 0.65P
CASE 515AP
ISSUE A



TOP VIEW



SIDE VIEW



BOTTOM VIEW

NOTES:

1. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5-2018.
2. ALL DIMENSION ARE IN MILLIMETERS.
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
4. FULL-CUT u8FL FUSED WF.



DETAIL "A"
SCALE 2:1



DETAIL "B"
SCALE 2:1

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.70	0.75	0.80
A1	0.00	----	0.05
b	0.23	0.33	0.43
c	0.15	0.20	0.25
D	3.20	3.30	3.40
D1	2.95	3.13	3.30
D2	1.98	2.20	2.40
E	3.20	3.30	3.40
E1	2.80	3.00	3.15
E2	1.40	1.60	1.80
E3	1.35	1.50	1.60
E4	0.15	0.25	0.40
e	0.65 BSC		
G	0.30	0.43	0.55
G1	0.25	0.35	0.45
K	0.55	0.75	0.95
L	0.35	0.52	0.65
L1	0.06	0.15	0.30
L2	0.25 BSC		



RECOMMENDED MOUNTING FOOTPRINT*

* FOR ADDITIONAL INFORMATION ON OUR Pb-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

Share Feedback
Your Opinion Matters

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales