

# IGBT Die

## PCFG75T65SQF

Using novel field stop IGBT technology, ON Semiconductor's new series of field stop 4<sup>th</sup> generation IGBTs offer the optimum performance for solar inverter and UPS applications where low conduction and switching losses are essential.

### Features

- Maximum Junction Temperature:  $T_J = 175^{\circ}\text{C}$
- Positive Temperature Co-efficient for Easy Parallel Operating
- High Current Capability
- Low Saturation Voltage:  $V_{CE(sat)} = 1.6\text{ V (Typ.) @ } I_C = 75\text{ A}$
- High Input Impedance
- Fast Switching
- Tighten Parameter Distribution

### Typical Applications

- Solar Inverters
- UPS Systems

### MECHANICAL DATA


Parameter	Mils	$\mu\text{m}$
Die Size	$183.07 \times 183.07$	$4650 \times 4650$
Gate Pad Size	$160 \times 155.48$	$4064 \times 3949.1$
Emitter Pad Size	$14.05 \times 18$	$357 \times 457.2$
Die Thickness	2.48	63
Scribe Width	80 $\mu\text{m}$	
Top Metal	5 $\mu\text{m}$ AlSiCu	
Back Metal	1.05 $\mu\text{m}$ Al/NiV/Ag	
Topside Passivation	Silicon Nitride	
Wafer Diameter	200 mm	
Max Possible Die Per Wafer	1178	
Recommended Storage Environment	In original container, in dry nitrogen, < 3 months at ambient temperature of $23^{\circ}\text{C}$	




ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)

$V_{RCE} = 650\text{ V}$   
 $I_C = \text{Limited by } T_{J(max)}$



IGBT Die



DIE Outline

### ORDERING INFORMATION

Device	Inking?	Shipping Method
PCFG75T65SQF	No	Sawn Wafer on Tape

# PCFG75T65SQF

## MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Collector to Emitter Voltage, $T_J = 25^\circ\text{C}$	$V_{CES}$	650	V
Gate to Emitter Voltage	$V_{GES}$	$\pm 20$	V
Collector Current @ $T_C = 25^\circ\text{C}$	$I_C$	(Note 1)	A
Pulsed Collector Current	$I_{CM}$	300	A
Operating Junction Temperature	$T_J$	-40 to +175	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	+18 to +28	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Depending on the thermal properties of assembly.
2. Not subject to production test – verified by design/characterization.

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
-----------	-----------------	--------	-----	-----	-----	------

### OFF CHARACTERISTICS

Collector–Emitter Breakdown Voltage	$V_{GE} = 0\text{ V}, I_C = 1\text{ mA}$	$BV_{CES}$	650			V
Temperature Coefficient of Breakdown Voltage	$I_C = 1\text{ mA}$ , reference to $25^\circ\text{C}$	$\Delta BV_{CES}/\Delta T_J$		0.6		$\text{V}/^\circ\text{C}$
Collector–Emitter Cutoff Current	$V_{GE} = 0\text{ V}, V_{CE} = V_{CES}$	$I_{DSS}$			250	$\mu\text{A}$
Gate Leakage Current	$V_{CE} = 0\text{ V}, V_{GE} = V_{GES}$	$I_{GSS}$			$\pm 400$	nA

### ON CHARACTERISTICS

G–E Threshold Voltage	$V_{GE} = V_{CE}, I_C = 75\text{ mA}$	$V_{GE(th)}$	2.6	4.5	6.4	V
Collector–Emitter Saturation Voltage	$I_C = 75\text{ A}, V_{GE} = 15\text{ V}$	$V_{CE(sat)}$		1.6	2.1	V
	$I_C = 75\text{ A}, V_{GE} = 15\text{ V}, T_C = 175^\circ\text{C}$			1.92		V

### DYNAMIC CHARACTERISTICS

Input Capacitance	$V_{GE} = 0\text{ V}, V_{CE} = 30\text{ V}, f = 1\text{ MHz}$	$C_{ies}$		4845		pF
Reverse Transfer Capacitance		$C_{res}$		14		


### GATE CHARGE CHARACTERISTICS

Total Gate Charge	$V_{CE} = 400\text{ V}, I_C = 60\text{ A}, V_{GE} = 15\text{ V}$	$Q_g$		128		nC
Gate to Emitter Charge		$Q_{ge}$		23		
Gate to Collector Charge		$Q_{gc}$		29		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

\*Switching characteristics and thermal properties depend strongly on package (module) design and mounting technology. This product is intended for part AFGHL75T65SQD and extended electrical characteristics can be referenced to the AFGHL75T65SQD datasheet. For ordering, technique and other information on ON Semiconductor automotive bare die products, please contact [automotivebaredie@onsemi.com](mailto:automotivebaredie@onsemi.com).

# PCFG75T65SQF



(all dimensions in  $\mu\text{m}$ )

Figure 1. Die Layout

**onsemi, Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)