

ON Semiconductor

Is Now

onsemi™

To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and **onsemi** and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

IGBT Die

PCFG75T65SQF

Using novel field stop IGBT technology, ON Semiconductor's new series of field stop 4th generation IGBTs offer the optimum performance for solar inverter and UPS applications where low conduction and switching losses are essential.

Features

- Maximum Junction Temperature: $T_J = 175^\circ\text{C}$
- Positive Temperature Co-efficient for Easy Parallel Operating
- High Current Capability
- Low Saturation Voltage: $V_{CE(sat)} = 1.6\text{ V (Typ.) @ } I_C = 75\text{ A}$
- High Input Impedance
- Fast Switching
- Tighten Parameter Distribution

Typical Applications

- Solar Inverters
- UPS Systems

MECHANICAL DATA


Parameter	Mils	μm
Die Size	183.07 × 183.07	4650 × 4650
Gate Pad Size	160 × 155.48	4064 × 3949.1
Emitter Pad Size	14.05 × 18	357 × 457.2
Die Thickness	2.48	63
Scribe Width	80 μm	
Top Metal	5 μm AlSiCu	
Back Metal	1.05 μm Al/NiV/Ag	
Topside Passivation	Silicon Nitride	
Wafer Diameter	200 mm	
Max Possible Die Per Wafer	1178	
Recommended Storage Environment	In original container, in dry nitrogen, < 3 months at ambient temperature of 23°C	




ON Semiconductor®

www.onsemi.com

$V_{RCE} = 650\text{ V}$
 $I_C = \text{Limited by } T_{J(max)}$



IGBT Die



DIE Outline

ORDERING INFORMATION

Device	Inking?	Shipping Method
PCFG75T65SQF	No	Sawn Wafer on Tape

PCFG75T65SQF

MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Collector to Emitter Voltage, $T_J = 25^\circ\text{C}$	V_{CES}	650	V
Gate to Emitter Voltage	V_{GES}	± 20	V
Collector Current @ $T_C = 25^\circ\text{C}$	I_C	(Note 1)	A
Pulsed Collector Current	I_{CM}	300	A
Operating Junction Temperature	T_J	-40 to +175	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	+18 to +28	$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Depending on the thermal properties of assembly.
2. Not subject to production test – verified by design/characterization.

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
-----------	-----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Collector–Emitter Breakdown Voltage	$V_{GE} = 0\text{ V}, I_C = 1\text{ mA}$	BV_{CES}	650			V
Temperature Coefficient of Breakdown Voltage	$I_C = 1\text{ mA}$, reference to 25°C	$\Delta BV_{CES}/\Delta T_J$		0.6		$\text{V}/^\circ\text{C}$
Collector–Emitter Cutoff Current	$V_{GE} = 0\text{ V}, V_{CE} = V_{CES}$	I_{DSS}			250	μA
Gate Leakage Current	$V_{CE} = 0\text{ V}, V_{GE} = V_{GES}$	I_{GSS}			± 400	nA

ON CHARACTERISTICS

G–E Threshold Voltage	$V_{GE} = V_{CE}, I_C = 75\text{ mA}$	$V_{GE(th)}$	2.6	4.5	6.4	V
Collector–Emitter Saturation Voltage	$I_C = 75\text{ A}, V_{GE} = 15\text{ V}$	$V_{CE(sat)}$		1.6	2.1	V
	$I_C = 75\text{ A}, V_{GE} = 15\text{ V}, T_C = 175^\circ\text{C}$			1.92		V

DYNAMIC CHARACTERISTICS

Input Capacitance	$V_{GE} = 0\text{ V}, V_{CE} = 30\text{ V}, f = 1\text{ MHz}$	C_{ies}		4845		pF
Reverse Transfer Capacitance		C_{res}		14		

GATE CHARGE CHARACTERISTICS


Total Gate Charge	$V_{CE} = 400\text{ V}, I_C = 60\text{ A}, V_{GE} = 15\text{ V}$	Q_g		128		nC
Gate to Emitter Charge		Q_{ge}		23		
Gate to Collector Charge		Q_{gc}		29		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

*Switching characteristics and thermal properties depend strongly on package (module) design and mounting technology. This product is intended for part AFGHL75T65SQD and extended electrical characteristics can be referenced to the AFGHL75T65SQD datasheet.


For ordering, technique and other information on ON Semiconductor automotive bare die products, please contact automotivebaredie@onsemi.com.

PCFG75T65SQF



(all dimensions in μm)

Figure 1. Die Layout

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative