

VCSEL Driver with Buck PWM Controller Evaluation Board User's Manual



ON Semiconductor®

www.onsemi.com

NCL30105G1EVB

Overview

This manual covers the specification, theory of operation, testing and construction of the NCL30105G1EVB evaluation board. This evaluation board uses NCL30105 as a high pulse current low duty cycle VCSEL driver. The expected duty cycle is less than 5% in typical applications. The NCL30105 is an inverted buck converter design with constant off time control.

Features

The key features of this evaluation board include:

- High Peak Current
- Small Size
- Fast Rise/Fall Time
- PWM Control

SPECIFICATIONS

Input voltage	8.8 V dc – 22 V dc	Nom.
Output Voltage	3 V dc	Nom.
Output Current	4 A	Peak
Output Ripple	± 6.5%	
Output Rise/Fall Time	8 μ s / 36 μ s	
Switching Frequency	146 kHz	@12 V
Dimming Interface	PWM	SMA connector
PCB Size	25 mm × 55 mm	




Figure 1. Evaluation Board

THEORY OF OPERATION

Overview

The NCL30105G1EVb drives a low voltage high current VCSEL for camera illumination for the automotive market.

Current Control

The NCL30105 is a peak current mode control with constant off time. Peak current control provides accurate current regulation. The value of R7 sets the peak current as follows:

$$I_{\text{peak}} = \frac{1.01 \text{ V}}{R7}$$

The soft start pin controls the peak current at turn on. A capacitor on this pin is charged up by a 20 μA internal current source. For PWM operation this capacitor is very small to allow for fast rise times. Analog dimming can be done by programming the voltage on the soft start pin. The connection for this option is not brought out on this demo board although this control method is still available.

The off time is held constant in operation. R5 programs the off time. Constant off time control eliminates sub harmonic oscillation in buck converters where the duty cycle exceeds 50%. The on time is determined by the input voltage, the output voltage, and the inductor value.

Consequently, the switching frequency will vary over line and load conditions even though the off time is constant. The NCL30105 has a maximum on time $\sim 34 \mu\text{s}$ which is set internally.

Vcc

Q1 is an emitter follower that limits Vcc to $\sim 14 \text{ V}$. The NCL30105 has an upper Vcc limit of 22 V. Some automotive applications exceed the 22 V limit especially in the case of load dump.

Current Sense

The current sense pin has a Leading Edge Blanking (LEB) function to avoid false triggering of the current sense comparator. The LEB is $\sim 500 \text{ ns}$.

Dimming

The demo board is set up for PWM dimming through J3 (SMA). A 0–5 V square wave signal will provide PWM dimming. The absence of a signal to J3, the output defaults to off.

The output current (green trace) follows the PWM input signal (yellow trace). The output filter affects the rise and fall times.




Figure 2. Dimming Signal vs. I_{OUT}




Figure 3. Fall Time vs. Input Signal





Figure 4. Rise Time vs. Input Signal

The rise and fall times are affected by the output filter values. Raising the Fsw will reduce the size requirement for the output capacitor which reduces rise and fall times.

Reducing the off time will increase the switching frequency and reduce current ripple for a given output inductor.

SCHEMATIC



NCL30105G1EVB

BILL OF MATERIAL

BILL OF MATERIAL

Qty	Reference	Part	Distributor	Dist. P/N	Manufacturer	Mfr_PN	Insert	Safety Controlled
5	C1, C2, C3, C4, C6	4.7 μ F 25 V	Digikey	1276-3178-1-ND	Samsung	CL31B475KAHN NWE	Yes	No
2	C5, C7	220 pF	Digikey	311-1416-1-ND	Yageo	CC0402JRNPO9 BN221	Yes	No
1	D1	FSV530AF	ON Semiconductor	FSV530AFCT-ND	ON Semiconductor	FSV530AF	Yes	No
1	D2	SZMM3Z15V T1G	ON Semiconductor	SZMM3Z15VT1GOS CT-ND	ON Semiconductor	SZMM3Z15VT1G	Yes	No
1	J1	CONN JACK PWR	Digikey	732-5929-1-ND	Wurth	694106106102	Yes	No
1	J2	OSTTA024163	Digikey	ED2580-ND	On Shore	OSTTA024163	Yes	No
1	J3	SMA	Digikey	WM5525-ND	Molex	731000114	Yes	No
1	L1	4.7 μ H	Digikey	587-1624-1-ND	Taiyo Yuden	CBC3225T4R7MR	Yes	No
1	L2	15 μ H	Digikey	732-1242-1-ND	Wurth	7447709150	Yes	No
1	Q1	MMBT3904W T1G	ON Semiconductor	MMBT3904WT1G	ON Semiconductor	MMBT3904WT1G	Yes	No
1	Q2	NVMFS5C46 8NT1G	ON Semiconductor	NVMFS5C468NT1G OSCT-ND	ON Semiconductor	NVMFS5C468NT 1G	Yes	No
1	R1	10k	Digikey	311-10.0KLRCT-ND	Yaego	RC0402FR-0710 KL	Yes	No
2	R2, R3	49.9	Digikey	311-49.9LRCT-ND	Yaego	RC0402FR-0749 R9L	Yes	No
2	R4, R6	100	Digikey	311-100LRCT-ND	Yaego	RC0402FR-0710 0RL	Yes	No
1	R5	30k	Digikey	311-30.0KLRCT-ND	Yaego	RC0402FR-0730 KL	Yes	No
1	R7	220m	Digikey	408-1608-1-ND	Susumu	KRL2012E-M-R2 20-F-T5	Yes	No
1	U1	NCL30105DR 2G	ON Semiconductor	NCL30105DR2GOS CT-ND	ON Semiconductor	NCL30105DR2G	Yes	No

TEST PROCEDURE

1. Require Equipment
 - a. DC Power Supply 12 V @ 2 A
 - b. Function Generator
 - c. LED Load similar to Luminus CBT-90-B-L11-J101 (observe the correct polarity)
2. Connector the LED Load to J2
3. Apply 12 V to J1 (2.1 x 5.5 Power Connector)
4. Connect a function generator and set as follows:
 - a. Frequency – 100 Hz
 - b. Duty Cycle – 5%
 - c. Vin – 0–5 V (into a 50 Ω load)
5. Observe that the output current transitions from 0 to ~4 A in sync with the function generator output.




Figure 6. Test Setup

onsemi, **onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and will only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

THE BOARD IS PROVIDED BY ONSEMI TO YOU "AS IS" AND WITHOUT ANY REPRESENTATIONS OR WARRANTIES WHATSOEVER. WITHOUT LIMITING THE FOREGOING, ONSEMI (AND ITS LICENSORS/SUPPLIERS) HEREBY DISCLAIMS ANY AND ALL REPRESENTATIONS AND WARRANTIES IN RELATION TO THE BOARD, ANY MODIFICATIONS, OR THIS AGREEMENT, WHETHER EXPRESS, IMPLIED, STATUTORY OR OTHERWISE, INCLUDING WITHOUT LIMITATION ANY AND ALL REPRESENTATIONS AND WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, TITLE, NON-INFRINGEMENT, AND THOSE ARISING FROM A COURSE OF DEALING, TRADE USAGE, TRADE CUSTOM OR TRADE PRACTICE.

onsemi reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by **onsemi** shall not constitute any representation or warranty by **onsemi**, and no additional obligations or liabilities shall arise from **onsemi** having provided such information or services.

onsemi products including the boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. You agree to indemnify, defend and hold harmless **onsemi**, its directors, officers, employees, representatives, agents, subsidiaries, affiliates, distributors, and assigns, against any and all liabilities, losses, costs, damages, judgments, and expenses, arising out of any claim, demand, investigation, lawsuit, regulatory action or cause of action arising out of or associated with any unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of any products and/or the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

FCC WARNING – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by **onsemi** to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

onsemi does not convey any license under its patent rights nor the rights of others.

LIMITATIONS OF LIABILITY: **onsemi** shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if **onsemi** is advised of the possibility of such damages. In no event shall **onsemi**'s aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

The board is provided to you subject to the license and other terms per **onsemi**'s standard terms and conditions of sale. For more information and documentation, please visit www.onsemi.com.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales