

AR0544 PRISM Module

Prototype 1/4.2-inch 5 MP Module

Preliminary Document

PRISM1M-AR0544CSSC130110-G EVB

The AR0544 5 MP Premier Reference Image Sensor Module (PRISM) module is part of the **onsemi** PRISM family of modules offering standardized connectors, layout configuration and OTPM protocol. The modules are compatible with Evaluations systems and reference designs offered by **onsemi**. The modules are offered from **onsemi** as prototype modules not meant for customer production shipments.

Table 1. KEY PERFORMANCE PARAMETERS

Parameter	Value
SENSOR	
Sensor Part Number	AR0544CSSC33SMD20-E
FUNCTIONAL	
Output	Raw
CFA	RGB-Color
Max. fps	60 fps @ 2592 x 1944
Interface	2-lane MIPI D-PHY
MECHANICAL	
Module size X*Y*Z(mm)	8.5 x 23.5 x 51.5
Module Weight	≈0.4 g
OPTICAL	
Optical Format	1/4.2-inch
Image active resolution	2592 x 1944
Pixel size	1.4 μm
CRA	33.2° (MAX)
Focus Range	0.21 m~INFINITE
Hyperfocal Distance	0.44 m
Effective Focal Length (EFL)	1.64 mm
Lens F number	2.2
Lens Structure	5P
Diagonal Field of View (DFOV)	120°
Vertical Field of View (VFOV)	80.1°
Horizontal Field of View (HFOV)	99.2°
TV distortion	≤ ±10%



Applications

- Security Camera
- IoT
- Car DVR

This Preliminary document is for informational purposes only. **onsemi** may update or withdraw it without notice. Content and referenced products are under development and subject to change.

Table 1. KEY PERFORMANCE PARAMETERS (continued)

Parameter	Value
ELECTRICAL	
Supply voltages	VDDIO: 1.8 V (1.7 V < Vsupply < 1.9 V) VDD: 1.05 V (1.00 V < Vsupply < 1.10 V) VAA: 2.8 V (2.6 < Vsupply < 2.9 V)
I2C Pull-up Resistor in Module (Note 1)	No pull-up resistor in module
PROGRAMMABLE STORAGE	
This module has programmable storage.	EEPROM is programed per PRISM programming specifications. OTPM is supported but not programmed. Please refer to the PRISM Module EEPROM and OTPM Application note (AND90264/D) for more information.


1. onsemi recommends that host sites add a 1.5k pull-up resistor.

Table 2. ORDERING INFORMATION

Part Number	Orderable Product Attribute Description
PRISM1M-AR0544CSSC130110-GEVB	AR0544 5 MP 1/4.2" color 33° CRA CSP package in PRISM module with 120.2° DFOV Lens
PRISM1_ADPTR_DM3D1_GEBV	Adapter Board to Demo3, DevWareX Supported

Table 3. MODULE CONNECTOR PINOUT

Pin Number	Pin Name	Pin Number	Pin Name
1	GPIO1	34	GPI3
2	DGND	33	DGND
3	DGND	32	EXTCLK
4	DATA_0P	31	DGND
5	DATA_0N	30	DATA_1P
6	DGND	29	DATA_1N
7	CLK_P	28	DGND
8	CLK_N	27	NC
9	DGND	26	NC
10	NC	25	DGND
11	NC	24	VDD
12	DGND	23	VDD
13	VDDIO	22	SDATA
14	SCLK	21	RESET_N
15	GPIO0	20	GPI2
16	DGND	19	AGND
17	VAA	18	VAA



MODULE CONNECTOR

Part Number	Number of Pins	A	B	C
BM20B(0.8)-34DP-0.4V(51)	Plug	34	0.8 mm	0.4 mm



Figure 2.

REVISION HISTORY

Revision	Description of Changes	Date
P1	Made this document public.	2/26/2026
P2	Added module weight to Table 1.	3/23/2026


This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

MECHANICAL DIMENSIONS




MODULE-34, 8.50x23.50x5.15
CASE MODGT
ISSUE A


DATE 02 DEC 2025



TOP VIEW



SIDE VIEW



BOTTOM VIEW

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. RIGID PCB AREA.
4. RIGID PCB AND HOLDER.
5. LENS TOP DIAMETER.
6. FLEXIBLE PRINTED CIRCUIT.
7. OPTICAL FIELD OF VIEW AT ΦB .
8. CONNECTOR: BM20B(0.8)-34DP-0.4V(51), 34 PINS.
9. BACKSIDE GROUNDED.
10. OBJECT ORIENTATION IS DEFINED BY THE IMAGE SHOWN.

MILLIMETERS			
DIM	MIN	NOM	MAX
A	5.00	5.15	5.30
A1	0.35	0.40	0.45
A2	0.10	0.15	0.20
A3	0.35	0.40	0.45
D	8.35	8.50	8.65
D1	8.80	9.00	9.20
E	23.30	23.50	23.70
E1	8.35	8.50	8.65
E2	4.30	4.50	4.70
E3	17.00 (REF)		
F	4.60 (REF)		
ΦB	120.20° (REF)		

onsemi, **onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and will only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

THE BOARD IS PROVIDED BY ONSEMI TO YOU "AS IS" AND WITHOUT ANY REPRESENTATIONS OR WARRANTIES WHATSOEVER. WITHOUT LIMITING THE FOREGOING, ONSEMI (AND ITS LICENSORS/SUPPLIERS) HEREBY DISCLAIMS ANY AND ALL REPRESENTATIONS AND WARRANTIES IN RELATION TO THE BOARD, ANY MODIFICATIONS, OR THIS AGREEMENT, WHETHER EXPRESS, IMPLIED, STATUTORY OR OTHERWISE, INCLUDING WITHOUT LIMITATION ANY AND ALL REPRESENTATIONS AND WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, TITLE, NON-INFRINGEMENT, AND THOSE ARISING FROM A COURSE OF DEALING, TRADE USAGE, TRADE CUSTOM OR TRADE PRACTICE.

onsemi reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by **onsemi** shall not constitute any representation or warranty by **onsemi**, and no additional obligations or liabilities shall arise from **onsemi** having provided such information or services.

onsemi products including the boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. You agree to indemnify, defend and hold harmless **onsemi**, its directors, officers, employees, representatives, agents, subsidiaries, affiliates, distributors, and assigns, against any and all liabilities, losses, costs, damages, judgments, and expenses, arising out of any claim, demand, investigation, lawsuit, regulatory action or cause of action arising out of or associated with any unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of any products and/or the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

FCC WARNING – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by **onsemi** to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

onsemi does not convey any license under its patent rights nor the rights of others.

LIMITATIONS OF LIABILITY: **onsemi** shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if **onsemi** is advised of the possibility of such damages. In no event shall **onsemi**'s aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

The board is provided to you subject to the license and other terms per **onsemi**'s standard terms and conditions of sale. For more information and documentation, please visit www.onsemi.com.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales