


## **Test Procedure for the NCP1597A Evaluation Board**



**Figure 1: Test Setup** 

The following steps describe the test procedure for all of these boards:

## **Suggested Equipment:**

Current limited DC Power Supply (e.g. AGILENT 6645A)	1pc
DC Volt-Meter able to measure up to 60 V DC (e.g. KEITHLEY 2000)	2pcs
DC Amp-Meter able to measure up to 1 A DC (e.g. KEITHLEY 2000)	1pc
DC Amp-Meter able to measure up to 6 A DC (e.g. FLUKE 89 IV)	1pc
DC Electronic Load (e.g. AGILENT 6060B)	1pc

05/13/10 -1- www.onsemi.com

## **Test Procedure:**

- 1. Connect the test setup as shown in Figure 1.
- 2. Apply an input voltage, V<sub>IN</sub> = 4-5 Vdc (Current Limit must be set to 4A)
- 5. Apply Iout(load) = 0 A
- 4. Check that  $V_{OUT} = 1.7 1.9 \text{ Vdc}$
- 6. Set Iout to desired level 0 A- 2 A
- 7. Check that  $V_{OUT} = 1.7 1.9 \text{ Vdc}$
- 8. Turn off the load
- 9. Turn off Vin
- 10. End of the test