



Test Procedure for the NCV47822 Evaluation Board

The NCV47822 is dual channel High Side Switch with:

- Two adjustable current limits up to 350 mA
- Enable inputs with 3.3 V Logic compatible thresholds
- Diagnostic Features:
 - Short To Battery (STB) and Open Load (OL) in OFF State
 - Internal Components for OFF State Diagnostics
 - Open Collector Flag Output
 - Two Output Voltage Monitoring Outputs (Analog)

For detailed information read the technical specification.

Power supplying of the chip is possible from one or two independent sources. **INPUT1** must be always supplied and **INPUT2** as optional for V_{in2} supply.

Basic procedure of function verification, Diagnostic Functions inactive

1. Power supplying

a. Power supplying from one source

Connect the test setup as is shown in **Figure 1** (See **Table 1** with required equipment). Connect power supply to **INPUT1** connector **J₁** (Power supplying of **INPUT2** is not needed).

- **Hi_F** – Positive Force line
- **Hi_S** – Positive Sense line
- **Lo_F** – Negative Force line
- **Lo_S** – Negative Sense line

Connect V_{in2} pin to **INPUT1** via appropriate position of jumper “ **V_{in2} to IN1 or IN2 connection**”.

b. Power supplying from two sources

Connect the test setup as is shown in **Figure 1** (See **Table 1** with required equipment). Connect two power supplies to **INPUT1** connector **J₁** and to **INPUT2** connector **J₂**, respectively.

- **Hi_F** – Positive Force line
- **Hi_S** – Positive Sense line
- **Lo_F** – Negative Force line
- **Lo_S** – Negative Sense line

Values of input voltages V_{in1} and V_{in2} can be different. This option is suitable for reducing of power dissipation on chip.

Connect V_{in2} pin to **INPUT2** via appropriate position of jumper “ **V_{in2} to IN1 or IN2 connection**”.

2. Current Limit settings

Connect jumpers **J₁₀ – J₁₃** for output current limitation from V_{out1} pin and **J₂₀ – J₂₃** for output current limitation from V_{out2} pin.

- **J_{n0}** – $I_{LIMn0} \sim 14.4$ mA
- **J_{n1}** – $I_{LIMn1} \sim 154.6$ mA
- **J_{n2}** – $I_{LIMn2} \sim 330$ mA
- **J_{n3}** – I_{LIMn3} – R_{CSOn3} positions available for individual current limit setting by resistor from range 2185 Ω to 76.5 k Ω

3. Diagnostic Function (inactive)

Connect **DE** and **CS** inputs to GND via appropriate jumper to disable diagnostic function.



4. Power ON

Set Input Voltage and turn on Power Supply/Supplies.

Enable output of the channel to power the regulated output voltage by connecting the **ENABLE** input to corresponding V_{in} via jumper. Enabling can be performed by external voltage source as well.

5. Load the outputs by resistive loads connected via jumpers:

- $J_5, J_7 - 60 \Omega$ ($I_{out} \sim 220 \text{ mA}$)
- $J_6, J_8 - 1 \text{ k}\Omega$ ($I_{out} \sim 13 \text{ mA}$)

External loads can be used instead build-in resistive loads as well.

6. Monitor Output Feedback Voltages on $V_{out_FB1,2}$ outputs, given according to Equation 1

$$V_{out_FB_n} = \frac{V_{out_n}}{6} \quad (\text{eq. 1})$$

7. Monitor Current Sense Output voltages on appropriate connector. They should be max 2.55 V in steady state. The CSO voltages are proportional to output currents according to Equation 2.

$$V_{CSO_n} = I_{out_n} \left(R_{CSO_n} \times \frac{1}{RATIO} \right) \quad (\text{eq. 2})$$

Where:

- RATIO = 265 for $I_{out1,2}$ from 10 mA to 50 mA
- RATIO = 285 for $I_{out1,2}$ from 50 mA to 350 mA

8. Compare your results with measured results in **Table 2**.

9. Power OFF

Disable output of the channel by connecting the **ENABLE** input to **GND** via jumper. Or Turn OFF external voltage source.



Diagnostic Functions verification

1. Diagnostic Function (active)

Perform steps from 1 to 4 of Basic procedure of function verification and keep both channels disabled.

Short to battery detection (in OFF State)

Set **DE** input to **5 V** via appropriate jumper.

Set **CS** input to **GND**. If **EF** is **LOW**, Short to Battery on **CH1** event occurred.

Set **CS** input to **5 V**. If **EF** is **LOW**, Short to Battery on **CH2** event occurred.

Open Load detection (in OFF State)

Set **DE** input to **5 V** via appropriate jumper.

Enable detection by connecting the **ENABLE** input to corresponding V_{in} via jumper. Enabling can be performed by external voltage source as well.

Set **CS** input to **GND**. If **EF** is **LOW**, Open Load on **CH1** event occurred.

Set **CS** input to **5 V**. If **EF** is **LOW**, Open Load on **CH2** event occurred.

Combine selection $R_{CS01,2}$ and Resistive Loads. You can use external load as well.

Overcurrent detection

Set **DE** input to **GND** via appropriate jumper.

Enable output of the channel to power the regulated output voltage by connecting the **ENABLE** input to corresponding V_{in} via jumper. Enabling can be performed by external voltage source as well.

Set **CS** input to **GND**. If **EF** is **LOW**, Overcurrent on **CH1** occurred and **CSO₁** output is **HIGH**.

Set **CS** input to **5 V**. If **EF** is **LOW**, Overcurrent on **CH2** occurred and **CSO₂** output is **HIGH**.

Combine selection $R_{CS01,2}$ and Resistive Loads. You can use external load as well.

For supplying **DE** and **CS** inputs is used an 5 V LDO regulator U_2 powered from **INPUT1**.




Figure 1. General Test Setup

Table 1: Required Equipment

Equipment	Ranges
Power Supply	0 V – 45 V / 2 A
Load	0 mA – 1 A
V - meter	0 V – 45 V
A - meter	0 mA – 1 A



Table 2: Measured Results

Parameter	Test Conditions	Symbol	Value		Unit
			Nominal	Measured	
Output Voltage	$V_{in} = 13.5\text{ V}, I_{out_n} = 200\text{ mA}, R_{CSO_n} = \text{Short to ground}$	V_{out1}	13.3	13.23	V
		V_{out2}		13.23	
		V_{out_FB1}	2.21	2.22	
		V_{out_FB2}		2.22	
Output Current	$V_{in} = 13.5\text{ V}, V_{out_n} = 12.5\text{ V}, R_{CSO_n} = 47\text{ k}\Omega$	I_{out1}	14.4	16.1	mA
		I_{out2}		15.7	
	$V_{in} = 13.5\text{ V}, V_{out_n} = 12.5\text{ V}, R_{CSO_n} = 4.7\text{ k}\Omega$	I_{out1}	154.6	156	
		I_{out2}		161	
	$V_{in} = 13.5\text{ V}, V_{out_n} = 12.5\text{ V}, R_{CSO_n} = 2.2\text{ k}\Omega$	I_{out1}	330	343	
		I_{out2}		342	
Output Current	$V_{in} = 13.5\text{ V}, V_{out_n} = 0\text{ V}, R_{CSO_n} = 47\text{ k}\Omega$	I_{out1}	14.4	16.7	mA
		I_{out2}		16.7	
	$V_{in} = 13.5\text{ V}, V_{out_n} = 0\text{ V}, R_{CSO_n} = 4.7\text{ k}\Omega$	I_{out1}	154.6	168	
		I_{out2}		167	
	$V_{in} = 13.5\text{ V}, V_{out_n} = 0\text{ V}, R_{CSO_n} = 2.2\text{ k}\Omega$	I_{out1}	347	360	
		I_{out2}		360	




Figure 2. Top side PCB Layout (3 x 3 inch)