



Test Procedure for the NCV7544VTFS5C466GEVB Evaluation Board




Figure 1: Test Setup Configuration

Required Equipment

- Oscilloscope
- Bench Power Supply, current capability min. 10 A, Ampermeter
- Voltmeter (alternatively free oscilloscope channel)
- Two loads (12V motors or power resistors 4R7/25W)
- PC Software for NCV7544 EVB Control
- Micro USB Cable
- NCV7544 Evaluation Board



Test procedure Step 1 (Connect the board):

1. Connect supply
2. Check I_{BAT}
3. Check VCC voltage on IO

Table 1: Desired Results

$I_{BAT} = I_{Bat_NotProgrammed}$
$V(VCC) = VCC$

Test procedure Step 2 (Program the MCU):

1. Connect programmer through JTAG connector
2. Load and flash .hex file
3. Disconnect supply

Test procedure Step 3 (Standalone mode, outputs off):

4. Connect loads (motors or resistors)
5. Turn Pot1 and Pot2 left
6. Connect supply
7. Check I_{BAT}
8. Check V_{CHP} voltage on TP_CHP
9. Check V_{sen} voltage on IO

Table 2: Desired Results

LED1 on
$I_{BAT} = I_{Bat_act}$
$V(TP_CHP) = V_{CHP}$
$V(Vsen1) = V_{sen_off}$ (when duty-cycle 0%)
$V(Vsen2) = V_{sen_off}$ (when duty-cycle 0%)
$V(Vsen1) = V_{sen_on}$ (when duty-cycle 100%)
$V(Vsen2) = V_{sen_on}$ (when duty-cycle 100%)

Test procedure Step 4 (Standalone mode, outputs on):

1. Set SW1-4 up
2. Turn Pot1 and Pot2 right
3. Check OUT1-4 voltage on TP_OUT1-4
4. Check V_{sen} voltage on IO

**Table 3: Desired Results**

LED1 on
$V(\text{HB_OUT1}) = \text{OUTx LS} / \text{OUTx HS}$ (PWM per Pot1)
$V(\text{HB_OUT2}) = \text{OUTx LS} / \text{OUTx HS}$ (PWM per Pot2)
$V(\text{HB_OUT3}) = \text{OUTx LS}$
$V(\text{HB_OUT4}) = \text{OUTx LS}$
$V(\text{Vsen1}) = \text{Vsen_on}$ (when duty-cycle 100%)
$V(\text{Vsen2}) = \text{Vsen_on}$ (when duty-cycle 100%)

Test procedure Step 5 (Standalone mode, outputs on):

1. Set SW1/2 down
2. Turn Pot1 and Pot2 right
3. Check OUT1-4 voltage on TP_OUT1-4
4. Check Vsen voltage on IO

Table 4: Desired Results

$V(\text{HB_OUT1}) = \text{OUTx LS}$
$V(\text{HB_OUT2}) = \text{OUTx LS}$
$V(\text{HB_OUT3}) = \text{OUTx LS} / \text{OUTx HS}$ (PWM per Pot1)
$V(\text{HB_OUT4}) = \text{OUTx LS} / \text{OUTx HS}$ (PWM per Pot2)
$V(\text{Vsen1}) = \text{Vsen_on}$ (when duty-cycle 100%)
$V(\text{Vsen2}) = \text{Vsen_on}$ (when duty-cycle 100%)

Test procedure Step 6 (PC Mode):

1. Connect USB
2. Start NCV7544 Control Software
 - a. Basic Window: Try all controls (Run Forward, Run Backward, Stop, Speed Control)
 - b. Board Window: Check Status bits and Motor Current and Supply

Table 5: Desired Results

LED3 on
OUT1-4 = $\text{OUTx LS} / \text{OUTx HS}$ (PWM duty-cycle per PWM1/2 slider position)
Motors controlled by buttons and PWM generators
Board status bit reflecting board state
Board measured values reflecting board state



DC Characteristics

	MIN	TYP	MAX
VCC	4.9 V	5.0 V	5.1 V
I_{Bat} NotProgrammed			50 mA
I_{Bat_act} (outputs off)		90 mA	110 mA
V_{CHP, Active mode}	Vbat + 8.3 V	Vbat + 8.9 V	Vbat + 9.5 V
OUT_x LS	0 V		0.1 V
OUT_x HS	Vbat – 0.2 V		Vbat
V_{sen_off}			1 mV
V_{sen_on}		0.1 x I(HB_OUT _x)	

PC Software

Window	Parameter	TYP
Board	Supply Voltage	V _{Bat}
Board	I _{sen 1}	I(HB_OUT1/3)
Board	I _{sen 2}	I(HB_OUT2/4)
Board	Status Bits	Normal Mode set