ON Semiconductor

Is Now



To learn more about onsemi[™], please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

VN2410L

Small Signal MOSFET

240 V, 200 mA, N-Channel TO-92

Features

• Pb-Free Packages are Available*

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Drain – Source Voltage	V _{DSS}	240	Vdc
Drain – Gate Voltage	V_{DGR}	240	Vdc
Gate – Source Voltage – Continuous – Non–repetitive (t _p ≤ 50 μs)	V _{GS} V _{GSM}	± 20 ± 40	Vdc Vpk
Continuous Drain Current	I _D	200	mAdc
Pulsed Drain Current	I _{DM}	500	mAdc
Power Dissipation @ T _C = 25°C Derate above 25°C	P _D	350 2.8	mW mW/°C
Operating and Storage Temperature	T _J , T _{stg}	–55 to 150	°C

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	312.5	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/16 inch from case for 10 seconds	T _L	300	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.




ON Semiconductor®


http://onsemi.com

200 mA, 240 V $R_{DS(on)} = 10 \Omega$

N-Channel D O



MARKING DIAGRAM & PIN ASSIGNMENT



A = Assembly Location

Y = Year

WW = Work Week

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

^{*}For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

VN2410L

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}C$ unless otherwise noted)

	Symbol	Min	Max	Unit	
STATIC CHARACTERISTICS				-	•
Drain – Source Breakdown Voltag $(V_{GS} = 0, I_D = 100 \mu A)$	е	V _{(BR)DSS}	240	_	Vdc
Zero Gate Voltage Drain Current $(V_{DS} = 120 \text{ Vdc}, V_{GS} = 0)$ $(V_{DS} = 120 \text{ Vdc}, V_{GS} = 0, T_A = 0)$	I _{DSS}	- -	10 500	μAdc	
Gate- Body Leakage (V _{DS} = 0, V _{GS} = ±15 V)		I _{GSS}	-	±100	nAdc
Gate Threshold Voltage (V _{DS} = V _{GS} , I _D = 1.0 mA)	V _{GS(th)}	0.8	2.0	Vdc	
On-State Drain Current (Note 1) ($V_{GS} = 10 \text{ V}, V_{DS} \ge 2.0 \text{ V}_{DS(on)}$	I _{D(on)}	1.0	_	Adc	
Drain–Source On Resistance (No $(V_{GS} = 2.5 \text{ V}, I_D = 0.1 \text{ A})$ $(V_{GS} = 10 \text{ V}, I_D = 0.5 \text{ A})$	te 1)	r _{DS(on)}	- -	10 10	Ω
Forward Transconductance (Note (V _{DS} = 10 V, I _D = 0.5 A)	9 _{fs}	300	-	mS	
DYNAMIC CHARACTERISTIC	DS .			-	•
Input Capacitance		C _{iss}	-	125	pF
Output Capacitance	$(V_{DS} = 25 \text{ Vdc}, V_{GS} = 0, \\ f = 1.0 \text{ MHz})$	C _{oss}	-	50	pF
Reverse Transfer Capacitance		C _{rss}	-	20	pF
SWITCHING CHARACTERIST	TICS				
Turn-On Time		t _(on)	-	8.0	ns
	(V _{DD} = 60 Vdc, I _D = 0.4 A,	t _(r)	-	8.0	ns
Turn-Off Time	$R_L = 150 \Omega$, $R_G = 25 \Omega$)	t _(off)	-	23	ns
		t _(f)	-	34	ns

^{1.} Pulse Test; Pulse Width $< 300 \mu s$, Duty Cycle $\le 2.0\%$.


ORDERING INFORMATION

Device	Package	Shipping
VN2410L	TO-92	1000 Units / Box
VN2410LG	TO-92 (Pb-Free)	1000 Units / Box
VN2410LZL1	TO-92	2000 Ammo Pack
VN2410LZL1G	TO-92 (Pb-Free)	2000 Ammo Pack

VN2410L

PACKAGE DIMENSIONS

TO-92 CASE 29-11 ISSUE AM



STRAIGHT LEAD **BULK PACK**



NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 CONTROLLING DIMENSION: INCH.
- CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED. LEAD DIMENSION IS UNCONTROLLED IN P AND
- BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.45	5.20
В	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
Н	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500		12.70	
L	0.250		6.35	
N	0.080	0.105	2.04	2.66
P		0.100		2.54
R	0.115		2.93	
٧	0.135		3.43	

STYLE 22:


PIN 1. SOURCE 2. GATE

3. DRAIN

NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M. 1994.
- CONTROLLING DIMENSION: MILLIMETERS.
- 3
- CONTOUR OF PACKAGE BEYOND
 DIMENSION R IS UNCONTROLLED.
 LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM

	MILLIMETERS		
DIM	MIN	MAX	
Α	4.45	5.20	
В	4.32	5.33	
С	3.18	4.19	
D	0.40	0.54	
G	2.40	2.80	
J	0.39	0.50	
K	12.70		
N	2.04	2.66	
P	1.50	4.00	
R	2.93		
٧	3.43		







ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice on semiconductor and war engineer trademarks of semiconductor components industries, Ite (SciLLC) solitate services are injective to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA **Phone**: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Cer Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative