



SCALE 1:1

## **SURMETIC 40, AXIAL LEAD** CASE 017AA ISSUE O

**DATE 23 SEP 2005** 

## NOTES:

- AUTES.

  1. CONTROLLING DIMENSION: INCH
  2. LEAD DIAMETER AND FINISH NOT CONTROLLED WITHIN DIMENSION F.
  3. CATHODE BAND INDICATES POLARITY

	INCHES		MILLIMETERS					
DIM	MIN	MAX	MIN	MAX				
Α	0.330	0.350	8.38	8.89				
В	0.130	0.145	3.30	3.68				
D	0.037	0.043	0.94	1.09				
F		0.050		1.27				
K	1.000	1.250	25.40	31.75				

	<b>→</b>	(O)	<b>~</b>	
	_		- D F┐	K
	<b>↓</b>		<del>\</del>	A
K	F			

DOCUMENT NUMBER:	98AON21393D	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	SURMETIC 40, AXIAL LEA	D	PAGE 1 OF 1

onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.