semi

DATE 26 OCT 2021

MILLIMETERS

14.18(REF)

NOM.

17.30

12.00

4.70

16.70

1.66

0.80

93.00

104.75

82.00

107.20

47.00

44.40

39.00

5.50

10.70

2.00

Х

11.40

13.90

31.45

33.95

36.95

42.65

53.40

59.10

62.10

64.60

0.00

0.00

70.70

PIN POSITION

MAX.

17.70

12.30

5.00

17.00

0.85

93.10

105.05

82.20

107.50

47.30

44.70

39.20

10.80

2.20

Υ

22.00

22.00

22.00

22.00

23.70

22.00

22.00

23.70

22.00

22.00

34.40

36.90

36.90

5.60

1.71

MIN

16.90

11.70

4.40

16.40

1.61

0.75

92.90

104.45

81.80

106.90

46.70

44.10

38.80

5.40

10.60

1.80

PIN

23

24

25

26

27

28

29

30

31

32

33

34

44

4

5

6

7

8

9

10

11

12

22

2.80

5.60

5.00

20.00

20.00

25.35

25.35

39.75

40.35

9.20

9.20

12.00

10.00

12.50


10.00

12.50

9.20

12.00

8.40 23.70



NOTES:


- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009
- 2. CONTROLLING DIMENSION : MILLIMETERS
- 3. DIMENSIONS b AND b1 APPLY TO THE PLATED TERMINALS AND ARE MEASURED AT DIMENSION A1
- 4. PIN POSITION TOLERANCE IS ± 0.4mm
- 5. PACKAGE MARKING IS LOCATED AS SHOWN ON THE SIDE OPPOSITE THE PACKAGE ORIENTATION FEATURES

| 13 | 42.55 | 9.20 | 35 | 20.00 | 34.40 |
|----|-------|-------|----|-------|-------|
| 14 | 45.35 | 9.20 | 36 | 20.00 | 36.90 |
| 15 | 50.70 | 9.20 | 37 | 25.35 | 34.40 |
| 16 | 53.50 | 9.20 | 38 | 25.35 | 36.90 |
| 17 | 56.30 | 9.20 | 39 | 45.35 | 34.40 |
| 18 | 55.70 | 12.00 | 40 | 45.35 | 36.90 |
| 19 | 70.70 | 10.00 | 41 | 50.70 | 34.40 |
| 20 | 70.70 | 12.50 | 42 | 50.70 | 36.90 |
| 21 | 2.70 | 22.00 | 43 | 70.70 | 34.40 |
| | | | | | |

| DOCUMENT NUMBER: | 98AON39004H | Electronic versions are uncontrolled except when accessed directly fron Printed versions are uncontrolled except when stamped "CONTROLLED | |
|--------------------------------|-------------|--|-------------|
| DESCRIPTION: PIM44, 93x47 (PRE | | | PAGE 1 OF 2 |

onsemi and OnSemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make charges without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products herein. special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

DATE 26 OCT 2021



XXXXX = Specific Device Code AT = Assembly & Test Site Code YYWW = Year and Work Week Code *This information is generic. Please refer to device data sheet for actual part marking. Pb–Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

| DOCUMENT NUMBER: | 98AON39004H | Electronic versions are uncontrolled except when accessed directly from Printed versions are uncontrolled except when stamped "CONTROLLED | |
|------------------|--------------------------|--|-------------|
| DESCRIPTION: | PIM44, 93x47 (PRESS FIT) | | PAGE 2 OF 2 |

onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product rights for circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi loss not convey any license under its patent rights nor the rights of others.