



DPAK-4 6.50x7.30x1.50, 2.30P
CASE 369AM
ISSUE A

DATE 06 NOV 2025



NOTES:

1. DIMENSIONING AND TOLERANCING AS PER ASME-Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. PIN 2 IS IDLE PIN WITH ELECTRICAL DESIGNATION ONLY CARRIED.



RECOMMENDED MOUNTING FOOTPRINT

*For additional information on our Pb-free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MILLIMETERS			
DIM	MIN	NOM	MAX
A	1.35	1.50	1.65
A1	0.02	0.10	0.18
b	0.45	0.60	0.75
b1	0.65	0.80	0.95
c	0.30	0.40	0.50
D	6.50 BSC		
D1	4.60 REF		
D2	2.60 REF		
D3	0.40 REF		
E	9.30	9.50	9.70
E1	7.30 BSC		
E2	6.05 REF		
E3	4.60 REF		
e	2.30 BSC		
e1	4.60 BSC		
L	0.55	0.70	0.85
L1	1.55	1.70	1.85
L2	0.35	0.50	0.65
L3	0.35	0.50	0.65
TOLERANCE FORM & POSITION			
aaa	0.15		
bbb	0.20		
eee	0.10		

DOCUMENT NUMBER:	98AON67243E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	DPAK-4 6.50x7.30x1.50, 2.30P	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.