

ON Semiconductor®

STR-DMS-NCV7694-GEVK Driver Monitoring System

Strata Enabled STR-DMS-NCV7694-GEVK Driver Monitoring System User Guide



Contents

1. INTRODUCTION	
Features	
2. USER GUIDE	
Connection of the modules when PWM flash taken from STR-ASSISTED-RSL10-GEVB	
Connection of the modules when PWM flash taken from Image Sensor	ļ

1. Introduction

STR-DMS-NCV7694-GEVK provides an easy to use evaluation platform within the Strata Development Environment for the NCV7694 Safety Controller for Infra-Red LED Illumination to Complement the Image Sensor for Automotive Applications from ON Semiconductor. Strata gives the developer access to any collateral one may need, including datasheets, BOMs and schematics, as well as providing a user interface for testing the performance of the NCV7694. This document will provide instructions on how to use the evaluation board.

Parameter	Description
Vin	9.5 V – 28 V (minimum Vin depends on the current through LEDs)
Size	Size: 21 mm x 21 mm x 12.7mm
Energy	40 mJ energy in SOA (more details in the following text)
	Tank capacitor: $4 \times T598D157M016ATE065$ automotive grade (optimized for 21×21 mm form factor)
Illumination	1250mW/sr (IR LED: Osram SFH4725S)
Frequency	60 Hz (aligned with the 60fps from image sensor), FW of RSL10 & GUI set to 62Hz
Voltage LEDs	8.6 V max. (2 LEDs in series @ 5 A). Adjustable at DC-DC output. 4.8 V – 10 V
Current pulses	Short: 5 A peak for 500us / Long: 1 A for 4ms. Adjustable current: 0.7 - 5 A
Adjustable parameters	On Strata: IR LED current, DC-DC output voltage, PWM signal (FLASH emulator for evaluation w/o camera)
	On Hardware: Input for FLASH (from camera or from Strata (PWM))
	On Image sensor (DevWare): FLASH signal (freq. and TON)
Strata	Adjustable parameters. Monitor ILED and DC/DC VOUT (calibrated).
	Diagnostic pin from NCV7694 LED driver.
Compatible Image Sensor Modules	AR0144, IVEC-0144 primarly (optimized LED FOV DMS). Possible with other image sensors AR0234, AR0239, AR0820, that use same FLASH mechanism.

2. USER GUIDE

This section provides step-by-step manual on how to use the STR-DMS-NCV7694-GEVK. In general it consist of three boards:

- STR-DMS-NCV7694-GEVB (GazeT housing IR LED board)
- STR-DMS-CONTROL-GEVB (Control board to adjust Voltage and current on IR LEDs)
- STR-ASSISTED-RSL10-GEVB (RSL10 SoC based Strata interface module)

Connection of the modules when PWM flash taken from STR-ASSISTED-RSL10-GEV B

The STR-DMS-NCV7694-ŒVK is delivered as platform that can operate as standalone evaluation kit. Using the Strata interface and control board, one can adjust:

- i. the Ton time (PWM flash) with fixed frequency 62Hz
- ii. Output voltage of DCDC converter NCV890204
- iii. LED current amplitude I_LED

Note: When operating from PWM flash out of Strata module, make sure that jumper CON4 is plugged




Fig. 1 CON4 jumper to be plugged when PWM flash signal taken from Strata Control board

STR-DMS-NCV7694-GEVK consists of two connectors:

i. Three - pin connector for Supply Voltage, Ground and PWM flash signal from Image Sensor

ii. Six – pin connector for flat FPC cable that provides control voltage for I_LED and Vout_DCDC adjustment, PWM from Strata together with Diagnostic pin output of NCV7694.




Fig. 2: 3-pin and 6-pin connectors on the back side of STR-DMS-NCV7694-GEVB LED module

Single Control board STR-DMS-CONTROL-GEVB can service up to three STR-DMS-NCV7694-GEVB GazeT IR LED modules. Here is the procedure on hardware connections of the system:

1. Connect the bundled 3-pin connector and 6-pin FPC connector to STR-DMS-NCV7694-GEVB per Fig.3. Please make sure that Blue part of the 6-pin FPC is looking upwards as depicted and LED module's hole for standoff/tripod is from housing's bottom side.




Fig. 3: 3-pin and 6-pin cable connections to IR LED module (STR-DMS-NCV7694-GEVB)

2. Connect the other part of 6-pin FPC cable into control board STR-DMS-CONTROL-GEVB as shown in Fig.4. Blue part of the FPC cable must go outside of the control board. User can control up to three GazeT IR LED driver modules over 6-pin FPC cables. Each module will have the same V_out DCDC and I_LED current and PWM flash signal.




Fig. 4: connection of the 6-pin FPC cable from GazeT LED driver module (STR-DMS-NCV7694-GEVB) into Control board (STR-DMS-CONTROL-GEVB)

3. Make sure you have available Regulated Constant Voltage Power supply with current capability up to 5A. Connect the external power supply and polarity per Fig.5 and set voltage to 13V (current limitation 5A min). Turn the power supply ON. With PWM generated by Strata interface, leave PWM cable from 3-pin connector open (unconnected). You can connect and simultaneously control up to three STR-DMS-NCV7694-GEVB over FPC cable to single STR-DMS-CONTROL-GEVB board. Supply wires should be connected together to Regulated Voltage Source (all minus poles and all plus poles).




Fig. 5: Connection of the external power supply

4. After the power supply is ON, connect the Mini USB cable to STR-DMS-CONTROL-GEVB and to computer

5. Once the system is fully powered, user can manipulate and test the performance of the system from Strata / Serial Console Interface (SCI).

The current DMS allows variation (i.e. variables) of LED current, NCV890204 output voltage and T_ON period (i.e. ON time of PWM flash pulse) by means of the STR-DMS-CONTROL-GEVB and STR-ASSIST-RS10-GEVB. There are two SW took (available within Strata SW tools) for adjusting the above mentioned parameters: i) Serial Control Interface (SCI); ii) Strata Developer Studio GUI.

SCI:

- Commands sent via command line
- Accept any "floating value" for particular variable from command line, thus easy to bring the DMS into malfunction if user does not know what he/she is doing
- Allows user to work with variable values outside the SOA area in the Strata GUI
- Intended rather for development and/or "skilled" users
- Takes more time (sending commands) to change variables compared to Strata GUI tool
- Cannot run simultaneously with Strata GUI (to operate via GUI, close the SCI first)
- Command examples:

I_LED (LED DRIVER NCV7694)

```
"cmd": "set_pwm1",
"payload": {
    "status": "bool",
    "current": "double"
}
```

```
}
```

{

{

VOUT (DCDC CONVERTER NCV890204)

```
"cmd": "set_pwm2",
"payload": {
    "status": "bool",
    "voltage": "double"
}
```

```
}
```

FLASH_PWM(62Hz)

```
{
    "cmd": "set_pwm3",
    "payload": {
        "status": "bool",
        "on_time": "double"
    }
}
```

Examples:

```
1. turn ON I_LED to 0.7A
{
        "cmd": "set_pwml",
        "payload": {
            "status": true,
            "current": 0.7
        }
    }
```

2. turn OFF I_LED


ł

```
"cmd": "set_pwm1",
"payload": {
    "status": false,
    "current": 0.7
}
```

Strata GUI:

}

- Available within Strata Development Studio
- Developed to make the DMS more stable, user friendly to control and operate within safety limits
- Operation restricted to "Safety Operation Area (SOA)" to reduce potential risk of damage or the DMS malfunction. LED current levels below 0.7A are removed from operation area.
- Initial variables: LED current=0.7A; T_ON PWM FLASH time=0ms; NCV890204 output voltage=10.0V
- Cannot run simultaneously with the SCI






Fig. 6: Control panel for Flash PWM, VOUT (DCDC converter) and I_LED. Safety operating area included.

SOA area is implemented in the Strata GUI. Accepted at the conditions: NCV890204 VOUT=10.0V; f_PWM_flash=62Hz. LED current levels below 0.7A are unavailable.

Thresholds:

- the IR LED (MPN: SFH 4725S) maximum specified LED current: 5A
- R_{ETL} value: 15kOhm -> maximum T_ON time 6ms per the NCV7694 specs -> thus 5ms maximum T_ON time accepted

Powerlaw: P=*E*/*t*=*U***I*

- SOA is accepted: 40mJ
- 40mJ=10V*I*t
- *t involves duty cycle (i.e. T_ON time)*
- thus: 40mC=I_LED*T_ON-> SOA envelope

How to start the DMS (example1): 1. set the LED current and turn the LED current button on. 2. Set the T_ON time and turn the PWM FLASH (T_ON time) on.

How to start the DMS (example2): 1. set the T_ON time and turn the T_ON time button on (i.e. PWM FLASH). 2. set the LED current and turn the LED current button on.

The NCV890204 output voltage variable can be adjusted afterwards the DMS runs (T_ON time is ON) with default value 10.0V. This precaution is done to prevent the DMS malfunction just after it starts due to insufficient voltage is applied at the particular working point.

If the working point is out of the SOA area that is the T_ON time is set too high in the example1, the GUI automatically adjust the previous variable (i.e. LED current in the example1 above) to stay within the SOA. In such case the working point sits onto the dashed orange curve (the SOA envelope). Consequently any change of the T_ON time or the LED current exceeding the SOA adjusts the working point position onto the SOA envelope.

$\label{eq:connection} \textbf{Connection of the modules when PWM flash taken from Image Sensor}$

 $The \, STR-DMS-NCV7694-G\!EVK \ \ as \ platform \ can \ operate \ with \ Image \ sensor. \ Using \ the \ Strata \ interface \ and \ control \ board, \ one \ can \ adjust:$

- i. Output voltage of DCDC converter NCV890204
- ii. LED current amplitude I_LED

Image Sensor will serve for PWM Flash generation set out of the DevWare system.

Note: When operating with Image sensor, PWM flash out of Strata module is not used, make sure that jumper CON4 is unplugged




Fig. 7 CON4 jumper to be un-plugged when PWM flash signal taken from Image Sensor

Please follow the connection steps as outlined in previous chapter. For PWM_Flash signal – this is generated directly from camera module (and not from Strata control board, hence CON4 jumper not assembled).

Make sure you have available Regulated Constant Voltage Power supply with current capability up to 10A (in case you connect more modules). Connect up to two or three STR-DMS-NCV7694-GEVB GazeT modules to the GazeT image sensor module over

three pin cabling as shown on Fig. 8. Image sensor module consists of supply connector that user hooks up to the external power supply. Set the voltage to 13V (current limitation 5A). Make sure you have the setup completed per below with 6-pin FPC cables interconnection between GazeT LED modules and Control board, IS to Deserializer – Demo3. Turn the power supply ON.





Fig. 8: Connection of the external power supply and Control board to GazeT LED and IS modules together with control board and Strata interface board

After the power supply is ON, connect the Mini USB cable to STR-DMS-CONTROL-GEVB and to computer

Once the system is fully powered, user can manipulate and test the performance of the system from Strata / Serial Console Interface (SCI) together with DevWare. The interface is the same except PWM_flash Signal generated out of the Image Sensor over three pin connector.

Important note: DevWare generates PWM flash signal directly from Image Sensor. Strata Control GUI / SCI serves only for DCDC converter Voltage and I_LED current settings. Don't use Flash PWM Signal.





Gaze T NCV7694 LED driver modules

Gaze T AR0144 Image Sensor




Fig. 9: Example of well exposed image, 3 LEDs connected, $Ton \approx 500us$, I_LED = 4.5 A Background objects also illuminated apart from the subject

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is as such not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and should as such only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

The board is delivered "AS IS" and without warranty of any kind including, but not limited to, that the board is production-worthy, that the functions contained in the board will meet your requirements, or that the operation of the board will be uninterrupted or error free. ON Semiconductor expressly disclaims all warranties, express, implied or otherwise, including without limitation, warranties of fitness for a particular purpose and non-infringement of intellectual property rights.

ON Semiconductor reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by ON Semiconductor shall not constitute any representation or warranty by ON Semiconductor, and no additional obligations or liabilities shall arise from ON Semiconductor having provided such information or services.

The boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. Should you purchase or use the board for any such unintended or unauthorized application, you shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

FCC WARNING – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by ON Semiconductor to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

ON Semiconductor does not convey any license under its patent rights nor the rights of others.

LIMITATIONS OF LIABILITY: ON Semiconductor shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if ON Semiconductor is advised of the possibility of such damages. In no event shall ON Semiconductor's aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

PUBLICATION ORDERING INFORMATION

LITERATURE FULLFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA

Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 ON Semiconductor Website:

Order Literature: https://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative