



# Test Procedure for the NCP110AMX180TBGEVB Evaluation Board

## 1. QUIESCENT CURRENT




Figure 1: Test configuration for measurement  $I_Q$ , Quiescent Current

- 1. Connect circuit as shown figure on 1
- 2. Apply voltage at  $V_{\text{Input.}}$  Default test  $V_{\text{input}}$  is  $V_{\text{out\_nom}} + 0.3$  V or 1.1 V whichever is greater
- 3. Value shown  $\mu$ A meter is measured quiescent current.
- 4. Measurement is finished. Disconnect supply voltage.

\*Note – Be carefully if any device is connected on output, because leakage current can affect measurement accuracy.





#### 2. LOAD REGULATION




Figure 2: Test configuration for measurement REG<sub>LOAD</sub>, Load Regulation

- 1. Connect circuit as shown figure on 2
- 2. Apply voltage at V<sub>Input</sub>. Default test V<sub>input</sub> is V<sub>out\_nom</sub>+0.3 V or 1.1 V whichever is greater
- 3. Set minimal required current I<sub>1</sub>, e.g. 1 mA, and switch load ON.
- 4. Note the value  $V_1$  from voltmeter Vo.
- 5. Switch load OFF and set maximal required current  $I_2$ , e.g. 200 mA and switch load ON.
- 6. Note the value  $V_2$  from voltmeter Vo.
- 7. Load regulation is obtained via following formula: REG<sub>LOAD</sub>=(V<sub>1</sub>-V<sub>2</sub>), [V]
- 8. Measurement is finished. Disconnect supply voltage.





#### 3. LINE REGULATION




Figure 3: Test configuration for measurement REG<sub>LINE</sub>, Line Regulation

- 1. Connect circuit as shown on figure 3
- 2. Set load to the required current e.g. 1 mA
- 3. Set minimal input voltage  $V_{11}$ ,  $V_{OUT_NOM}$ +0.3V or 1.1 V whichever is greater
- 4. Note the value  $V_{11}$  and  $V_{01}$ .
- 5. Set maximal input voltage  $V_{12} = 5.5 V$
- 6. Note the value  $V_{12}$  and  $V_{02}$ .
- 7. Load regulation is obtained via following formula: REG<sub>LINE</sub>=(V<sub>01</sub>-V<sub>02</sub>)/(V<sub>11</sub>-V<sub>12</sub>), [V/V]
- 8. Measurement is finished. Disconnect supply voltage.





### 4. ENABLE START-UP




Figure 4: Test configuration for measurement enables response

- 1. Connect circuit as shown on figure 4
- 2. Set generator to SQUARE PULSE,  $0.9 \le AMPLITUDE \le V_{IN}$ , FREQUENCY=10Hz, DUTY=10%
- 3. Apply voltage at  $V_{Input.}$  Default test  $V_{input}$  is  $V_{out_nom}$ +0.3 V or 1.1 V whichever is greater
- 4. Set required  $I_{OUT}$ , e.g. 10 mA
- 5. Connect oscilloscope to EN signal and VOUTPUT.
- 6. Watch enable response of the regulator after asserting EN pin.
- 7. Measurement is finished. Disconnect supply voltage.