

Test Procedure for the NCP137AFCTADJT2G Demo Board




Figure 1: Test Setup

Test Procedure

1. Connect the test setup as shown in Figure 1.
2. Apply supply voltage $V_{bias} = 5.5\text{ V}$
3. Apply supply voltage $V_{in} = 3.5\text{ V}$
4. Apply $I_{out} = 10\text{ mA}$ load.
5. Set the desired V_{out} in range from 0.5 V to 3.0 V by trimer ADJ .
6. Set the supply voltage V_{in} to $V_{out} + 0.5\text{ V}$
7. Increase I_{out} load current to 0.7 A
8. Check the Output Voltage V_{out} is $V_{out} @ 10\text{ mA } +/- 1\%$
9. Power down the load
10. Power down V_{in} and V_{bias} supply
11. End of test