

## SECO-HVDCDC1362-40W-GEVB Testing procedure

This document describes functional test of SECO-HVDCDC1362-40W-GEVB evaluation board.

Equipment needed to run functional test:

- Regulated DC output high voltage power supply up to 300VDC and minimum 50W (NOTE: AC output is NOT allowed)
- DC Electronic load with minimum 20VDC and 50W loading

## Procedure:

 Connect the DC output of the HV regulated source into the input terminals with correct polarity as depicted below. On the output connector, connect DC electronic load with correct polarity as shown below.



- 2. Turn on HV DC source and DC electronic load. Test is the following:
  - Set 250VDC on the input terminals and no loading out of the DC electronic load -> observe ~15Vout on the DC electronic load display
  - > Set **250VDC** on the input terminals and adjust *DC electronic load* to **2.7A** of load current-> observe ~15Vout on the DC electronic load display
  - Set 300VDC on the input terminals and no loading out of the DC electronic load -> observe ~15Vout on the DC electronic load display
  - > Set **300VDC** on the input terminals and adjust *DC electronic load* to **2.7A** of load current-> observe ~15Vout on the DC electronic load display

May.2021 Rev. B