

<complex-block></complex-block>	hay and a same	CA	<b>3x47 (PRESS FIT</b> ASE 180HG ISSUE O	Ŋ			DATE	10 NO\	√ 2021
V + V + V + V + V + V + V + V + V + V +				1. DIMENSIONIN 2. CONTROLLING 3. DIMENSIONS I ARE MEASURE 4. PIN POSITION 5. PACKAGE MAI	DIMENSION : AND b1 APPL D AT DIMENSI TOLERANCE IS RKING IS LOCA	MILLIMETE _Y TO THE F ON A1 +± 0.4mm .TED AS SHO RIENTATION	RS PLATED TERM DWN ON THI I FEATURES	MINALS AND	
	ØP2 -	-D		<u>┎╴╢─┬╶</u> ╽	A A1 A2 A3	16.90 14.1 11.70 4.40	17.30 18(REF) 12.00 4.70	17.70 12.30 5.00	
$ \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\$		······································			b b1 D D1 D2	1.61 0.75 92.90 104.45 81.80	1.66 0.80 93.00 104.75 82.00	1.71 0.85 93.10 105.05 82.20	
93.00 90.00 90.00 90.00 90.00 90.00 90.00 90.00 90.00 90.00 90.00 18.45 90.00 18.45 90.00 18.45 90.00 18.45 90.00 18.45 90.00 18.45 90.00 18.45 90.00 10	PACKAGE ORIENTATION FEATURE			A1	E E1 E2 P P1	46.70 44.10 38.80 5.40 10.60	47.00 44.40 39.00 5.50 10.70	47.30 44.70 39.20 5.60 10.80	
$\frac{1}{39,00} + \frac{10000}{9,00} + \frac{10000}{9,00} + \frac{10000}{9,000} + \frac{10000}{33} + \frac{10000}{33} + \frac{10000}{34} + \frac{100000}{34} + \frac{10000000}{34} + \frac{1000000}{34} + \frac{1000000}{34} + \frac{10000000}{34} + \frac{10000000}{34} + \frac{1000000000000}{34} + 1000000000000000000000000000000000000$	ł	82.00		PIN POSITI       PIN     X       1     0.00       2     0.00	ON Y 0.00 4.00	P <b>I</b> N 27 28	PIN POSI X 62.50 65.30	10N Y 0.00 0.00	
Ø2.50 (x4)	0.00			5     6.00       6     6.00       7     9.00       8     9.00	0.00 4.00 0.00 4.00	31 32 33 34	13.70 16.70 19.70 23.20	19.80 19.80 19.80 19.80	
17   38.00   2.80   43   63.50   31.30     18   38.00   5.60   44   63.50   34.10     19   41.30   0.00   45   63.50   31.30     20   41.30   2.80   46   67.20   31.30     21   41.30   5.60   47   67.20   34.10     22   54.10   0.00   48   67.20   34.10     23   54.10   3.30   49   70.90   31.30     24   56.90   0.00   50   70.90   34.10     25   56.60   3.30   51   70.90   36.90     26   59.70   0.00   50   70.90   36.90		RECOMMENDED	PLATED	11     26.90       12     29.90       13     29.90       14     32.90	3.30 0.00 3.30 0.00	37 38 39 40	38.00 54.10 59.60 61.70	26.00 14.70 24.60 27.50	
23   54.10   3.30   49   70.90   31.30     24   56.90   0.00   50   70.90   34.10     25   56.60   3.30   51   70.90   36.90     26   59.70   0.00   50   70.90   36.90				17     38.00       18     38.00       19     41.30       20     41.30	2.80 5.60 0.00 2.80	43 44 45 46	63.50 63.50 63.50 67.20	31.30 34.10 36.90 31.30	
			Flectronic versions are u	22     54.10       23     54.10       24     56.90       25     56.60       26     59.70	0.00 3.30 0.00 3.30 0.00	48 49 50 51	67.20 70.90 70.90 70.90	36.90 31.30 34.10 36.90	Repository
DOCUMENT NUMBER:   98AON39438H   Electronic versions are uncontrolled except when accessed directly from the Document Repositive Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.     DESCRIPTION:   PIM51 93X47 (PRESS FIT)   PAGE 1 OF	DOCUMENT NUMBER: DESCRIPTION:	98AON39438H PIM51 93X47 (PRESS FIT)	Printed versions are unco	ontrolled except when	stamped "C		LLED COI	PY" in red.	

onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

## PIM51, 93x47 (PRESS FIT) CASE 180HG ISSUE O

## DATE 08 NOV 2021

GENERIC MARKING DIAGRAM*	
XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX	
FRONTSIDE MARKING	
2D CODE	
BACKSIDE MARKING	
XXXXX = Specific Device Code	*

AT = Assembly & Test Site Code YYWW = Year and Work Week Code This information is generic. Please refer to device data sheet for actual part marking. Pb–Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON39438H	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.			
DESCRIPTION:	PIM51 93X47 (PRESS FIT)		PAGE 2 OF 2		

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.