## Onsemí

**System Solution Guide - Preview** 

1110

## Drone





## **Table of Contents**

#### **Overview** Application

Market Information & Trend The Evolution of Drone Technology

#### **System Implementation**

The Diverse Applications of Drones	05
Drone Classifications	06
Autonomous Navigation Systems for Drones	07
Drone Sensing Systems	08

#### **Solution Overview**

**>>>** 

Onsemi

Block Diagram – Industrial Drone	09
Hyperlux SG – Global Shutter Image Sensor Family	10
Hyperlux LP - Image Sensor Family	11
Hyperlux LH - Image Sensor Family	13
CQD SWIR – Best Depth Sensing Technologies for Navigation Systems	14
Key Parameters Comparison of Hyperlux Image Sensor Families	14
SWIR - Extended Vision for Drone Navigation Systems	15
SWIR - ACUROS	16
Smart iToF Global Shutter Depth Sensors	17
Smart iToF Global Shutter Depth Sensors - AF0130 & AF0131	18
Smart & Mobile Robotics	19
Battery Powered Tools	20
Guide	



Register now to unlock all System Solution Guides

System Solution Guide - Preview

Drone

Get Latest Version

03

04

## **Full Guide Preview**

**Get Latest** Version







Station Denting
Name of Annal Solar Lands
Their Television
Long the set of the control of the set of th
tall integrated part strategies require a large state and
AND ADDRESS OF ADDRES
Sanation interest and any series
ngana it
Maria California
onsemi mane ( manes ) we

11



16





and the of the fine with other his same t

ONSI

12







-

Ξ

3









20.07

or

on

14

1

19

1123

-----

THE

9





10







## **ONSEMI**

## **Block Diagram - Drone**

Get Latest Version

#### **Block Diagram - Drone**

The block diagram below illustrates an industrial drone solution featuring recommended products from **onsemi**. This solution integrates multiple image sensing technologies, utilizing **onsemi's** Global and Rolling Shutter sensor families. Most of the functional block devices, including power management, communication, and many more, can be sourced from **onsemi's** comprehensive range of solutions.



**Use our Interactive Block Diagrams Tool** 

## Open IBD Tool

## onsemi

## **Solution Overview**

Get Latest Version

#### **Drone Sensing Systems**

When selecting image sensors for drones, it's crucial to consider the specific conditions and requirements of your application. Typically, a system might use six to eight sensors, but up to twelve sensors are not uncommon. Global shutter sensors, which capture the entire image simultaneously, are ideal for moving objects as they prevent distortions and motion artifacts. This is particularly important for applications like mapping, surveying, and industrial inspections, where precision is crucial. By capturing the entire frame simultaneously, global shutters prevent distortions such as the "jello effect" and motion blur, which are common with rolling shutters.

- Low power image sensors are beneficial due to their low power consumption and the ability to be placed in multiple locations, providing a comprehensive view of the scene.
- High Dynamic Range (HDR) cameras are essential in drone technology for capturing detailed and accurate images in varying lighting conditions. They balance exposure in both bright and dark areas, ensuring no details are lost in challenging lighting conditions.
- **High Resolution:** 20-megapixel Hyperlux AR2020 will further enhance these capabilities, allowing for even more detailed and accurate inspections and surveys
- Extended Vision: Seeing Beyond the Visible with Swir

#### Hyperlux SG Family Global Shutter Technology





Hyperlux LP Low Power Consumption



Hyperlux LH High Dynamic Range

onsemi

System Solution Guide - Preview

## **Solution Overview**

Get Latest Version

#### Hyperlux SG – Global Shutter Image Sensor Family

The Hyperlux SG global shutter image sensor family from **onsemi** captures high-speed, distortion-free images, making it ideal for barcode scanning, machine vision, and robotics. Models like ARX383, AR0145, and AR0235 offer up to 120 fps, programmable regions of interest, auto-exposure, and low-power operation. These sensors are designed to deliver exceptional image quality even in challenging lighting conditions. Their compact form factor makes them suitable for a wide range of industrial applications.



#### Hyperlux LP - Image Sensor Family

The **onsemi** Hyperlux LP image sensor family is designed for a range of applications, including the AR2020, AR0544, and AR0830. These sensors offer exceptionally low power consumption, ensuring devices run longer and more efficiently. With the innovative wake-on-motion feature, your device can stay in a low-power state until motion is detected, saving even more energy. Additionally, the sensors provide excellent performance in low-light and NIR wavelengths. Moreover, the Smart ROI (Region of Interest) in the AR2020 sensor allows for intelligent focus on specific areas, enhancing performance and precision.



#### Hyperlux LH - Image Sensor Family

The onsemi Hyperlux LH image sensor family is designed for a range of applications, including the AR0822 and AR0246. These sensors achieve stunning 4K video quality with enhanced NIR and eHDR capabilities, ensuring exceptional image performance in various lighting conditions. With industry-leading 120dB ultrahigh dynamic range (HDR), these sensors provide clear and accurate images even in challenging environments. The compact design of the Hyperlux LH sensors makes them ideal for integration into space-constrained systems, enhancing both performance and efficiency.

The sensors are designed with a 2.0  $\mu$ m pixel size, contributing to their high sensitivity and image clarity. Furthermore, these sensors are built for low power consumption, making them ideal for battery-operated devices and reducing overall energy costs in systems.





## **Solution Overview**

Get Latest Version

#### **SWIR - Extended View**

The **onsemi** SWIR ACUROS series offers cutting-edge short-wave infrared (SWIR) cameras and image sensors, meticulously engineered for high-performance imaging applications. These sensors exhibit remarkable spectral range ranging from 400 nm to 1700 nm (SWIR) and 400-2100 nm (eSWIR), ensuring exceptional depth and clarity across diverse lighting conditions. Equipped with a global shutter and a 15µm pixel size, the ACUROS cameras deliver high-resolution, high-dynamic-range imaging with minimal noise, making them ideal for capturing precise and detailed images.

These advanced capabilities make the ACUROS cameras particularly well-suited for applications such as imaging through opaque materials like plastic, material sorting and recycling, and moisture content analysis (water absorption at 1450 nm). The CQD SWIR advantage allows these cameras to 'see through' many opaque materials, providing higher resolution sensors for larger inspection areas and supporting high frame rates for dynamic imaging tasks.

This combination of high sensitivity, robust performance, and superior image quality positions the ACUROS series as a reliable choice for professionals seeking top-tier imaging solutions in various demanding applications.



#### Smart iToF Global Shutter Depth Sensors - AF0130 & AF0131

**onsemi** AF0130 and AF0131 Smart Indirect Time of Flight (iToF) 1.2 MP CMOS sensors are designed for exceptional depth sensing and imaging. These sensors feature a 1/3.2-inch optical format and BSI CMOS global shutter technology, including 1.2 MP CMOS Smart iToF Sensor with Advanced 3.5  $\mu$ m Pixel Stacked BSI Technology, superior low-light and ambient-light performance, enhanced NIR response at 850 nm and 940 nm wavelength (QE > 40%), dual laser operation for increased depth range, and laser eye safety monitoring.

## Key features of Hyperlux ID depth iToF sensors include :

- High Depth Accuracy: Provides accurate distance measurements, crucial for tasks requiring precise 3D mapping and object detection.
- High Frame Rates: Capable of capturing fastmoving objects (60 – 100 fps), ensuring reliable performance in dynamic environments.
- Low Power Consumption: Optimized for energy efficiency (400 mW in Mode2.2 (100 MHz) @ 30 fps and 0.35 ms exposure 600 mW in Mode3.2 (100+120 MHz) @ 30 fps and 0.35 ms exposure), making them suitable for battery-powered and multi-sensor systems.

Onsemi





Get Latest Version

# onsemi

## Intelligent Technology. Better Future.

#### **Register now to unlock all System Solution Guides and get aditional exclusive benefits!**

- Utilize Elite Power Simulator & other developer tools.
- Watch exclusive webinars and seminars.

>**>>>** 

Open full System Solution Guide

onsemi.com

{ { {

Onsemi

Drone

System Solution Guide

onsemi, the onsemi logo, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.