Onsemí

System Solution Guide - Preview Al Data Center



onsemi.com

Table of Contents

onsemi

	Get Latest Version
Overview	
Applications	03
System Purpose	04
Market Information & Trend	05
System Implementation	
Al Data Center Main Architecture	07
Server Rack Structure	08
System Description	
AI Datacenter System Overview, AC-DC Conversion	09
Hot-swap and IBC, Multiphase and PoL DC-DC Power Distribution	10
Solution Overview	
Block Diagram - Al Datacenter	11
Topologies	12
Reference Design for AI Server PSU	13
Silicon Carbide (SiC)	14
T10 LV-MV SI MOSFET	16
AC-DC Controller	1/
Gan Driver and IGan	18
Multi-phase Controller & Smart Power Stage Module	19
POL BUCK Regulator 8	20
	01
Recommended Produ	21
Onsem l	
Register now to unlock all System Solution Guides	

System Solution Guide - Preview

Full Guide Preview



16

Onsemi

Get Latest

Block Diagram - Al Data Center

Get Latest Version

Block Diagram - Al Datacenter

The block diagram below represents AI datacenter solution recommended by **onsemi**. The diagram illustrates both AC-DC conversion and DC-DC power distribution stages utilized in AI data centers. **onsemi's** integrated approach leverages complementary products including cutting-edge Si, SiC and GaN technologies for power switching. Additionally, it incorporates gate drivers, multi-phase controllers & 48V controller, smart power stage (SPS) modules, smart fuses and PoL buck converters for power management. This combination enables systems with enhanced efficiency and increased power density, resulting in a smaller footprint.





Reference Design

Get Latest Version

Reference Design - 12 kW AI Cloud PSU

onsemi is at the forefront of powering the future of AI through its best-in-class silicon (Si) and silicon carbide (SiC) technologies, providing a comprehensive suite of power solutions (from **3kW to 25-30kW** HVDC) tailored for data centers, from the grid to GPU. Our technology is designed to meet the surging power demands of AI-driven operations, ensuring enhanced efficiency and lower TCO (total cost of ownership). With a focus on optimized energy usage and increased power density, our solutions are not only compact but also support a sustainable ecosystem.

onsemi's 12kW PSU reference design stands out in the market by delivering exceptional power output, advanced technology, and high efficiency, making it an ideal solution for modern data centers. With a power delivery of 12kW, it surpasses competitors by 50%, effectively meeting the rigorous demands of Al and cloud computing environments.

12 kW AI Cloud PSU Specifications

The integration of cutting-edge M3S MOSFET + SiC JFETs ensures superior performance, higher switching frequencies and enhanced thermal management. Achieving an impressive efficiency of 98%, this PSU significantly reduces energy costs and cooling requirements.

Key Features

- Input Voltage: V_{IN} = 180 305 VAC
- Input Frequency: F_{IN} = 47 63 Hz
- Maximum Input Current: I_{IN} = 68 A
- Output Voltage: V_{OUT} = 50 V
- Peak Efficiency: 98 % (@ 277 V_{IN} & 50 % load)
- THD: ≤5% @ 30% to 100% output power
- Hold-up Time: 20 ms @ full load
- Form Factor: 80 x 42 x 750 mm, 75 W/in³



Hold-Up Circuit AUX Supply

Three-Phase LLC DC-DC Converter

|--|

Three-Phase Totem Pole PFC





Figure 13: 12 kW AI Cloud PSU Schematic

ONSEM

Silicon Carbide (SiC) Solutions

Get Latest Version

Silicon Carbide (SiC)

onsemi's 650V M3S **EliteSiC** MOSFETs offers superior switching performance and lower device capacitances to achieve higher efficiency. This cutting-edge technology achieves a remarkable 97.5% peak efficiency for ORV3 PSU specifications. With best-in-class Figure-of-Merit (FoM) for high switching frequency applications, it excels in both hard-switching and soft-switching operations, achieving up to 99.6% efficiency in the PFC stage. Additionally, **onsemi's** high-performance SiC Cascode JFETs deliver high switching speeds, low on-resistance, and compatibility with existing drivers make them a compelling solution for hyperscale data centers, offering lower system costs and excellent efficiency.

650V SIC MOSFET NTBL023N065M3S

The 650V **M3S** SiC MOSFETs family is optimized for fast switching applications. Perform best with an 18V gate drive but also work well with 15V. The **TOLL** package enhances thermal & switching performance due to its Kelvin Source configuration and reduced parasitic source inductance.

Key Features:

- TOLL package with Kelvin source configuration
- Excellent FOM [= R_{DS(on)} * Eoss]
- Ultra low gate charge (Q_{G(tot)} = 69 nC)
- High speed switching with low capacitance (Coss = 152 pF)
- 15V to 18V gate drive
- Typ. R_{DS(on)} = 23 mΩ at Vgs = 18V
- 100% avalanche tested
- Target applications: Data centers, Server power, Cloud system, Telecom

Learn more about EliteSiC MOSFET M3S family

Figure 16: R_{DS(on)} x Area Comparison

Download Application Note

Figure 14: 650V M3S SiC MOS Packages for AI Data Center

Figure 15: 650V M3S SiC MOSFET FoM Comparison

750V SiC Cascode JFETs

Achieve best balance between cost and performance for soft switching; between cost and reliability for HVDC ORing (protect against reverse input current) meanwhile keeping the same driving compatibility as SJ FET.

Key Features:

- Trench structure with reduced cell pitch
- Optimized drift region
- Reduced substrate thickness
- Industry's lowest on-resistance per unit area (R_{DS(on)} x Area)
- Target applications: Al Datacenter Power Supply, EV Charging, PFC, Solar Inverters

Learn more about SiC Cascode JFET Portfolio

Onsemi

AI Data Center

Get Latest Version

onsemi

Intelligent Technology. Better Future.

Register now to unlock all System Solution Guides and get additional exclusive benefits!

- Utilize Elite Power Simulator & other developer tools.
- Watch exclusive webinars and seminars.

Open full System Solution Guide

onsemi, the onsemi logo, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

{ { {