

## AR0822

# Image Sensor, 8 MP, Rolling Shutter, Hyperlux™ LH

## Product Overview

For complete documentation, see the data sheet.

The AR0822 belongs to onsemi's Hyperlux LH product family, it is a 8-megapixel (MP) stacked 1/1.8inch (8.81mm diagonal) BSI (back-side illuminated) CMOS digital image sensor based upon a 2.0 μm pixel. It features an activepixel array of 3840 (H) x 2160 (V) and is capable of 4K video at 60 frames-per-second (fps), capturing images in either linear or eHDR modes (120 dB) with a rollingshutter readout.

## Features

- 4K (8 MP) at 60 fps for Excellent Video Performance
- Fast, Full-Resolution Video Capture of 3840 X 2160 at 30 fps in 3- Exposure embedded High Dynamic Range (eHDR) up to 120 dB
- Advanced On-Sensor eHDR Reconstruct with Flexible Exposure Ratio Control
- Two Exposure Line Li-HDR Output
- Wake-on-Motion Feature
- Extended Dynamic Range (eDR)
- Intelligent Lineralization to Minimize Motion Artifacts and LED Flickers

## Applications

- 4K/ 8 MP Imaging

## End Products

- Security and Surveillance Cameras
- Robotics
- Vehicle Dashboard Cameras

## Part Electrical Specifications

Product	Status	Compliance	Type	Me-gapi-xels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (µm)	Output Interface	Color	Family	Package Type	Case Outline	MSL Type	MSL Temp (°C)	Container Type	Container Qty.
AR0822NPSC10 SMTA0-DP	Active		CMOS	8	90	1/1.8 inch	Electronic Rolling Shutter and Global Reset Release	2.0 x 2.0	MIPI	RGB	Hyperlux LH	PBG A75 14.0 0x9.50x1.55 1.00 P	117 CU. PDF	4	260	JTRAY	1470
AR0822NPSC10 SMTA0-DR	Active		CMOS	8	90	1/1.8 inch	Electronic Rolling Shutter and Global Reset Release	2.0 x 2.0	MIPI	RGB	Hyperlux LH	PBG A75 14.0 0x9.50x1.55 1.00 P	117 CU. PDF	4	260	JTRAY	1470
AR0822NPSM10 SMTA0-DP	Active		CMOS	8	90	1/1.8 inch	Electronic Rolling Shutter and Global Reset Release	2.0 x 2.0	MIPI	Mono	Hyperlux LH	PBG A75 14.0 0x9.50x1.55 1.00 P	117 CU. PDF	4	260	JTRAY	1470
AR0822NPSM10 SMTA0-DR	Active		CMOS	8	90	1/1.8 inch	Electronic Rolling Shutter and Global Reset Release	2.0 x 2.0	MIPI	Mono	Hyperlux LH	PBG A75 14.0 0x9.50x1.55 1.00 P	117 CU. PDF	4	260	JTRAY	1470