



FINAL PRODUCT/PROCESS CHANGE NOTIFICATION #20324GCGeneric Copy

Issue Date: 10-Nov-2014

TITLE: Assembly and Test site transfer from Kanto Sanyo Semiconductors Co., Ltd to ON Semiconductor SSMP Philippines Corporation (Group 08-C)

PROPOSED FIRST SHIP DATE: 10-Feb-2015 (or earlier upon approval due to shortage of product)

AFFECTED CHANGE CATEGORY(S): Assembly and Test site

FOR ANY QUESTIONS CONCERNING THIS NOTIFICATION:

Contact your local ON Semiconductor Sales Office or
<toshiitsu.igarashi@onsemi.com><takeshi2.hoshino@onsemi.com> <shinya.okada@onsemi.com>
<ikuo.saeki@onsemi.com><Toshimitsu.Namiki@onsemi.com><naoki.koyama@onsemi.com>
<takehito.tsukui@onsemi.com> <keiji.ueda@onsemi.com>

SAMPLES: Contact your local ON Semiconductor Sales Office or <jun.hasunuma@onsemi.com>

ADDITIONAL RELIABILITY DATA: Available

Contact your local ON Semiconductor Sales Office
or <Takashi.Naruse@onsemi.com><Satoru.Fujinuma@onsemi.com>

NOTIFICATION TYPE:

Final Product/Process Change Notification (FPCN)

Final change notification sent to customers. FPCNs are issued at least 90 days prior to implementation of the change.

ON Semiconductor will consider this change approved unless specific conditions of acceptance are provided in writing within 30 days of receipt of this notice. To do so, contact <quality@onsemi.com>.

DESCRIPTION AND PURPOSE:

As a part of restructuring of semiconductor production infrastructure, Hanyu plant of Kanto Sanyo Semiconductors Co., Ltd was closed at the end of June, 2014.

In order to continue supply of applicable products under this condition, the products and the equipments is transferring to ON Semiconductor SSMP Philippines Corporation.

The materials and package outline of these products will remain identical. Qualification tests are designed to show that the reliability of transferred devices will continue to meet or exceed ON Semiconductor standards.


FINAL PRODUCT/PROCESS CHANGE NOTIFICATION #20324GC
RELIABILITY DATA SUMMARY:

Package name : TQFP100

| Test Items | Test Condition | Test Time | Results |
|---|--|-----------|---------|
| Temperature Humidity Bias * | Ta=85degC,RH=85%, Vcc=Recommended | 168hrs | Pass |
| Temperature Humidity Storage * | Ta=85degC,RH=85% | 168hrs | Pass |
| Temperature Cycle * | Ta=-65degC(30min) ⇔ Ta=150degC (30min) | 100cycles | Pass |
| Pressure Cooker * | Ta=121degC,RH=100% ,205kPa | 100hrs | Pass |
| High Temperature Storage | Ta=150degC | 168hrs | Pass |
| Resistance to Soldering heat (Reflow Soldering) | 255degC,10s (Peak260degC) | 2times | Pass |
| Solderability | 245degC,3s(with Flux) Soldering area,95% over(Sn-3.0Ag-0.5Cu) | 1time | Pass |

Notes:

The test items with * mark are put into operation after the reflow soldering (at 255degC for 10seconds) -> SMD
 Temperature Humidity Bias Test: PD>=0.1W -> Intermittent power application consists of 1h ON and 3h OFF.

Judgment Criteria :

Judgment Criteria are due to the limits of the electrical characteristics in the detail specification. (Except for Solderability)

Package name : TQFP120

| Test Items | Test Condition | Test Time | Results |
|---|--|-----------|---------|
| Temperature Humidity Bias * | Ta=85degC,RH=85%, Vcc=Recommended | 168hrs | Pass |
| Temperature Humidity Storage * | Ta=85degC,RH=85% | 168hrs | Pass |
| Temperature Cycle * | Ta=-65degC(30min) ⇔ Ta=150degC (30min) | 100cycles | Pass |
| Pressure Cooker * | Ta=121degC,RH=100% ,205kPa | 100hrs | Pass |
| High Temperature Storage | Ta=150degC | 168hrs | Pass |
| Resistance to Soldering heat (Reflow Soldering) | 255degC,10s (Peak260degC) | 2times | Pass |
| Solderability | 245degC,3s(with Flux) Soldering area,95% over(Sn-3.0Ag-0.5Cu) | 1time | Pass |

Notes:

The test items with * mark are put into operation after the reflow soldering (at 255degC for 10seconds) -> SMD
 Temperature Humidity Bias Test: PD>=0.1W -> Intermittent power application consists of 1h ON and 3h OFF.

Judgment Criteria :

Judgment Criteria are due to the limits of the electrical characteristics in the detail specification. (Except for Solderability)



FINAL PRODUCT/PROCESS CHANGE NOTIFICATION #20324GC

Package name : TQFP120L

| Test Items | Test Condition | Test Time | Results |
|---|--|-----------|---------|
| Temperature Humidity Bias * | Ta=85degC,RH=85%, Vcc=Recommended | 168hrs | Pass |
| Temperature Humidity Storage * | Ta=85degC,RH=85% | 168hrs | Pass |
| Temperature Cycle * | Ta=-65degC(30min) ⇔ Ta=150degC (30min) | 100cycles | Pass |
| Pressure Cooker * | Ta=121degC,RH=100% ,205kPa | 100hrs | Pass |
| High Temperature Storage | Ta=150degC | 168hrs | Pass |
| Resistance to Soldering heat (Reflow Soldering) | 255degC,10s (Peak260degC) | 2times | Pass |
| Solderability | 245degC,3s(with Flux) Soldering area,95% over(Sn-3.0Ag-0.5Cu) | 1time | Pass |

Notes:

The test items with * mark are put into operation after the reflow soldering (at 255degC for 10seconds) -> SMD
 Temperature Humidity Bias Test: PD>=0.1W -> Intermittent power application consists of 1h ON and 3h OFF.

Judgment Criteria :

Judgment Criteria are due to the limits of the electrical characteristics in the detail specification. (Except for Solderability)

This FPCN will be updated after reliability evaluation was completed.

Reliability test is still in progress.

Estimated date for completion: 28/Nov/2014

ELECTRICAL CHARACTERISTIC SUMMARY:

There is no change in the electrical performance. Datasheet specifications remain unchanged.

CHANGED PART IDENTIFICATION:

Products manufactured at SSMP will be marked with 'L7' preceding the Serial No. on shipping label.



FINAL PRODUCT/PROCESS CHANGE NOTIFICATION #20324GC

List of affected General Parts:

LC74736PT-E
LC749000PT-8B15H
LC749402PT-H
LC75806PT-H
LC75806PTS-T-H
LC75809PT-H
LC75809PTS-H
LC75809PTS-T-H
LC75810T-8725-E
LC75810TS-8725-E
LC75812PTH-8565-H
LC75812PTS-8565-H
LC75813T-E
LC75813TS-E
LC75847T-E
LC75847TS-E
LC823410-10R-H

List of affected Customer Specific Parts:

LC749402PT-UDE-H
LC749492PT-UCE-H
LC75090PT-H
LC75806PTS-T-UKP-H
LC75809PT-US-H
LC75810T-8728-E
LC75813TS-USL-E
LC75818PT-8560-UM-H
LC75818PTH-8561-H
LC75847TS-UALS-E
LC75847TS-USD-E
LC75847TS-USL-E
LC877G16A-5BV6-2H