ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

General Purpose Amplifier Transistors

PNP Surface Mount

• Moisture Sensitivity Level: 1

• ESD Rating: TBD

MAXIMUM RATINGS (T_A = 25° C)

Rating	Symbol	Value	Unit
Collector-Base Voltage	V _{(BR)CBO}	50	Vdc
Collector-Emitter Voltage	V _{(BR)CEO}	50	Vdc
Emitter-Base Voltage	V _{(BR)EBO}	7.0	Vdc
Collector Current – Continuous	Ι _C	150	mAdc
Collector Current – Peak	I _{C(P)}	200	mAdc
Base Current	I _B	30	mAdc


THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Power Dissipation	PD	200	mW
Junction Temperature	TJ	150	°C
Storage Temperature	T _{stg}	-55 to +150	°C



ON Semiconductor®

http://onsemi.com





ORDERING INFORMATION

Device†	Package	Shipping [†]	
2SA1162GT1	SC-59	3000/Tape & Reel	
2SA1162YT1	SC-59	3000/Tape & Reel	

†The "T1" suffix refers to a 7 inch reel.

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

Characteristic Symbol Min Unit Max 50 _ Vdc Collector-Emitter Breakdown Voltage (I_C = 2.0 mAdc, I_B = 0) V_{(BR)CEO} Collector–Base Breakdown Voltage ($I_C = 10 \ \mu Adc$, $I_E = 0$) V_{(BR)CBO} 50 _ Vdc Emitter–Base Breakdown Voltage ($I_E = 10 \ \mu Adc, I_C = 0$) V_{(BR)EBO} 7.0 _ Vdc Collector–Base Cutoff Current ($V_{CB} = 50$ Vdc, $I_E = 0$) I_{CBO} _ 0.1 μAdc Emitter Cut–off Current (V_{EB} = 5 V, I_C = 0 V) 0.1 _ μA I_{EBO} Collector-Emitter Cutoff Current ICEO $(V_{CE} = 10 \text{ Vdc}, I_B = 0)$ $(V_{CE} = 30 \text{ Vdc}, I_B = 0)$ _ 0.1 μAdc 2.0 . μAdc _ DC Current Gain (Note 1) $(V_{CE} = 6.0 \text{ Vdc}, I_C = 2.0 \text{ mAdc})$ h_{FE} _ 2SA1162YT1 120 240 2SA1162GT1 200 400 Collector–Emitter Saturation Voltage (I_C = 100 mAdc, I_B = 10 mAdc) 0.3 V_{CE(sat)} _ Vdc SMALL-SIGNAL CHARACTERISTICS

ELECTRICAL CHARACTERISTICS (T _A = 25°C unless otherwise noted)
--


Current-Gain – Bandwidth Product ($I_C = 1.0 \text{ mA}, V_{CE} = 10.0 \text{ V}, f = 10 \text{ MHz}$)	f _T	80	_	MHz
Output Capacitance (V _{CB} = 10 V, f = 1.0 MHz)	C _{obo}	_	7.0	pF
Noise Figure (I_C = 0.1 mA, V_{CE} = 6.0 Vdc, R_S = 10 kΩ, f = 1.0 kHz, BW = 200 Hz)	NF	-	10	dB

1. Pulse Test: Pulse Width \leq 300 µs, D.C. \leq 2%.

INFORMATION FOR USING THE SC-59 SURFACE MOUNT PACKAGE

MINIMUM RECOMMENDED FOOTPRINT FOR SURFACE MOUNTED APPLICATIONS

Surface mount board layout is a critical portion of the total design. The footprint for the semiconductor packages must be the correct size to insure proper solder connection interface between the board and the package. With the correct pad geometry, the packages will self align when subjected to a solder reflow process.



SC-59 POWER DISSIPATION

The power dissipation of the SC–59 is a function of the pad size. This can vary from the minimum pad size for soldering to the pad size given for maximum power dissipation. Power dissipation for a surface mount device is determined by $T_{J(max)}$, the maximum rated junction temperature of the die, $R\theta_{JA}$, the thermal resistance from the device junction to ambient; and the operating temperature, T_A . Using the values provided on the data sheet, P_D can be calculated as follows.

$$P_{D} = \frac{T_{J(max)} - T_{A}}{R_{\theta JA}}$$

The values for the equation are found in the maximum ratings table on the data sheet. Substituting these values into

the equation for an ambient temperature T_A of 25°C, one can calculate the power dissipation of the device which in this case is 338 milliwatts.

$$P_{D} = \frac{150^{\circ}C - 25^{\circ}C}{370^{\circ}C/W} = 338 \text{ milliwatts}$$

The 370°C/W assumes the use of the recommended footprint on a glass epoxy printed circuit board to achieve a power dissipation of 338 milliwatts. Another alternative would be to use a ceramic substrate or an aluminum core board such as Thermal Clad[™]. Using a board material such as Thermal Clad, the power dissipation can be doubled using the same footprint.

SOLDERING PRECAUTIONS

The melting temperature of solder is higher than the rated temperature of the device. When the entire device is heated to a high temperature, failure to complete soldering within a short time could result in device failure. Therefore, the following items should always be observed in order to minimize the thermal stress to which the devices are subjected.

- Always preheat the device.
- The delta temperature between the preheat and soldering should be 100°C or less.*
- When preheating and soldering, the temperature of the leads and the case must not exceed the maximum temperature ratings as shown on the data sheet. When using infrared heating with the reflow soldering method, the difference should be a maximum of 10°C.

- The soldering temperature and time should not exceed 260°C for more than 10 seconds.
- When shifting from preheating to soldering, the maximum temperature gradient should be 5°C or less.
- After soldering has been completed, the device should be allowed to cool naturally for at least three minutes. Gradual cooling should be used as the use of forced cooling will increase the temperature gradient and result in latent failure due to mechanical stress.
- Mechanical stress or shock should not be applied during cooling

* Soldering a device without preheating can cause excessive thermal shock and stress which can result in damage to the device.

SOLDER STENCIL GUIDELINES

Prior to placing surface mount components onto a printed circuit board, solder paste must be applied to the pads. A solder stencil is required to screen the optimum amount of solder paste onto the footprint. The stencil is made of brass or stainless steel with a typical thickness of 0.008 inches. The stencil opening size for the surface mounted package should be the same as the pad size on the printed circuit board, i.e., a 1:1 registration.

TYPICAL SOLDER HEATING PROFILE

For any given circuit board, there will be a group of control settings that will give the desired heat pattern. The operator must set temperatures for several heating zones, and a figure for belt speed. Taken together, these control settings make up a heating "profile" for that particular circuit board. On machines controlled by a computer, the computer remembers these profiles from one operating session to the next. Figure 1 shows a typical heating profile for use when soldering a surface mount device to a printed circuit board. This profile will vary among soldering systems but it is a good starting point. Factors that can affect the profile include the type of soldering system in use, density and types of components on the board, type of solder used, and the type of board or substrate material being used. This profile shows temperature versus time.

The line on the graph shows the actual temperature that might be experienced on the surface of a test board at or near a central solder joint. The two profiles are based on a high density and a low density board. The Vitronics SMD310 convection/infrared reflow soldering system was used to generate this profile. The type of solder used was 62/36/2 Tin Lead Silver with a melting point between 177–189°C. When this type of furnace is used for solder reflow work, the circuit boards and solder joints tend to heat first. The components on the board are then heated by conduction. The circuit board, because it has a large surface area, absorbs the thermal energy more efficiently, then distributes this energy to the component may be up to 30 degrees cooler than the adjacent solder joints.





Figure 1. Typical Solder Heating Profile

PACKAGE DIMENSIONS

SC-59 CASE 318D-04 ISSUE F



NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: MILLIMETER.							
		MILLIMETERS		INCHES			
	DIM	MIN	MAX	MIN	MAX		
	Α	2.70	3.10	0.1063	0.1220		
	В	1.30	1.70	0.0512	0.0669		
	С	1.00	1.30	0.0394	0.0511		
	D	0.35	0.50	0.0138	0.0196		
	G	1.70	2.10	0.0670	0.0826		
	Н	0.013	0.100	0.0005	0.0040		
	J	0.09	0.18	0.0034	0.0070		
	K	0.20	0.60	0.0079	0.0236		
	L	1.25	1.65	0.0493	0.0649		
	S	2.50	3.00	0.0985	0.1181		
	OTVI E	· .					

STYLE 1: PIN 1. EMITTER 2. BASE 3. COLLECTOR

Thermal Clad is a registered trademark of the Bergquist Company.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2–9–1 Kamimeguro, Meguro–ku, Tokyo, Japan 153–0051 Phone: 81–3–5773–3850 ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.