onsemi

COLLECTOR

3

2

BASE

Amplifier Transistors

NPN Silicon

BC546B, BC547A, B, C, BC548B, C

Features

• Pb-Free Packages are Available*


MAXIMUM RATINGS

Rating		Symbol	Value	Unit
Collector - Emitter Voltage	BC546 BC547 BC548	V _{CEO}	65 45 30	Vdc
Collector - Base Voltage	BC546 BC547 BC548	V _{CBO}	80 50 30	Vdc
Emitter - Base Voltage		V _{EBO}	6.0	Vdc
Collector Current – Continuous		IC	100	mAdc
Total Device Dissipation @ T_A : Derate above 25°C	= 25°C	PD	625 5.0	mW mW/°C
Total Device Dissipation @ T_C Derate above 25°C	= 25°C	PD	1.5 12	W mW/°C
Operating and Storage Junction Temperature Range	n	T _J , T _{stg}	-55 to +150	°C
THERMAL CHARACTERIS	TICE	5		

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient	R_{\thetaJA}	200	°C/W
Thermal Resistance, Junction-to-Case	R _{θJC}	83.3	°C/W

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



= Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.


*For additional information on our Pb–Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.


BC546B, BC547A, B, C, BC548B, C

Characteristic		Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS						•
Collector – Emitter Breakdown Voltage $(I_C = 1.0 \text{ mA}, I_B = 0)$	BC546 BC547	V _{(BR)CEO}	65 45	- -	-	V
	BC548		30	-	-	
Collector – Base Breakdown Voltage ($I_C = 100 \ \mu Adc$)	BC546 BC547 BC548	V _{(BR)CBO}	80 50 30		- - -	V
Emitter – Base Breakdown Voltage ($I_E = 10 \ \mu A, I_C = 0$)	BC546 BC547 BC548	V _{(BR)EBO}	6.0 6.0 6.0	- - -	- - -	V
	BC546 BC547 BC548 BC546/547/548	ICES		0.2 0.2 0.2 -	15 15 15 4.0	nA μA
ON CHARACTERISTICS			V			
DC Current Gain (I _C = 10 μ A, V _{CE} = 5.0 V)	BC547A BC546B/547B/548B BC548C	h _{FE}		90 150 270		-
(I _C = 2.0 mA, V _{CE} = 5.0 V)	BC546 BC547 BC548 BC547A BC546B/547B/548B BC547C/BC548C		110 110 110 110 200 420	- - 180 290 520	450 800 800 220 450 800	
(I _C = 100 mA, V _{CE} = 5.0 V)	BC547A/548A BC546B/547B/548B BC548C	RIN		120 180 300	- - -	
$ Collector - Emitter Saturation Voltage \\ (I_C = 10 mA, I_B = 0.5 mA) \\ (I_C = 100 mA, I_B = 5.0 mA) \\ (I_C = 10 mA, I_B = See Note 1) $	NC AC	V _{CE(sat)}	- - -	0.09 0.2 0.3	0.25 0.6 0.6	V
Base – Emitter Saturation Voltage (I _C = 10 mA, I _B = 0.5 mA)		V _{BE(sat)}	-	0.7	-	V
$\begin{array}{l} \text{Base} - \text{Emitter On Voltage} \\ (I_{C} = 2.0 \text{ mA}, \text{V}_{CE} = 5.0 \text{ V}) \\ (I_{C} = 10 \text{ mA}, \text{V}_{CE} = 5.0 \text{ V}) \end{array}$	EN .	V _{BE(on)}	0.55 _		0.7 0.77	V
SMALL-SIGNAL CHARACTERISTICS						
Current – Gain – Bandwidth Product ($I_C = 10 \text{ mA}, V_{CE} = 5.0 \text{ V}, f = 100 \text{ MHz}$)	BC546 BC547 BC548	f _T	150 150 150	300 300 300	- - -	MHz
Output Capacitance $(V_{CB} = 10 \text{ V}, I_C = 0, f = 1.0 \text{ MHz})$		C _{obo}	-	1.7	4.5	pF
Input Capacitance (V _{EB} = 0.5 V, I _C = 0, f = 1.0 MHz)		C _{ibo}	-	10	-	pF
Small – Signal Current Gain (I _C = 2.0 mA, V _{CE} = 5.0 V, f = 1.0 kHz)	BC546 BC547/548 BC547A BC546B/547B/548B BC547C/548C	h _{fe}	125 125 125 240 450	- 220 330 600	500 900 260 500 900	-
Noise Figure (I _C = 0.2 mA, V _{CE} = 5.0 V, R _S = 2 kΩ, f = 1.0	O kHz, ∆f = 200 Hz) BC546 BC547 BC548	NF		2.0 2.0 2.0	10 10 10	dB

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

BC547/BC548





BC546

BC546B, BC547A, B, C, BC548B, C

ORDERING INFORMATION


Device	Package	Shipping [†]
BC546B	TO-92	5000 Units / Bulk
BC546BG	TO-92 (Pb-Free)	5000 Units / Bulk
BC546BRL1	TO-92	2000 / Tape & Reel
BC546BRL1G	TO-92 (Pb-Free)	2000 / Tape & Reel
BC546BZL1G	TO-92 (Pb-Free)	2000 / Ammo Box
BC547ARL	TO-92	2000 / Tape & Reel
BC547ARLG	TO-92 (Pb-Free)	2000 / Tape & Reel
BC547AZL1G	TO-92 (Pb-Free)	2000 / Ammo Box
BC547BG	TO-92 (Pb-Free)	5000 Units / Bulk
BC547BRL1G	TO-92 (Pb-Free)	2000 / Tape & Reel
BC547BZL1G	TO-92 (Pb-Free)	2000 / Ammo Box
BC547CG	TO-92 (Pb-Free)	5000 Units / Bulk
BC547CZL1G	TO-92 (Pb-Free)	2000 / Ammo Box
BC548BG	TO-92 (Pb-Free)	5000 Units / Bulk
BC548BRL1G	TO-92 (Pb-Free)	2000 / Tape & Reel
BC548BZL1G	TO-92 (Pb-Free)	2000 / Ammo Box
BC548CG	TO-92 (Pb-Free)	5000 Units / Bulk
BC548CZL1G	TO-92 (Pb-Free)	2000 / Ammo Box

(For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS

ON Semiconductor®





STYLES ON PAGE 2

DOCUMENT NUMBER:	98ASB42022B	Electronic versions are uncontrolle	t Repository. Printed	
STATUS:	ON SEMICONDUCTOR STANDARD	accessed directly from the Document versions are uncontrolled except		
NEW STANDARD:		"CONTROLLED COPY" in red.		
DESCRIPTION:	TO-92 (TO-226)		PAGE 1 OF 3	

TO-92 (TO-226) CASE 29-11 ISSUE AM

DATE 09 MAR 2007

STYLE 1: PIN 1. EMITTER 2. BASE 3. COLLECTOR STYLE 6: PIN 1. GATE 2. SOURCE & SUBSTRATE 3. DRAIN STYLE 11: PIN 1. ANODE 2. CATHODE & ANODE 3. CATHODE STYLE 16: PIN 1. ANODE 2. GATE 3. CATHODE STYLE 21: PIN 1. COLLECTOR 2. EMITTER 3. BASE STYLE 22: PIN 1. VCC 2. GROUND 2 3. OUTPUT STYLE 31: PIN 1. GATE 2. DRAIN 3. SOURCE

	BASE EMITTER COLLECTOR
2.	SOURCE DRAIN GATE
2.	MAIN TERMINAL 1 Gate Main Terminal 2
2.	COLLECTOR BASE EMITTER
2.	SOURCE GATE DRAIN

2	1. 2.	ANODE ANODE CATHODE
2	1. 2.	DRAIN Gate Source & Substrate
2	1. 2.	ANODE 1 GATE CATHODE 2
2	1. 2.	ANODE CATHODE NOT CONNECTED
2	1. 2.	GATE SOURCE DRAIN
2	1. 2.	CATHODE ANODE GATE

STYLE 33: PIN 1. RETURN 2. INPUT 3. OUTPUT

2.	CATHODE CATHODE ANODE
2.	BASE 1 EMITTER BASE 2
2.	EMITTER COLLECTOR BASE
	GATE ANODE CATHODE
2.	EMITTER Collector/Anode Cathode
2.	NOT CONNECTED ANODE CATHODE
2.	INPUT GROUND LOGIC

STYLE 4:

STYLE 5: PIN 1. DRAIN 2. SOURCE 3. GATE STYLE 10: PIN 1. CATHODE 2. GATE 3. ANODE STYLE 15: PIN 1. ANODE 1 2. CATHODE 3. ANODE 2 STYLE 20: PIN 1. NOT CONNECTED 2. CATHODE 3. ANODE STYLE 25: PIN 1. MT 1 2. GATE 3. MT 2 STYLE 30: PIN 1. DRAIN 2. GATE 3. SOURCE STYLE 35: PIN 1. DRAIN 2. GATE 3. SOURCE STYLE 35: PIN 1. GATE 2. COLLECTOR 3. EMITTER

DOCUMENT NUMBER:	98ASB42022B	Electronic versions are uncontrolle		
STATUS:	ON SEMICONDUCTOR STANDARD	ONDUCTOR STANDARD accessed directly from the Document Roversions are uncontrolled except whether the standard exce		
NEW STANDARD:		"CONTROLLED COPY" in red.		
DESCRIPTION:	TO-92 (TO-226)		PAGE 2 OF 3	



ON Semiconductor®

DOCUMENT NUMBER: 98ASB42022B

PAGE 3 OF 3

ISSUE	REVISION	DATE
AM	ADDED BENT-LEAD TAPE & REEL VERSION. REQ. BY J. SUPINA.	09 MAR 2007

ON Semiconductor and images are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the BSCILLC product care a stuation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death agesociated with such unintended or unauthorized use payes that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunit/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>