ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



Praetorian® L-C LCD and Camera EMI Filter Array with ESD Protection

CM1492-06DE

Features


- Six channels of EMI filtering with integrated ESD protection
- Pi-style EMI filters in a capacitor-inductorcapacitor (C-L-C) network
- ±15kV ESD protection on each channel (contact):


IEC 61000-4-2 Level 4, contact discharge

- ±30kV ESD protection on each channel (HBM)
- Greater than 30dB attenuation (typical) at 1GHz
- TDFN package with 0.40mm lead pitch:
 - 6-channel = 12-lead TDFN
- Tiny TDFN package size:
 - 12-lead: 2.5mm x 1.35mm
- RoHS-compliant, lead-free packaging

Applications

- LCD and camera data lines in mobile handsets
- Wireless handsets
- · LCD and camera modules





| PIN DESCRIPTIONS | | | | | |
|------------------|---------|------------------------|--|--|--|
| PINS | NAME | DESCRIPTION | | | |
| 1 | FILTER1 | Filter + ESD Channel 1 | | | |
| 2 | FILTER2 | Filter + ESD Channel 2 | | | |
| 3 | FILTER3 | Filter + ESD Channel 3 | | | |
| 4 | FILTER4 | Filter + ESD Channel 4 | | | |
| 5 | FILTER5 | Filter + ESD Channel 5 | | | |
| 6 | FILTER6 | Filter + ESD Channel 6 | | | |
| 7 | FILTER6 | Filter + ESD Channel 6 | | | |
| 8 | FILTER5 | Filter + ESD Channel 5 | | | |
| 9 | FILTER4 | Filter + ESD Channel 4 | | | |
| 10 | FILTER3 | Filter + ESD Channel 3 | | | |
| 11 | FILTER2 | Filter + ESD Channel 2 | | | |
| 12 | FILTER1 | Filter + ESD Channel 1 | | | |
| GND PAD | GND | Device Ground | | | |

Ordering Information

| PART NUMBERING INFORMATION | | | | | | |
|----------------------------|---------|-------------------|--------------|--|--|--|
| Pins | Package | Order Part Number | Part Marking | | | |
| 12 | TDFN-12 | CM1492-06DE | N926 | | | |

Note 1: Parts are shipped in Tape and Reel form unless otherwise specified.

CM1492-06DE

Specifications

| ABSOLUTE MAXIMUM RATINGS | | | | | |
|---------------------------|------------|----|--|--|--|
| PARAMETER | | | | | |
| Storage Temperature Range | 65 to +150 | °C | | | |
| Current per Inductor | 30 | mA | | | |
| DC Package Power Rating | 500 | mW | | | |

| STANDARD OPERATING CONDITIONS | | | | | |
|-------------------------------|------------|-------|--|--|--|
| PARAMETER | RATING | UNITS | | | |
| Operating Temperature Range | -40 to +85 | °C | | | |

| | ELECTRICAL OPERATING CHAP | RACTERISTICS (S | ee No | ote 1) | | |
|--------------------|--|---|-------|------------|------|----------|
| SYMBOL | PARAMETER | CONDITIONS | MIN | TYP | MAX | UNITS |
| L | Channel Inductance | | | 17 | | nH |
| C _{TOTAL} | Total Channel Capacitance | At 2.5VDC Reverse Bias, 1MHz, 30mVAC | 19 | 24 | 29 | pF |
| С | Capacitance C1 | At 2.5VDC Reverse Bias, 1MHz, 30mVAC | | 12 | | pF |
| V | Standoff Voltage | $I_{\text{DIODE}} = 10 \mu A$ | | 6.0 | | V |
| I _{LEAK} | Diode Leakage Current (reverse bias) | $V_{DIODE} = +3.3V$ | | 0.1 | 1.0 | μΑ |
| V _{SIG} | Signal Clamp Voltage | | | | | |
| | Positive Clamp | $I_{LOAD} = 10mA$ | 5.6 | 6.8 | 9.0 | V |
| | Negative Clamp | $I_{LOAD} = -10 \text{mA}$ | -1.5 | -0.8 | -0.4 | V |
| V _{ESD} | In-system ESD Withstand Voltage a) Human Body Model, MIL-STD-883, Method 3015 b) Contact Discharge per IEC 61000-4-2 Level 4 | Notes 2 and 3 | ±30 | | | kV |
| _ | | | ±15 | | | kV |
| R _{DYN} | Dynamic Resistance Positive Negative | | | 2.3 0.9 | | Ω |
| f _c | Roll-off Frequency at -6dB Attenuation $Z_{\text{SOUBCE}} = 50\Omega, Z_{\text{LOAD}} = 50\Omega$ | | | 400 | | MHz |

Note 1: $T_A=25$ °C unless otherwise specified.

Note 2: ESD applied to input and output pins with respect to GND, one at a time.

Note 3: Clamping voltage is measured at the opposite side of the EMI filter to the ESD pin (i.e. if ESD is applied to pin A1 then clamping voltage is measured at pin C1). Unused pins are left open.

Performance Information

Typical Diode Capacitance vs. Input Voltage




Figure 1. Filter Capacitance vs. Input Voltage (normalized to capacitance at 2.5VDC and 25°C)




Figure 2. Typical Performance Curve


Mechanical Details

TDFN-12 Mechanical Specifications, 0.4mm

Dimensions for the CM1492-06DE supplied in a 12-lead, 0.4mm pitch TDFN package are presented below.

| PACKAGE DIMENSIONS | | | | | | | |
|--------------------|-------------|---------|------|-----------|-------------|-------|--|
| | TDFN | | | | | | |
| | MO-229C* | | | | | | |
| | 12 | | | | | | |
| | | 1 | | İ | | | |
| | 1 | 1 | 1 | | | 1 | |
| | 0.70 | 0.75 | 0.80 | 0.028 | 0.030 | 0.031 | |
| | 0.00 | 0.02 | 0.05 | 0.000 | 0.001 0.002 | | |
| | 0 | .200 RE | F | 0.008 REF | | | |
| | 0.15 | 0.20 | 0.25 | 0.006 | 0.008 | 0.010 | |
| | 2.40 | 2.50 | 2.60 | 0.094 | 0.098 | 0.102 | |
| | 1.90 | 2.00 | 2.10 | 0.075 | 0.079 | 0.083 | |
| | 1.25 | 1.35 | 1.45 | 0.049 | 0.053 | 0.057 | |
| | 0.30 | 0.40 | 0.50 | 0.012 | 0.016 | 0.020 | |
| | 0.40 BSC | | | 0.016 BSC | | | |
| | 0.20 | | | 0.008 | | | |
| | 0.15 | 0.25 | 0.35 | 0.006 | 0.010 | 0.014 | |
| | 3000 pieces | | | | | | |
| i | | | | | | | |

^{*}This package is compliant with JEDEC standard MO-229C with the exception of the D, D2, E, E2, K and L dimensions as called out in the table above.



Dimensions for 12-Lead, 0.4mm pitch TDFN package

CM1492-06DE

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5773-3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local

Sales Representative