

CSPEMI307A

4-Channel ESD/EMI Filter Array Plus 4-Channel ESD Array for USB

Product Description

The CSPEMI307A is a multichannel EMI/ESD array offering a combination of four low-pass filter + ESD channels to reduce EMI/RFI emissions on a data port and four dedicated ESD-only channels intended specifically for ESD protection on a USB port. Each EMI/RFI channel integrates a high quality pi-style filter (C-R-C) which provides greater than 30 dB attenuation in the 800–2700 MHz range. These pi-style filters support bidirectional filtering, controlling EMI both to and from a data port connector.

The CSPEMI307A provides a high-level of ESD protection on all eight channels for sensitive electronic components that may be subjected to electrostatic discharge (ESD). The input pins are designed and characterized to safely dissipate ESD strikes of ± 15 kV, exceeding the maximum requirement of the IEC 61000-4-2 international standard. Using the MIL-STD-883 (Method 3015) specification for Human Body Model (HBM) ESD, the device provides protection for contact discharges to greater than ± 30 kV.

The CSPEMI307A is particularly well suited for portable electronics (e.g. cellular telephones, PDAs, notebook computers) because of its small package footprint and low weight. The CSPEMI307A is available in a space-saving, low-profile Chip Scale Package with lead-free finishing.

Features

- Four Channels of Combined EMI/RFI Filtering + ESD Protection
- Four Additional Channels of ESD-Only Protection
- EMI/ESD Channels Provide Greater than 32 dB Attenuation at 1 GHz
- ± 15 kV ESD Protection on all Channels (IEC 61000-4-2 Level 4, Contact Discharge)
- ± 30 kV ESD Protection on all Channels (HBM)
- Chip Scale Package Features Extremely Low Lead Inductance for Optimum Filter and ESD Performance
- 15-Bump, 2.960 mm x 1.330 mm Footprint Chip Scale Package (CSP)
- These Devices are Pb-Free and are RoHS Compliant

Applications

- EMI Filtering and ESD Protection for both Data and I/O Ports
- Outer 4 Channels Provide ESD Protection for USB Lines and other I/O Port Applications
- Wireless Handsets
- Handheld PCs / PDAs
- MP3 Players
- Notebooks
- Desktop PCs




ON Semiconductor®

<http://onsemi.com>



WLCSP15
CASE 567BS

MARKING DIAGRAM



307A = CSPEMI307A


ORDERING INFORMATION

Device	Package	Shipping†
CSPEMI307A	CSP-15 (Pb-Free)	3500/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

CSPEMI307A

ELECTRICAL SCHEMATIC




*See Package/Pinout Diagrams for expanded pin information.

Table 1. PIN DESCRIPTIONS

Pin(s)	Name	Description
A1	ESD_1	ESD Channel 1
A2	FILTER+ESD_1	Filter + ESD Channel 1
A3	FILTER+ESD_2	Filter + ESD Channel 2
A4	FILTER+ESD_3	Filter + ESD Channel 3
A5	FILTER+ESD_4	Filter + ESD Channel 4
A6	ESD_2	ESD Channel 2
B1-B3	GND	Device Ground
C1	ESD_3	ESD Channel 3
C2	FILTER+ESD_1	Filter + ESD Channel 1
C3	FILTER+ESD_2	Filter + ESD Channel 2
C4	FILTER+ESD_3	Filter + ESD Channel 3
C5	FILTER+ESD_4	Filter + ESD Channel 4
C6	ESD_4	ESD Channel 4

PACKAGE / PINOUT DIAGRAMS



Note: Lead-free devices are specified by using a "+" character for the top side orientation mark.

SPECIFICATIONS

Table 2. ABSOLUTE MAXIMUM RATINGS

Parameter	Rating	Units
Storage Temperature Range	-65 to +150	°C
DC Power per Resistor	100	mW
DC Package Power Rating	600	mW

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Table 3. STANDARD OPERATING CONDITIONS

Parameter	Rating	Units
Operating Temperature Range	-40 to +85	°C

CSPEMI307A

Table 4. ELECTRICAL OPERATING CHARACTERISTICS (Note 1)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
R	Resistance		80	100	120	Ω
C	Capacitance	At 2.5 V DC	24	30	36	pF
TCR	Temperature Coefficient of Resistance			1200		ppm/ $^{\circ}$ C
TCC	Temperature Coefficient of Capacitance	At 2.5 V DC		-300		ppm/ $^{\circ}$ C
V _{DIODE}	Diode Voltage (reverse bias)	I _{DIODE} = 10 μ A	5.5			V
I _{LEAK}	Diode Leakage Current (reverse bias)	V _{DIODE} = 3.3 V			100	nA
V _{SIG}	Signal Voltage Positive Clamp Negative Clamp	I _{LOAD} = 10 mA	5.6 -0.4	6.8 -0.8	9.0 -1.5	V
V _{ESD}	In-system ESD Withstand Voltage a) Human Body Model, MIL-STD-883, Method 3015 b) Contact Discharge per IEC 61000-4-2 Level 4	(Notes 2 and 4)	\pm 30 \pm 15			kV
V _{CL}	Clamping Voltage during ESD Discharge MIL-STD-883 (Method 3015), 8 kV Positive Transients Negative Transients	(Notes 2, 3 and 4)		+10 -5		V
f _C	Cut-off frequency Z _{SOURCE} = 50 Ω , Z _{LOAD} = 50 Ω	R = 100 Ω , C = 30 pF		64		MHz

1. T_A = 25 $^{\circ}$ C unless otherwise specified.
2. ESD applied to input and output pins with respect to GND, one at a time.
3. Clamping voltage is measured at the opposite side of the EMI filter to the ESD pin. For example, if ESD is applied to Pin A2, then clamping voltage is measured at Pin C2.
4. Unused pins are left open.

PERFORMANCE INFORMATION

Typical Filter Performance (T_A = 25 $^{\circ}$ C, DC Bias = 0 V, 50 Ω Environment)




Figure 1. Insertion Loss vs. Frequency (A2-C2 to GND B2)

PERFORMANCE INFORMATION (Cont'd)

Typical Filter Performance ($T_A = 25^\circ\text{C}$, DC Bias = 0 V, 50 Ω Environment)




Figure 2. Insertion Loss vs. Frequency (A3-C3 to GND B2)




Figure 3. Insertion Loss vs. Frequency (A4-C4 to GND B2)

CSPEMI307A

PERFORMANCE INFORMATION (Cont'd)

Typical Filter Performance ($T_A = 25^\circ\text{C}$, DC Bias = 0 V, 50 Ω Environment)




Figure 4. Insertion Loss vs. Frequency (A5-C5 to GND B2)




Figure 5. Comparison of Filter Response Curves for CSPEMI307A vs. DC Bias

PERFORMANCE INFORMATION (Cont'd)




Figure 6. Filter Capacitance vs. Input Voltage over Temperature
(normalized to capacitance at 2.5 VDC and 25°C)




Figure 7. Resistance vs. Temperature (normalized to resistance at 25°C)

APPLICATION INFORMATION

Parameter	Value
Pad Size on PCB	0.240 mm
Pad Shape	Round
Pad Definition	Non-Solder Mask defined pads
Solder Mask Opening	0.290 mm Round
Solder Stencil Thickness	0.125 mm – 0.150 mm
Solder Stencil Aperture Opening (laser cut, 5% tapered walls)	0.300 mm Round
Solder Flux Ratio	50/50 by volume
Solder Paste Type	No Clean
Pad Protective Finish	OSP (Entek Cu Plus 106A)
Tolerance – Edge To Corner Ball	$\pm 50 \mu\text{m}$
Solder Ball Side Coplanarity	$\pm 20 \mu\text{m}$
Maximum Dwell Time Above Liquidous	60 seconds
Maximum Soldering Temperature for Lead-free Devices using a Lead-free Solder Paste	260°C




Figure 8. Recommended Non-Solder Mask Defined Pad Illustration





Figure 9. Lead-free (SnAgCu) Solder Ball Reflow Profile




SCALE 4:1

WLCSP15, 2.96x1.33
CASE 567BS
ISSUE O


DATE 26 JUL 2010



TOP VIEW



SIDE VIEW




BOTTOM VIEW

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. COPLANARITY APPLIES TO SPHERICAL CROWNS OF SOLDER BALLS.

DIM	MILLIMETERS	
	MIN	MAX
A	0.56	0.65
A1	0.21	0.27
A2	0.40	REF
b	0.29	0.35
D	2.96	BSC
E	1.33	BSC
eD	0.50	BSC
eE	0.435	BSC

RECOMMENDED
SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	98AON49826E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	WLCSP15, 2.96X1.33	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales