# **SS2003M**

# **Schottky Barrier Diode** 30V, 2.0A, Low VF, Single MCPH6



http://onsemi.com

## **Applications**

- · High frequency rectification (switching regulators, converters, choppers)
- · Halogen free compliance

#### **Features**

- · Small Switching noise
- Low forward voltage (IF=2A, VF max=0.40V)
- · Small package permitting applied sets to be small and slim

## **Specifications**


#### Absolute Maximum Ratings at Ta=25°C

· High frequency rectification (sv	witching regul	ators, convei	ters, choppers	s)			
<ul> <li>Halogen free compliance</li> </ul>							_\
						. (	
Features						15l	)
<ul> <li>Small Switching noise</li> </ul>							
• Low forward voltage (IF=2A, VF max=0.40V)							
Small package permitting applied sets to be small and slim							
					NE		
Specifications					2.		
Absolute Maximum Ratings at Ta=25°C							
Parameter	Symbol		Cc itions	<u> </u>	Ratings	Unit	
Repetitive Peak Reverse Voltage	VRRM				101,	30 V	
Nonrepetitive Peak Reverse Surge Voltage	VRSM			0		30 V	
Average Output Current	lo			1111	(21)	2.0 A	
Surge Forward Current	<u>sM</u>	Iz sine wave,	c)'c'e	70 20	) `	10 A	
Junction Temperature			1, 1		-55 to +	125 °C	
Storage Temperature		$\sim$		111-2	-55 to +	125 °C	

Stresses exceeding Maximum Ration may da ge the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implie \_xtended ex esses abo is the recommended Operating Conditions may affect device reliability.

#### Package Di. ensions


unit · 7022 014



### Ordering & Package Information

Device	Package	Shipping	memo
SS2003M-TL-W	MCPH6 SC-88, SC-70-6, SOT-363	3,000 pcs./reel	Pb-Free and Halogen Free


#### Packing Type: TL



## Marking



### **Electrical Connection**




#### Electrical Characteristics at Ta=25°C

Parameter	Symbol	Conditions	Ratings			Unit
		Conditions	min	typ	max	Uill
Reverse Voltage	VR	I <sub>R</sub> =2.0mA	30			V
Forward Voltage	VF	IF=1.0A		0.30	0.35	V
		IF=2.0A		0.35	0.40	V
Reverse Current	IR	V <sub>R</sub> =15V			1.25	mA
Interterminal Capacitance	С	V <sub>R</sub> =10V, f=1MHz		75		pF
Reverse Recovery Time	t <sub>rr</sub>	IF=IR=100mA, See specified Test Circuit.			20	ns
Thermal Resistance	Rth(j-a)1	When mounted in Cu-foiled area of 1.44mm <sup>2</sup> x0.03mm on glass epoxy substrate		93.4		°C / W
	Rth(j-a)2	When mounted on ceramic substrate (500mm <sup>2</sup> ×0.8mm)		71.4		°C / W

# trr Test Cicuit







# **Outline Drawing**

SS2003M-TL-W

## Land Pattern Example





COMMENDED FOR NEW DESIGN

COMMENDED FOR NEW

ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights or others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/A