MOSFET – N-Channel, POWERTRENCH®

80 V, 300 A, 1.4 mΩ

FDBL86361-F085



N-Channel

Features

- Typical $R_{DS(on)}$ = 1.1 mΩ at V_{GS} = 10 V, I_D = 80 A
- Typical $Q_{g(tot)}$ = 172 nC at V_{GS} = 10 V, I_D = 80 A
- UIS Capability
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

Applications

- Automotive Engine Control
- PowerTrain Management
- Solenoid and Motor Drivers
- Integrated Starter/Alternator
- Primary Switch for 12 V Systems



H-PSOF8L
CASE 100CU



H-PSOF-8
CASE 100BQ

MARKING DIAGRAM



A	= Assembly Site
Y	= Year of Production
WW	= Work Week
ZZ	= Lot Code
FDBL86361	= Specific Device Code

MOSFET MAXIMUM RATINGS (T_J = 25 °C unless otherwise noted)

Symbol	Parameter	Ratings	Unit
V_{DSS}	Drain-to-Source Voltage	80	V
V_{GS}	Gate-to-Source Voltage	±20	V
I_D	Drain Current – Continuous (V_{GS} = 10), T_C = 25 °C (Note 1)	300	A
	Pulsed Drain Current, T_C = 25 °C	See Figure 4	
E_{AS}	Single Pulse Avalanche Energy (Note 2)	820	mJ
P_D	Power Dissipation	429	W
	Derate Above 25 °C	2.86	W/°C
T_J, T_{STG}	Operating and Storage Temperature	−55 to +175	°C
$R_{\theta JC}$	Thermal Resistance, Junction to Case	0.35	°C/W
$R_{\theta JA}$	Maximum Thermal Resistance, Junction to Ambient (Note 3)	43	°C/W

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Current is limited by bondwire configuration.
2. Starting T_J = 25 °C, L = 0.4 mH, I_{AS} = 64 A, V_{DD} = 40 V during inductor charging and V_{DD} = 0 V during time in avalanche.
3. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance, where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design, while $R_{\theta JA}$ is determined by the board design. The maximum rating presented here is based on mounting on a 1 in^2 pad of 2oz copper.

ORDERING INFORMATION

Device	Package	Shipping†
FDBL86361-F085	H-PSOF8L (Case 100CU)	2000 / Tape & Reel
FDBL86361-F085AW	H-PSOF-8 (Case 100BQ)	2000 / Tape & Reel

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2014

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise noted)

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
OFF CHARACTERISTICS							
BV_{DSS}	Drain-to-Source Breakdown Voltage	I_D = 250 μA, V_{GS} = 0 V		80	–	–	V
I_{DSS}	Drain-to-Source Leakage Current	V_{DS} = 80 V, V_{GS} = 0 V	T_J = 25 °C	–	–	1	μA
			T_J = 175 °C (Note 4)	–	–	1	mA
I_{GSS}	Gate-to-Source Leakage Current	V_{GS} = ±20 V		–	–	±100	nA
ON CHARACTERISTICS							
$V_{GS(th)}$	Gate to Source Threshold Voltage	V_{GS} = V_{DS}, I_D = 250 μA		2.0	3.0	4.0	V
$R_{DS(on)}$	Drain to Source on Resistance	I_D = 80 A, V_{GS} = 10 V	T_J = 25 °C	–	1.1	1.4	mΩ
			T_J = 175 °C (Note 4)	–	2.4	3.1	mΩ
DYNAMIC CHARACTERISTICS							
C_{iss}	Input Capacitance	V_{DS} = 25 V, V_{GS} = 0 V, f = 1 MHz		–	12800	–	pF
C_{oss}	Output Capacitance			–	1925	–	pF
C_{rss}	Reverse Transfer Capacitance			–	139	–	pF
R_g	Gate Resistance	f = 1 MHz		–	2.7	–	Ω
$Q_{g(ToT)}$	Total Gate Charge at 10 V	V_{GS} = 0 to 10 V	V_{DD} = 64 V, I_D = 80 A	–	172	188	nC
$Q_{g(th)}$	Threshold Gate Charge	V_{GS} = 0 to 2 V		–	23	27	nC
Q_{gs}	Gate-to-Source Gate Charge			–	51	–	nC
Q_{gd}	Gate-to-Drain “Miller” Charge			–	34	–	nC
SWITCHING CHARACTERISTICS							
t_{on}	Turn-On Time	V_{DD} = 40 V, I_D = 80 A, V_{GS} = 10 V, R_{GEN} = 6 Ω		–	–	128	ns
$t_{d(on)}$	Turn-On Delay			–	42	–	ns
t_r	Rise Time			–	73	–	ns
$t_{d(off)}$	Turn-Off Delay			–	87	–	ns
t_f	Fall Time			–	48	–	ns
t_{off}	Turn-Off Time			–	–	193	ns
DRAIN-SOURCE DIODE CHARACTERISTIC							
V_{SD}	Source-to-Drain Diode Voltage	I_{SD} = 80 A, V_{GS} = 0 V		–	–	1.25	V
		I_{SD} = 40 A, V_{GS} = 0 V		–	–	1.2	V
t_{rr}	Reverse-Recovery Time	I_F = 80 A, dI_{SD}/dt = 100 A/μs, V_{DD} = 64 V		–	117	136	ns
Q_{rr}	Reverse-Recovery Charge			–	205	269	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. The maximum value is specified by design at T_J = 175 °C. Product is not tested to this condition in production.

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS



Figure 1. Normalized Power Dissipation vs. Case Temperature



Figure 2. Maximum Continuous Drain Current vs. Case Temperature



Figure 3. Normalized Maximum Transient Thermal Impedance



Figure 4. Peak Current Capability

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS (continued)



Figure 5. Forward Bias Safe Operating Area



Refer to **onsemi** Application Notes AN7514 and AN7515.

Figure 6. Unclamped Inductive Switching Capability



Figure 7. Transfer Characteristics



Figure 8. Forward Diode Characteristics



Figure 9. Saturation Characteristics



Figure 10. Saturation Characteristics

Share Feedback
Your Opinion Matters

TYPICAL CHARACTERISTICS (continued)



Figure 11. R_{DSON} vs. Gate Voltage



Figure 12. Normalized R_{DSON} vs. Junction Temperature



Figure 13. Normalized Gate Threshold Voltage vs. Temperature



Figure 14. Normalized Drain to Source Breakdown Voltage vs. Junction Temperature



Figure 15. Capacitance vs. Drain to Source Voltage



Figure 16. Gate Charge vs. Gate to Source Voltage

POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries.

Share Feedback
Your Opinion Matters

REVISION HISTORY

Revision	Description of Changes	Date
8	Added -AW device variant to the datasheet. Updated Ordering Information to include both standard and -AW OPN. Added CASE 100BQ package outline and related device information.	10/14/2026

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

Share Feedback
Your Opinion Matters



H−PSOF−8 10.43x9.90x2.30, 1.20P
CASE 100BQ
ISSUE A

DATE 21 APR 2026









MILLIMETERS			
DIM	MIN	NOM	MAX
A	2.20	2.30	2.40
A3	0.40	0.50	0.60
b	0.70	0.80	0.90
b1	9.70	9.80	9.90
b2	0.42	0.46	0.50
D	10.43 BSC		
D1	6.75	6.95	7.15
D2	3.10	3.30	3.50
D3	3.98	4.18	4.38
E	9.90 BSC		
E1	7.90	8.10	8.30
e	1.20 BSC		
H	11.48	11.68	11.88
k	3.00	3.15	3.30
L	1.40	1.60	1.80
L1	0.60	0.70	0.80
L2	0.50	0.60	0.70
L4	1.00	1.15	1.30
Θ	4°	7°	10°
TOLERANCE OF FORM & POSITION			
aaa	0.15		
bbb	0.10		
ccc	0.10		
ddd	0.05		
eee	0.10		



RECOMMENDED MOUNTING FOOTPRINT

*For addtional information on our Pb−Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NOTES:
1. DIMENSIONING AND TOLERANCING AS PER ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30mm FROM THE TERMINAL TIP.
4. PROFILE TOLERANCE APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.
5. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

GENERIC MARKING DIAGRAM*



A = Assembly Location
Y = Year
WW = Work Week
ZZ = Assembly Lot Code
XXXX = Specific Device Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON36297E**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	**H−PSOF−8 10.43x9.90x2.30, 1.20P**		**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.



H−PSOF8L 10.38x9.90x2.30, 1.20P
CASE 100CU
ISSUE G

DATE 24 AUG 2026



TOP VIEW



SECTION "A−A"
SCALE: 2X



LAND PATTERN RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB−FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE onsemi SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.



SIDE VIEW



DETAIL "B"
SCALE: 2X



BOTTOM VIEW

NOTES:
1. PACKAGE STANDARD REFERENCE: JEDEC MO−299, ISSUE B.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
3. "e" REPRESENTS THE TERMINAL PITCH.
4. COPLANARITY APPLIES TO EXPOSED PAD AND LEADS..
5. A VISUAL INDEX FEATURE MUST BE LOCATED WITHIN THE HATCHED AREA.
6. DIMENSIONS b1,L1,L2 APPLY TO PLATED TERMINALS.
7. THE LOCATION AND SIZE OF EJECTOR MARKS ARE OPTIONAL.
8. THE LOCATION AND NUMBER OF FUSED LEADS ARE OPTIONAL.

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	2.20	2.30	2.40
A1	1.70	1.80	1.90
b	0.70	0.80	0.90
b1	9.70	9.80	9.90
b2	0.35	0.45	0.55
c	0.40	0.50	0.60
D	10.28	10.38	10.48
D/2	5.09	5.19	5.29
D1	10.98	11.08	11.18
D2	3.20	3.30	3.40
D3	2.60	2.70	2.80
D4	4.45	4.55	4.65
D5	3.20	3.30	3.40
D6	0.55	0.65	0.75
E	9.80	9.90	10.00
E1	7.30	7.40	7.50
E2	0.30	0.40	0.50
E3	7.40	7.50	7.60
E4	8.20	8.30	8.40

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
E5	9.36	9.46	9.56
E6	1.10	1.20	1.30
E7	0.15	0.18	0.21
e	1.20 BSC		
e/2	0.60 BSC		
H	11.58	11.68	11.78
H/2	5.74	5.84	5.94
H1	7.15 BSC		
L	1.90	2.00	2.10
L1	0.60	0.70	0.80
L2	0.50	0.60	0.70
L3	0.70	0.80	0.90
θ	10° REF		
θ1	10° REF		
aaa	0.20		
bbb	0.25		
ccc	0.20		
ddd	0.20		
eee	0.10		

GENERIC MARKING DIAGRAM*

A = Assembly Location
Y = Year
WW = Work Week
ZZ = Assembly Lot Code
XXXX = Specific Device Code



*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON13813G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**H−PSOF8L 10.38x9.90x2.30, 1.20P**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales