

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



March 2009

FDG410NZ

Single N-Channel PowerTrench $^{\mbox{\it R}}$ MOSFET 20 V, 2.2 A, 70 m $_{\Omega}$

Features

- Max $r_{DS(on)}$ = 70 m Ω at V_{GS} = 4.5 V, I_D = 2.2 A
- Max $r_{DS(on)}$ = 77 m Ω at V_{GS} = 2.5 V, I_D = 2.0 A
- Max $r_{DS(on)}$ = 87 m Ω at V_{GS} = 1.8 V, I_D = 1.8 A
- Max $r_{DS(on)}$ = 115 m Ω at V_{GS} = 1.5 V, I_D = 1.5 A
- HBM ESD protection level > 2 kV (Note 3)
- High performance trench technology for extremely low r_{DS(on)}
- High power and current handling capability
- Fast switching speed
- Low gate charge
- RoHS Compliant




General Description


This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized use in small switching regulaters, providing an extremely low $r_{DS(on)}$ and gate charge $(Q_{\rm g})$ in a small package.

Applications

- DC/DC converter
- Power management
- Load switch



SC70-6



MOSFET Maximum Ratings TA = 25 °C unless otherwise noted

Symbol	Parar		Ratings	Units	
V_{DS}	Drain to Source Voltage			20	V
V_{GS}	Gate to Source Voltage			±8	V
	-Continuous	T _A = 25 °C	(Note 1a)	2.2	Δ.
ID	-Pulsed			6.0	Α
Б	Power Dissipation	T _A = 25 °C	(Note 1a)	0.42	w
P_{D}	Power Dissipation	T _A = 25 °C	(Note 1b)	0.38	VV
T _J , T _{STG}	Operating and Storage Junction Tempe	rature Range		-55 to +150	°C

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1a)	300	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1b)	333	*C/VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
.41	FDG410NZ	SC70-6	7 "	8 mm	3000 units

Electrical Characteristics $T_J = 25$ °C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chara	cteristics					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$	20			V
$\frac{\Delta BV_{DS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25 °C		17		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 16 V, V _{GS} = 0 V			1	μΑ
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 8 \text{ V}, V_{DS} = 0 \text{ V}$			±10	μΑ

On Characteristics

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$	0.4	0.7	1.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25 °C		-3		mV/°C
r _{DS(on)} Stat		$V_{GS} = 4.5 \text{ V}, I_D = 2.2 \text{ A}$		50	70	77 87 mΩ
		$V_{GS} = 2.5 \text{ V}, I_D = 2.0 \text{ A}$		56	77	
	Static Drain to Source On Resistance	$V_{GS} = 1.8 \text{ V}, I_D = 1.8 \text{ A}$		67	87	
		$V_{GS} = 1.5 \text{ V}, I_D = 1.5 \text{ A}$		83	115	
		$V_{GS} = 4.5 \text{ V}, I_D = 2.2 \text{ A},$ $T_J = 125 \text{ °C}$		71	100	
9 _{FS}	Forward Transconductance	$V_{DD} = 5 \text{ V}, I_D = 2.2 \text{ A}$		11		S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 40.V.V 0.V	400	535	pF
Coss	Output Capacitance	$V_{DS} = 10 \text{ V}, V_{GS} = 0 \text{ V},$ $f = 1 \text{ MHz}$	70	95	pF
C _{rss}	Reverse Transfer Capacitance	1 - 1 1/1/12	45	70	pF
R_g	Gate Resistance		2.8		Ω

Switching Characteristics

t _{d(on)}	Turn-On Delay Time		5.3	11	ns
t _r	Rise Time	V _{DD} = 10 V, I _D = 2.2 A,	2.3	10	ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 4.5 \text{ V}, R_{GEN} = 6 \Omega$	18	33	ns
t _f	Fall Time		2.3	10	ns
Q_{g}	Total Gate Charge	45777	5.1	7.2	nC
Q _{gs}	Gate to Source Charge	$V_{GS} = 4.5 \text{ V}, V_{DD} = 10 \text{ V},$ $I_{D} = 2.2 \text{ A}$	0.6		nC
Q_{gd}	Gate to Drain "Miller" Charge	10 - 2.2 A	1.0		nC


Drain-Source Diode Characteristics

I _S	Maximum Continuous Drain-Source Diode Forward Current				0.35	Α
V_{SD}	Source to Drain Diode Forward Voltage $V_{GS} = 0 \text{ V}, I_S = 0.35 \text{ A}$ (Note 2)			0.6	1.2	V
t _{rr}	Reverse Recovery Time	I _E = 2.2 A, di/dt = 100 A/μs		11	20	ns
Q _{rr}	Reverse Recovery Charge	1 _F = 2.2 A, αι/αι = 100 A/μS		2.5	10	nC

The Results of the Re



a. 300 °C/W when mounted on a 1 in² pad of 2 oz copper.



b. 333 °C/W when mounted on a minimum pad of 2 oz copper.

^{2.} Pulse Test: Pulse Width < 300 µs, Duty cycle < 2.0%.
3: The diode connected between the gate and source serves only as protection against ESD. No gate overvoltage rating is implied.

Typical Characteristics T_J = 25 °C unless otherwise noted




Figure 1. On Region Characteristics




Figure 3. Normalized On Resistance vs Junction Temperature




Figure 5. Transfer Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics $T_J = 25$ °C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain to Source Voltage




Figure 9. Forward Bias Safe Operating Area




Figure 10. Gate Leakage Current vs Gate to Source Voltage




Figure 11. Single Pulse Maximum Power Dissipation

Typical Characteristics $T_J = 25$ °C unless otherwise noted








Figure 12. Junction-to-Ambient Transient Thermal Response Curve

Dimensional Outline and Pad Layout









NOTES: UNLESS OTHERWISE SPECIFIED

- A) THIS PACKAGE CONFORMS TO EIAJ SC-88, 1996.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH.

MAA06AREV5





TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

Auto-SPM™ Build it Now™ CorePLUS™ CorePOWER™ $CROSSVOLT^{\text{TM}}$

Current Transfer Logic™ EcoSPARK® EfficentMax™

EZSWITCH™ *

Fairchild[®]

Fairchild Semiconductor® FACT Quiet Series™

FACT[®] FAST® FastvCore[™] FETBench™ FlashWriter® *

F-PFS™ FRFET®

Global Power ResourceSM Green FPS™ Green FPS™ e-Series™

Gmax™ GTO™ IntelliMAX™ ISOPLANAR™ MegaBuck™ MIČROCOUPLER™

MicroFET™ MicroPak™ MillerDrive™ MotionMax™ Motion-SPM™ OPTOLOGIC® OPTOPLANAR®

PDP SPM™ Power-SPM™ PowerTrench[®] PowerXS™

Programmable Active Droop™

OFET® QSTM Quiet Series™ RapidConfigure™

Saving our world, 1mW /W /kW at a time™ SmartMax™

SMART START™ SPM® STEALTH™ SuperFET™ SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS™ SyncFET™

Sync-Lock™ SYSTEM ® The Power Franchise® puwer '

TinyBoost™ TinyBuck™ TinyLogic[®] TINYOPTO™ TinvPower™ TinyPWM™ TinyWire™ TriFault Detect™ TRUECURRENT***

UHC® Ultra FRFET™ UniFET™ VCXTN VisualMax™ XSTM

μSerDes™

*Trademarks of System General Corporation, used under license by Fairchild Semiconductor

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY
FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS **Definition of Terms**

Datasheet Identification Product Status		Definition
Advance Information Formative / In Design		Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary First Production		Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. 140

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and h

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative