MOSFET - POWERTRENCH[®], N-Channel

80 V, 110 A, 2.4 m Ω

FDB86363-F085

Features

- Typical $R_{DS(on)} = 2.0 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 80 \text{ A}$
- Typical $Q_{g(tot)} = 131 \text{ nC}$ at $V_{GS} = 10 \text{ V}$, $I_D = 80 \text{ A}$
- UIS Capability
- AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free, Halide Free and is RoHS Compliant


Applications


- Automotive Engine Control
- Power Train Management
- Solenoid and Motor Drivers
- Integrated Starter/Alternator
- Primary Switch for 12 V Systems



ON Semiconductor®

www.onsemi.com





D²PAK-3 (TO-263, 3-LEAD) CASE 418AJ

PIN CONFIGURATION

Position	Designation
Pin 1	Gate
Pin 2 / Tab	Drain
Pin 3	Source

MARKING DIAGRAM

	O \$Y&Z&3&K FDB86363
\$Y &Z &3 &K FDB86363	 = ON Semiconductor Logo = Assembly Plant Code = Numeric Date Code = Lot Code = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

MOSFET MAXIMUM RATINGS (T_J = 25°C, Unless otherwise noted)

Symbol	Parameter		Ratings	Units
V _{DSS}	Drain-to-Source Voltage		80	V
V _{GS}	Gate-to-Source Voltage		±20	V
I _D	Drain Current –Continuous (V_{GS} = 10 V) (Note 1) T_{C} = 25°C		110	А
	-Pulsed	$T_C = 25^{\circ}C$	See Figure 4	
E _{AS}	Single Pulse Avalanche Energy	(Note 2)	512	mJ
PD	Power Dissipation		300	W
	Derate Above 25°C		2.0	W/∘C
TJ, T _{STG}	Operating and Storage Temperature		-55 to +175	°C
ReJC	Thermal Resistance, Junction to Case		0.5	°C/W
Reja	Maximum Thermal Resistance, Junction to Ambient	(Note 3)	43	°C/W

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Current is limited by bondwire configuration. 2. Starting $T_J = 25^{\circ}$ C, L = 0.25 mH, I_{AS} = 64 A, V_{DD} = 80 V during inductor charging and V_{DD} = 0 V during time in avalanche. 3. R_{0JA} is the sum of the junction–to–case and case–to–ambient thermal resistance, where the case thermal reference is defined as the solder mounting surface of the drain pins. Rejc is guaranteed by design, while RejA is determined by the board design. The maximum rating presented here is based on mounting on a 1 in² pad of 2 oz copper.

PACKAGE MARKING AND ORDERING INFORMATION

Device Marking	Device	Package	Shipping [†]
FDB86363	FDB86363-F085	D2PAK (TO–263) (Pb–Free/Halide Free)	800 units / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D

FDB86363-F085

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Units		
OFF CHAR	OFF CHARACTERISTICS							
B _{VDSS}	Drain-to-Source Breakdown Voltage	$I_D = 250 \ \mu A, \ V_{GS} = 0 \ V$	80			V		
I _{DSS}	Drain-to-Source Leakage Current	V_{DS} = 80 V, V_{GS} = 0 V, T_{J} = 25°C			1	μΑ		
	Current	$V_{DS} = 80 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 175^{\circ}\text{C} \text{ (Note 4)}$			1	mA		
I _{GSS}	Gate-to-Source Leakage Current	$V_{GS} = \pm 20 \text{ V}$			±100	nA		

ON CHARACTERISTICS

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \ \mu A$	2.0	3.0	4.0	V
R _{DS(on)}	DS(on) Drain-to-Source On-Resistance	$I_D = 80 \text{ A}, \text{ V}_{GS} = 10 \text{ V}, \text{ T}_J = 25^{\circ}\text{C}$		2.0	2.4	mΩ
		I_D = 80 A, V_{GS} = 10 V, T_J = 175°C (Note 4)		3.8	4.3	

DYNAMIC CHARACTERISTICS

C _{iss}	Input Capacitance	$V_{DS} = 40 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		10000		pF
C _{oss}	Output Capacitance			1400		pF
C _{rss}	Reverse Transfer Capacitance			95		pF
Rg	Gate Resistance	f = 1 MHz		3.3		Ω
Q _{g(TOT)}	Total Gate Charge	$V_{GS} = 0 V$ to 10 V	$V_{DD} = 64 \text{ V}, I_D = 80 \text{ A}$	131	150	nC
Q _{g(th)}	Threshold Gate Charge	$V_{GS} = 0 V \text{ to } 2 V$		18	21	nC
Q _{gs}	Gate-to-Source Gate Charge		-	47		nC
Q _{gd}	Gate-to-Drain "Miller" Charge			24		nC

SWITCHING CHARACTERISTICS

t _{on}	Turn–On Time	V_{DD} = 40 V, I_D = 80 A, V_{GS} = 10V, R_{GEN} = 6 Ω		231	ns
t _{d(on)}	Turn–On Delay		38		ns
t _r	Rise Time		129		ns
t _{d(off)}	Turn-Off Delay		64		ns
t _f	Fall Time		40		ns
t _{off}	Turn–Off Time			135	ns

DRAIN-SOURCE DIODE CHARACTERISTICS


V _{SD}	Source-to-Drain Diode Voltage	$V_{GS} = 0 V, I_{SD} = 80 A$ $V_{GS} = 0 V, I_{SD} = 40 A$		1.25 1.2	V
t _{rr}	Reverse–Recovery Time	I_{F} = 80 A, $\Delta I_{SD}/\Delta t$ = 100 A/µs, V_{DD} = 64 V	88	101	ns
Q _{rr}	Reverse–Recovery Charge		129	157	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. The maximum value is specified by design at $T_J = 175^{\circ}$ C. Product is not tested to this condition in production.

FDB86363-F085

TYPICAL CHARACTERISTICS








Figure 2. Maximum Continuous Drain Current vs. Case Temperature




Figure 3. Normalized Maximum Transient Thermal Impedance




Figure 4. Peak Current Capability

TYPICAL CHARACTERISTICS




Figure 5. Forward Bias Safe Operating Area




Figure 7. Transfer Characteristics




Figure 9. Saturation Characteristics




Figure 6. Unclamped Inductive Switching Capability




Figure 8. Forward Diode Characteristics




Figure 10. Saturation Characteristics

FDB86363-F085

TYPICAL CHARACTERISTICS






Figure 11. R_{DSON} vs. Gate Voltage








Figure 15. Capacitance vs. Drain to Source Voltage




Figure 12. Normalized R_{DSON} vs. Junction Temperature





Figure 14. Normalized Drain to Source Breakdown Voltage vs. Junction Temperature







POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS









© Semiconductor Components Industries, LLC, 2018

rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>