

MOSFET – Single N-Channel, Logic Level, POWERTRENCH®

30 V, 6.1 A, 27 m Ω

FDC855N

General Description

This N-Channel Logic Level MOSFET is an efficient solution for low voltage and battery powered applications. Utilizing **onsemi**'s advanced POWERTRENCH process, this device possesses minimized on–state resistance to optimize the power consumption. They are ideal for applications where in–line power loss is critical.

Features

- Max $r_{DS(on)} = 27 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, $I_D = 6.1 \text{ A}$
- Max $r_{DS(on)} = 36 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, $I_D = 5.3 \text{ A}$
- SUPERSOT[™] -6 Package: Small Footprint (72% smaller than Standard SO-8) Low Profile (1 mm thick)
- This Device is Pb-Free and is RoHS Compliant

Application

• Power Management in Notebook, Hard Disk Drive

MOSFET MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

Symbol	Para	Ratings	Units	
V _{DS}	Drain to Source Voltage		30	V
V_{GS}	Gate to Source Voltage		±20	V
I _D	Drain Current Continuous (Note 1a)		6.1	Α
		Pulsed	20	Α
P_{D}	Power Dissipation (Note 1a)		1.6	W
(Steady State)		(Note 1b)	0.8	
T _J , T _{STG}	Operating and Storage Junction Temperature Range		-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Ratings	Units
Rejc	Thermal Resistance, Junction to Case (Note 1)	30	°C/W
RθJA	Thermal Resistance, Junction to Ambient (Note 1a)	78	°C/W

V _{DS}	r _{DS(on)} MAX I _D MAX	
30 V	27 mΩ @ 10 V	6.1 A
	36 mΩ @ 4.5 V	5.3 A



TSOT23 6-Lead SUPERSOT™-6 CASE 419BL

MARKING DIAGRAM




.855 = Specific Device Code

M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

PINOUT



ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
OFF CHARA	ACTERISTICS					
BV _{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$	30	_	_	V
ΔBV_{DSS}	Breakdown Voltage Temperature	I _D = 250 μA, referenced to 25°C	-	24	-	mV/°C
ΔT_{J}	Coefficient					
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V	-	-	1	μΑ
		V _{DS} = 24 V, V _{GS} = 0 V, T _C = 125°C	-	-	250	
I_{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$	-	-	±100	nA
ON CHARAC	CTERISTICS					
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$	1.0	2.0	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I _D = 250 μA, referenced to 25°C	-	-6	-	mV/°C
r _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 6.1 A	-	20.7	27.0	mΩ
	,	V _{GS} = 4.5 V, I _D = 5.3 A	-	28.2	36.0	1
		V _{GS} = 10 V, I _D = 6.1 A, T _J = 125°C	-	30.1	39.3	1
9FS	Forward Transconductance	V _{DD} = 10 V, I _D = 6.1 A	-	20	-	S
DYNAMIC (CHARACTERISTICS					
C _{iss}	Input Capacitance	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz	-	493	655	pF
C _{oss}	Output Capacitance		-	108	145	pF
C _{rss}	Reverse Transfer Capacitance		-	62	95	pF
Rg	Gate Resistance	f = 1 MHz	-	1.0	-	Ω
SWITCHING	CHARACTERISTICS					
t _{d(on)}	Turn-On Delay Time	V _{DD} = 15 V, I _D = 6.1 A,	-	6	12	ns
t _r	Rise Time	$V_{GS} = 10 \text{ V}, R_{GEN} = 6 \Omega$	-	2	10	ns
t _{d(off)}	Turn-Off Delay Time		-	14	23	ns
t _f	Fall Time		_	2	10	ns
Qg	Total Gate Charge at 10 V	$V_{GS} = 0 \text{ V to } 10 \text{ V}, V_{DD} = 15 \text{ V}, I_D = 6.1 \text{ A}$	-	9.2	13	nC
	Total Gate Charge at 5 V	V _{GS} = 0 V to 5 V, V _{DD} = 15 V, I _D = 6.1 A	-	4.9	7.0	nC
Q _{gs}	Gate to Source Charge	V _{DD} = 15 V, I _D = 6.1 A	-	1.7	_	nC
Q _{gd}	Gate to Drain "Miller" Charge		-	3.1	-	nC
DRAIN-SOU	JRCE DIODE CHARACTERISTICS					
V _{SD}	Source-Drain Diode Forward Voltage	V _{GS} = 0 V, I _S = 1.3 A (Note 2)	-	0.80	1.2	V
t _{rr}	Reverse Recovery Time	I _F = 6.1 A, di/dt = 100 A/μs	-	17	31	ns
Q _{rr}	Reverse Recovery Charge		-	6	12	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

R_{0,JA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{0,JC} is guaranteed by design while R_{0,CA} is determined by the user's board design.



a. 78°C/W when mounted on
a 1 in² pad of 2 oz. copper



b. 156°C/W when mounted on a minimum pad of 2 oz. copper

2. Pulse Test: Pulse Width < 300 $\mu s,$ Duty cycle < 2.0 %.

TYPICAL CHARACTERISTICS

 $(T_J = 25^{\circ}C \text{ unless otherwise noted})$




Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage




Figure 3. Normalized On–Resistance vs Junction Temperature




Figure 4. On-Resistance vs Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs Source Current

TYPICAL CHARACTERISTICS (continued)

 $(T_J = 25^{\circ}C \text{ unless otherwise noted})$




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs Drain




Figure 9. Forward Bias Safe Operating Area




Figure 10. Single Pulse Maximum Power Dissipation




Figure 11. Transient Thermal Response Curve

ORDERING INFORMATION

Device	Device Marking	Package Type	Shipping [†]
FDC855N	.855	TSOT-23-6 (Pb-free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


POWERTRENCH is registered trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.


SUPERSOT is a trademark of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries.





TSOT23 6-Lead CASE 419BL **ISSUE A**

DATE 31 AUG 2020









SIDE VIEW

03/1414

SYMM
Ę
0.95
1.00 MIN
2.60
0.70 MIN

LAND PATTERN RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
- CONTROLLING DIMENSION: MILLIMETERS
 DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH,
 PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.25MM PER END. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM H.
- 4. SEATING PLANE IS DEFINED BY THE TERMINALS. "A1" IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

DIM	MILLIMETERS			
5,101	MIN.	NOM.	MAX.	
Α	0.90	1.00	1.10	
A1	0.00	0.05	0.10	
A2	0.70	0.85	1.00	
A3	0.25 BSC			
b	0.25	0.38	0.50	
С	0.10	0.18	0.26	
D	2.80	2.95	3.10	
d		0.30 RE	=	
Е	2.50	2.75	3.00	
E1	1.30	1.50	1.70	
е	0.95 BSC			
e1	1.90 BSC			
L1	0.60 REF			
L2	0.20	0.40	0.60	
θ	0°		10°	

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code

= Date Code Μ

= Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON83292G	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	TSOT23 6-Lead		PAGE 1 OF 1	

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales